

AGILA

2475ETP035P30-11

EAN 4031582438253



BETTER MOBILITY. BETTER LIFE.

Swivel castor with wheel brake, housing made of pressed steel, bright zinc plated, blue passivated, double ball bearing swivel head, bolt hole.

Wheel centre made of steel, Tread: Polyurethane, casted, precision ball bearing. Castors can be mounted with standard screws of any length.



Picture may differ from original product

Technical Data

Wheel diameter	35 mm
Wheel width	25 mm
Centre hole	11 mm
Offset	20 mm
Swivel Interference	62 mm
Overall height	58 mm
Temperature	- 20 / + 60 °C
Standard	EN_12530
Weight	0.215 kg
Swivel Radius	37.5 mm
Hardness of tread	Shore A 92
Load capacity	100 kg
Load capacity (static)	200 kg

Advantages at a glance

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○