

Eaton 192131

Catalog Number: 192131

Eaton Moeller series NZM - Molded Case Circuit Breaker. NZM2 PXR25 circuit breaker - integrated energy measurement class 1, 250A, 3p, box terminal, S, 2



General specifications

Product Name	Catalog Number
Eaton Moeller series NZM molded case circuit breaker electronic	192131
	EAN
	4015081926824
Product Length/Depth	Product Height
190 mm	160 mm
Product Width	Product Weight
115 mm	2.4 kg
Compliances	Certifications
RoHS conform	IEC/EN 60947
	IEC

Product specifications

Type

Circuit breaker

Special features

LSI overload protection and delayed and non-delayed short-circuit protective device

Class 1 energy measurement, r.m.s. value measurement, and "thermal memory"

USB interface for configuration and test function with Power Xpert

Protection Manager software

Interface module in equipment supplied.

Optionally communication-capable with internal

Modbus RTU module or CAM

Maximum back-up fuse, if the expected short-circuit currents at the installation location exceed the switching capacity of the circuit breaker (Rated short-circuit breaking capacity I_{cn})

Rated current = rated uninterrupted current: 250 A

Application

Use in unearthed supply systems at 690 V

Amperage Rating

250 A

Voltage rating

690 V - 690 V

Circuit breaker frame type

NZM2

Features

Protection unit

Resources

Brochures

[eaton-feerum-the-whole-grain-solution-success-story-en-us.pdf](#)

[eaton-digital-nzm-brochure-br013003en-en-us.pdf](#)

Catalogs

[eaton-digital-nzm-catalog-ca013003en-en-us.pdf](#)

Characteristic curve

[eaton-circuit-breaker-nzm-mccb-characteristic-curve-020.eps](#)

[eaton-circuit-breaker-nzm-mccb-characteristic-curve-024.eps](#)

Drawings

[eaton-circuit-breaker-nzm-mccb-dimensions-019.eps](#)

[eaton-circuit-breaker-switch-nzm-mccb-dimensions-017.eps](#)

Installation instructions

[eaton-circuit-breakers-nzmb-nzmn-basic-unit-bg2-instruction-leaflet-il012099zu.pdf](#)

Installation videos

[Introduction of the new digital circuit breaker NZM](#)

[The new digital NZM Range](#)

mCAD model

[DA-CS-nzm2_3p](#)

[DA-CD-nzm2_3p](#)

Technical data sheets

[eaton-nzm-technical-information-sheet](#)

Motor drive optional

10.10 Temperature rise

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

10.11 Short-circuit rating

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.12 Electromagnetic compatibility

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.13 Mechanical function

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

10.2.2 Corrosion resistance

Meets the product standard's requirements.

10.2.3.1 Verification of thermal stability of enclosures

Meets the product standard's requirements.

10.2.3.2 Verification of resistance of insulating materials to normal heat

Meets the product standard's requirements.

10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects

Meets the product standard's requirements.

10.2.4 Resistance to ultra-violet (UV) radiation

Meets the product standard's requirements.

10.2.5 Lifting

Does not apply, since the entire switchgear needs to be evaluated.

10.2.6 Mechanical impact

Does not apply, since the entire switchgear needs to be evaluated.

10.2.7 Inscriptions

Meets the product standard's requirements.

10.3 Degree of protection of assemblies

Does not apply, since the entire switchgear needs to be evaluated.

10.4 Clearances and creepage distances

Meets the product standard's requirements.

10.5 Protection against electric shock

Does not apply, since the entire switchgear needs to be evaluated.

10.6 Incorporation of switching devices and components

Does not apply, since the entire switchgear needs to be evaluated.

10.7 Internal electrical circuits and connections

Is the panel builder's responsibility.

10.8 Connections for external conductors

Is the panel builder's responsibility.

10.9.2 Power-frequency electric strength

Is the panel builder's responsibility.

10.9.3 Impulse withstand voltage

Is the panel builder's responsibility.

10.9.4 Testing of enclosures made of insulating material

Is the panel builder's responsibility.

Pollution degree

3

Mounting Method

Built-in device fixed built-in technique

DIN rail (top hat rail) mounting optional

Fixed

Climatic proofing

Damp heat, cyclic, to IEC 60068-2-30

Damp heat, constant, to IEC 60068-2-78

Equipment heat dissipation, current-dependent

51.56 W

Utilization category

A (IEC/EN 60947-2)

Isolation

500 V AC (between auxiliary contacts and main contacts)

300 V AC (between the auxiliary contacts)

Ambient operating temperature - max

70 °C

Ambient operating temperature - min

-25 °C

Ambient storage temperature - max

70 °C

Ambient storage temperature - min

40 °C

Number of auxiliary contacts (change-over contacts)

0

Number of auxiliary contacts (normally closed contacts)

0

Number of auxiliary contacts (normally open contacts)

0

Protection against direct contact

Finger and back-of-hand proof to DIN EN 50274/VDE 0106 part
110

Degree of protection

IP20 (basic degree of protection, in the operating controls area)
IP20

Direction of incoming supply

As required

Electrical connection type of main circuit

Frame clamp

Lifespan, mechanical

20000 operations

Overvoltage category

III

Degree of protection (IP), front side

IP66 (with door coupling rotary handle)
IP40 (with insulating surround)

Degree of protection (terminations)

IP00 (terminations, phase isolator and strip terminal)
IP10 (tunnel terminal)

Number of poles

Three-pole

Terminal capacity (copper strip)

Min. 2 segments of 9 mm x 0.8 mm at box terminal
Max. 10 segments of 24 mm x 0.8 mm at rear-side connection
(punched)
Max. 8 segments of 24 mm x 1 mm (2x) at box terminal
Max. 10 segments of 16 mm x 0.8 mm at box terminal
Min. 2 segments of 16 mm x 0.8 mm at rear-side connection
(punched)

Lifespan, electrical

10000 operations at 415 V AC-1
7500 operations at 690 V AC-1
10000 operations at 400 V AC-1

Functions

Systems, cable, selectivity and generator protection

Shock resistance

20 g (half-sinusoidal shock 20 ms)

Position of connection for main current circuit

Front side

Rated operational current for specified heat dissipation (I_n)

250 A

Power loss

51.56 W

Release system

Electronic release

Short-circuit total breaktime

< 10 ms

Rated short-time withstand current ($t = 0.3$ s)

1.9 kA

Rated short-time withstand current ($t = 1$ s)

1.9 kA

Short-circuit release delayed setting - max

2500 A

Short-circuit release delayed setting - min

200 A

Short-circuit release non-delayed setting - max

3000 A

Short-circuit release non-delayed setting - min

500 A

Terminal capacity (control cable)

0.75 mm² - 1.5 mm² (2x)

0.75 mm² - 2.5 mm² (1x)

Terminal capacity (copper busbar)

M8 at rear-side screw connection

Max. 24 mm x 8 mm direct at switch rear-side connection

Min. 16 mm x 5 mm direct at switch rear-side connection

Terminal capacity (copper solid conductor/cable)

16 mm² (1x) at tunnel terminal

6 mm² - 16 mm² (2x) at box terminal

10 mm² - 16 mm² (1x) at box terminal

10 mm² - 16 mm² (1x) direct at switch rear-side connection

6 mm² - 16 mm² (2x) direct at switch rear-side connection

Terminal capacity (aluminum solid conductor/cable)

16 mm² (1x) at tunnel terminal

Terminal capacity (copper stranded conductor/cable)

25 mm² - 70 mm² (2x) at box terminal

25 mm² - 185 mm² (1x) at box terminal

25 mm² - 185 mm² (1x) at 1-hole tunnel terminal

25 mm² - 185 mm² (1x) direct at switch rear-side connection

25 mm² - 70 mm² (2x) direct at switch rear-side connection

Terminal capacity (aluminum stranded conductor/cable)

25 mm² - 185 mm² (1x) at tunnel terminal

Handle type

Rocker lever

Short delay current setting (I_{sd}) - max

10 A

Short delay current setting (I_{sd}) - min

2 A

Instantaneous current setting (I_i) - max

12 A

Instantaneous current setting (I_i) - min

2 A

Number of operations per hour - max

120

Overload current setting (I_r) - max

250 A

Overload current setting (I_r) - min

100 A

Rated short-circuit breaking capacity I_{cs} (IEC/EN 60947) at 230 V, 50/60 Hz

100 kA

Rated short-circuit breaking capacity I_{cs} (IEC/EN 60947) at 400/415 V, 50/60 Hz

70 kA

Rated short-circuit breaking capacity I_{cs} (IEC/EN 60947) at 440 V, 50/60 Hz

65 kA

Rated short-circuit breaking capacity I_{cs} (IEC/EN 60947) at 525 V, 50/60 Hz

36 kA

Rated short-circuit breaking capacity I_{cs} (IEC/EN 60947) at 690 V, 50/60 Hz

5 kA

Rated short-circuit making capacity I_{cm} at 400/415 V, 50/60 Hz

154 kA

Rated short-circuit making capacity I_{cm} at 440 V, 50/60 Hz

143 kA

Rated short-circuit making capacity I_{cm} at 525 V, 50/60 Hz

80 kA

Rated short-circuit making capacity I_{cm} at 690 V, 50/60 Hz

40 kA

Standard terminals

Box terminal

Optional terminals

Connection on rear. Screw terminal. Tunnel terminal

Rated short-circuit making capacity I_{cm} at 240 V, 50/60 Hz

220 kA

Rated impulse withstand voltage (U_{imp}) at auxiliary contacts

6000 V

Rated impulse withstand voltage (U_{imp}) at main contacts

8000 V

Rated insulation voltage (U_i)

690 V AC



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia