



PRODUCT-DETAILS

SPLHCB16/25M

16MM GS-TPR COND SS BRD 25M-BL



General Information

Extended Product Type:	SPLHCB16/25M
Product ID:	7TCA296100R0169
EAN:	5020963010576
Catalog Description:	16MM GS-TPR COND SS BRD 25M-BL
Long Description:	Liquid Tight, Extreme Temperature Covered Steel Flexible Conduit with Stainless Steel Overbraid, Medium Flexibility, Nominal Conduit Size 16mm, 3/8 Inch US Conduit Size, Outside Diameter 17.8mm, Inside Diameter 12.5mm, Static Bend Radius 50mm, Reel Length 25 Meters, Thermoplastic Rubber Cover with Galvanised Steel Core, Black
Display Name:	SPLHCB16/25M

Additional Information

Product Main Type:	Adaptaflex Flexible Cable Protection
Application:	Liquid Tight - Extreme Temperature Environments

Ordering

EAN: 5020963010576

UPC: 786210245492

Dimensions

Outside Diameter: 17.8 mm

Technical

Number of Batteries: 0

Color: Black

Material: Galvanized Steel Core with Thermoplastic Rubber Cover

Environmental

WEEE Category: Product Not in WEEE Scope

RoHS Information: Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019

Container Information

Package Level 1 Units: 1 piece

Package Level 1 EAN: 5020963010576

Package Level 1 Height: 6 in
152 mm

Package Level 1 Depth / Length: 16 in
406 mm

Package Level 1 Width: 16 in
406 mm

Certificates and Declarations

Declaration of Conformity - CE: 9AKK107492A9618

RoHS Declaration: 9AKK107992A8994

REACH Declaration: 9AKK107992A8994

External Classifications and Standards

ETIM 8: EC001179 - Protective metallic hose

ETIM 9: EC001179 - Protective metallic hose

UNSPSC: 39131706

Categories

Products > Low Voltage Products and Systems > Installation Products > Cable Protection, Explosion Proof and Lighting > Flexible Cable Protection Systems

