

Fuse terminal Screw terminal for G fuse link 5x 20 mm and 5x 25 mm with LED 230V



Figure similar

Model	
product brand name	ALPHA
type of light source / as fault indicator	LED
design of the fuse link	glass fuse 5x25 mm
design of fuse holder	pluggable
General technical data	
insulation material	thermoplastic
terminal contact spacing	10 mm
Supply voltage	
operating voltage / rated value	250 V
type of voltage / for supply of the fault indicator	AC/DC
Protection class	
combustibility class acc. to UL 94	Other
Main circuit	
operating current / rated value	6.3 A

## Appearance

color	miscellaneous
-------	---------------

## Product details

product component / required / connection plate	No
---	----

## Number

number of terminal levels	1
---------------------------	---

## Connections

connectable conductor cross-section / solid	
• minimum	1 mm <sup>2</sup>
• maximum	1 mm <sup>2</sup>
connectable conductor cross-section / stranded	
• maximum	1.5 mm <sup>2</sup>
connectable conductor cross-section / finely stranded	
• with core end processing / minimum	0.75 mm <sup>2</sup>
• with core end processing / maximum	1.5 mm <sup>2</sup>
type of electrical connection	
• 1	screw-type terminal
• 2	screw-type terminal
position / of the terminal	lateral

## Mechanical Design

height / with lowest-profile installation	42 mm
length	57 mm
mounting type	DIN rail 35 mm
material / of the insulating body	Thermoplast

## Certificates

General Product Approval	Declaration of Conformity	other
--------------------------	---------------------------	-------



[Environmental Confirmations](#)

## Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8WA1011-1SF15>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/8WA1011-1SF15>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=8WA1011-1SF15](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8WA1011-1SF15)

**CAx-Online-Generator**  
<http://www.siemens.com/cax>

**Tender specifications**  
<http://www.siemens.com/specifications>