

### Soft Start-up Valve

# AV2000/3000/4000/5000



Series AV5000 introduced!

A start-up valve that gradually increases supply pressure during start up and rapidly exhausts system air when the supply air is shut off

### Large effective area (mm<sup>2</sup>)

Manual supply/exhaust function

- Low power consumption
- Modular with F.R.L. combinations

F.R.L. combination

AV2000/ 20 (Body size: 1/4) AV3000/ 37 (Body size: 3/8) AV4000/ 61 (Body size: 1/2) AV5000/113 (Body size: 3/4) AV5000/122 (Body size: 1)

### F.R.L. combinations



# Soft Start-up Valve AV2000/3000/4000/5000

How to Order



Consult SMC for details when ordering  $T\ddot{U}V$  approved products because of restrictions regarding product model, voltage specification, and electrical entry, etc.

Soft Start-up Valve AV2000/3000/4000/5000



Type D DIN terminal



Type Y DIN terminal



#### Accessories/Pressure gauge

	an loocale gaage
Description	Pressure gauge
Part no.	G36-10-01
Pressure range	1MPa

### **Specifications**

	Mode	1	AV2000	AV3000	AV4000	AV5	000				
Ро	rt size		1/4	3/8	1/2	3/4	1				
Pro	oof pressure			1.5MPa							
Ор	erating press	ure range	0.2 to 1MPa								
Pre	essure gauge	port size			1/8						
Am	bient and fluid	temperature			0 to 6	60°C Note 1)					
Eff	ective area	1(P)→2(A)	20	37	61	113	122				
(m	m²)	2(A)→3(R)	24	49	76	132	141				
We	eight (kg)		0.27	0.48	0.74	0.74 1.60					
s	Rated coil vo	Itage	100, 200,	100, 200, 110 to 120, 220VAC (50/60Hz), 12, 24VDC							
tion	Allowable volta	ge fluctuatior	-15% to +10% of rated voltage								
icat	Coil insulatio	n type		Equivalent to B type (130°C)							
specifications	Apparent power (current	AC Inrush	5.6VA (50Hz), 5.0VA (60Hz)								
ll sp	consumption)	Energized	3.4VA (2.1W)/50Hz, 2.3VA (1.5W)/60Hz								
rica	Current consi	umption DC		1.8W							
Electrical	Electrical ent	ry	Туре	Type D DIN terminal, Type Y DIN terminal							
ш	Optional spec	cification	Indica	Indicator light/Surge voltage suppressor Note 2)							
Pil	ot valve manu	al override	Non-locking push type (flush type), Locking type (tool required), Locking type (lever type)								

Note 1) Use dry air when operating at a low temperature.

Note 2) The grommet type can have a surge voltage suppressor (direct coupling type lead wire), but without indicator light.

### Piston B switching pressure (Open→Closed)



#### Needle valve flow characteristics Conditions: Primary pressure 0.5MPa





### AV2000/3000/4000/5000

### **Working Principle**





Working condition	Pilot valve	Pressure conditions	Working description	Pressure time chart (meter-out control) example	Cylinder drive circuit (meter-out control) example		
Low speed supply		1/2 Pp > PA	When pilot valve (a) sturned ON by ener - gization or manual override, the pilot air pushes piston A(3) and main valve (1) downward and opens main valve (1) while R port closes simultaneously. The air from P port moves to needle valve (2) where its flow is adjusted, and flows to A port. The meter-in control of needle valve (3) owly moves the cylinder from (A) to (B).	Initial operation return stroke			
High speed supply	ON	1/2 Pp ≤ PA	When $1/2 PP \le PA$ after the cylinder rea- che®, piston ® fully opens and PA in- creases rapidly as shown from © to $\bigcirc$ and becomes the same pressure as PP.	Time			
Normal operation		1/2 PP = approx. PA		ince piston B $(5)$ holds the fully open condition, during normal operation the /linder's speed will be controlled by the usual meter-out control.			
Quick exhaust	OFF	_	When pilot valve ② is turned OFF, spring ④ ① upward and opens R port while shutting pressure difference generated at this time of pressure on the A port side is quickly exhau	PP 1(P) 3(R) PA PA PA PA PA PA V V V V V V V V V V V V V			

### Soft Start-up Valve AV2000/3000/4000/5000

### Construction





#### Parts list

No.	Description	Material
1	Body	ADC
2	Сар	ADC
3	Cover	ADC

#### **Replacement parts**

No.	Description	Material		Part no.					
INO.	Description	Material	AV2000	AV3000	AV4000	AV5000			
4	Pilot valve assembly			SF4-	□-80 <sup>*</sup>				
5	Piston A assembly	POM, NBR	P424204A	P424304A	P424404A	P424504A			
6	Piston B assembly	Brass, NBR (HNBR)	P424205A	P424305A	P424405A	P424505A			
7	Main valve assembly	Brass, NBR (HNBR)	P424206A	P424306A	P424406A	P424506A			
8	Check valve	Brass, NBR (HNBR)	P424207	P424307	P424407	P424507			
9	Piston guide assembly	POM, NBR	P424208A	P424308A	P424408A	P424508A			
10	Needle assembly	Brass, NBR	P424209A	P424309A	P424409A	P424509A			
11	Valve spring	Steel wire	P424211	P424311	P424411	P424511			
12	Piston spring	ston spring Stainless steel		P424212 P424312		P424512			
13	Check spring Stainless steel		P424213	P424213 P424313		P424513			
14	Needle spring	Steel wire	P424214	P424314	P424414	_			
15	C type snap ring for shaft	Tool steel	G-5	STW-5	STW-8	STW-10			
16	C type snap ring for hole	Tool steel	0-9	0-10	RTW-12	RTW-15			
17	Seal	NBR	P424210	P424310	P424410	P424510			
18	Seal	NBR	P424218	P424315	P424415	P424514			
19	O-ring	NBR	10 x 8 x 1	11 x 9 x 1	12.5 x 9.5 x 1.5	16.5 x 12.5 x 2			

\* Refer to page 1 for pilot valve assembly part number designations.

**SMC** 

### AV2000/3000/4000/5000

### Dimensions

DIN terminal: AV 00-0-0, DZ DIN terminal for European use: AV 00-0-0Y, YZ



Model	Port size	A	в	с	D	Е	G	н	I	к	L	м	Ν	Р	Q	R
AV2000-02-0G AV2000-02-0GS	1/4	66	105	31	22	40	38	0	47.5		_	_	93	29	23.5	M4 x 0.7 Depth 4.5
AV2000-02-00 AV2000-02-0D	1/4	66	125	31	22	40	38	0	_	65.5 —	— 82.5	6 23	_	29	23.5	M4 x 0.7 Depth 4.5
AV2000-02-04 AV2000-02-042	1/4	66	125	31	22	40	38	0	_	67.5 —	 84.5	10.5 27.5	_	29	23.5	M4 x 0.7 Depth 4.5
AV3000-03-0G AV3000-03-0GS	3/8	76	112	36	24	48	43	2	50.5	_	-	_	100	28	27.5	M5 x 0.8 Depth 5
AV3000-03-00 AV3000-03-0DZ	3/8	76	132	36	24	48	43	2	_	66.5	— 83.5			28	27.5	M5 x 0.8 Depth 5
AV3000-03-0Y AV3000-03-0YZ	3/8	76	132	36	24	48	43	2	_	70.5	— 87.5	3.5 20.5		28	27.5	M5 x 0.8 Depth 5
AV4000-04-0G AV4000-04-0GS	1/2	98	127	47	32	52	57	3	62.5	_	_	_	115	42	37	M6 x 1 Depth 6
AV4000-04-00 AV4000-04-02	1/2	98	147	47	32	52	57	3	_	78.5	— 95.5	6	_	42	37	M6 x 1 Depth 6
AV4000-04-04 AV4000-04-042	1/2	98	147	47	32	52	57	3	_	82.5	— 99.5	— 10.5	_	42	37	M6 x 1 Depth 6
AV5000-□%-□G□ AV5000-□%-□GS□	3/4, 1	128	155	59	39	74	77	0	74	_	_	_	143	50	46	M6 x 1 Depth 7.5
AV5000-□%-□D□ AV5000-□%-□DZ□	3/4, 1	128	175	59	39	74	77	0	_	90	— 107		_	50	46	M6 x 1 Depth 7.5
AV5000-□%-□Y□ AV5000-□%-□YZ□	3/4, 1	128	175	59	39	74	77	0	_	94	— 111			50	46	M6 x 1 Depth 7.5

### Modular F.R.L. Combination Spacer

Select one of the spacers below when connecting to an F.R.L. combination unit (AC2000 to AC6000). (Spacers must be ordered separately.)



### Spacer



Model	Applicable model
Y200-A	AV2000
Y300-A	AV3000
Y400-A	AV4000
Y600-A	AV5000

### Spacer with bracket





Y200T-A

Y400T-A

Model	Applicable model
Y200T-A	AV2000
Y300T-A	AV3000
Y400T-A	AV4000
Y600T-A	AV5000

# Series AV2000/3000/4000/5000 Safety Instructions

These safety instructions are intended to prevent a hazardous situation and /or equipment damage. These instructions indicate the level of potential hazard by a label of **"Caution"**, **"Warning" or "Danger"**. To ensure safety, be sure to observe ISO 4414 Note 1), JIS B 8370 Note 2) and other safety practices.



Note 2) JIS B 8370 : General Rules for Pneumatic Equipment.

### **Warning**

- The compatibility of pneumatic equipment is the responsibility of the person who designs the pneumatic system or decides its specifications.
  Since the products specified here are used in various operating conditions, their compatibility for the specific pneumatic system must be based on specifications or after analysis and/or tests to meet your specific requirements.
- 2. Only trained personnel should operate pneumatically operated machinery and equipment.

Compressed air can be dangerous if an operator is unfamiliar with it. Assembly, handling or repair of pneumatic systems should be performed by trained and experienced operators.

- 3. Do not service machinery/equipment or attempt to remove components until safety is confirmed.
- 1. Inspection and maintenance of machinery/equipment should only be performed after confirmation of safe locked-out control positions.
- 2. When equipment is to be removed, confirm the safety process as mentioned above. Cut the supply pressure for this equipment and exhaust all residual compressed air in the system.
- 3. Before machinery/equipment is restarted, take measures to prevent shooting-out of cylinder piston rod, etc. (Bleed air into the system gradually to create back pressure.)
- 4. Contact SMC if the product is to be used in any of the following conditions:
- 1. Conditions and environments beyond the given specifications, or if product is used outdoors.
- 2. Installation on equipment in conjunction with atomic energy, railway, air navigation, vehicles, medical equipment, food and beverages, recreation equipment, emergency stop circuits, press applications, or safety equipment.
- 3. An application which has the possibility of having negative effects on people, property, or animals, requiring special safety analysis.



### AV2000/3000/4000/5000 Specific Product Precautions 1

Be sure to read before handling. Refer to page 7 for safety instructions.

Design

### **Warning** 1. Actuator drive

When a component such as a solenoid valve or actuator is to be driven using this product, take appropriate measures to prevent potential danger caused by actuator operation.

### 2. Holding of pressure

Since the products are subject to air leakage (allowed), they cannot be used for applications such as holding pressure in a pressure vessel.

### 3. Maintenance space

The installation should allow sufficient space for maintenance activities.

Selection

## **A**Warning

### 1. Confirm the specifications.

The products presented in this catalog are designed only for use in compressed air systems. Do not operate at pressures or temperatures, etc., beyond the range of specifications, as this can cause damage or malfunction. (Refer to specifications.)

Contact SMC when using a fluid other than compressed air.

### 2. Extended periods of continuous energization Contact SMC if valves will be continuously energized for

### extended periods of time.

#### **3. Operation of closed centre solenoid valves** When closed center solenoid valves are used, or when used on an actuator with a load factor of 50% or more, jumping (lurching) cannot be prevented even if this product is used.

### 4. Using a regulator on the secondary side

When mounting a regulator on the secondary side (A port side), use a residual pressure relief regulator (AR2550 to 4050) or a check type regulator (AR2560 to 6060).

With a standard regulator (AR1000 to 6000), the secondary side pressure may not be released when this valve is exhausted.

### 5. Operation of secondary side solenoid valves

To operate solenoid valves mounted on this product's secondary side (A port side), first confirm that the secondary side's pressure (P) has increased to become equal to the primary side's pressure (P).

### 6. Operation

The residual pressure release function of this product is for emergency use only; therefore, avoid operation in the same manner as ordinary 3 port valves.

### 7. Using a lubricator

If mounting a lubricator, mount it on the primary side (P port side), of this product. If mounted on the secondary side (A port side), back flow of oil will occur and may spurt out of the valve's R port.

### 8. Operation for air blowing

This product cannot be operated for air blowing due to the mechanism that switches the main valve to be fully open after the secondary side's pressure increases to approximately 1/2 of the primary side. Selection

### **≜**Caution

### 1. Leakage voltage

Particularly when using a C-R element (surge voltage suppressor) for protection of the switching element, take note that lea kage voltage will increase due to leakage current flowing through the C-R element, etc.



AC coil is 20% or less of rated voltage. DC coil is 3% or less of rated voltage.

### 2. Low temperature operation

Although the valve can be operated at a temperature as low as 0°C, measures should be taken to avoid solidification or free  $\,$  - zing of drainage and moisture, etc.

### Mounting

### **A**Warning

# 1. If air leakage increases or equipment does not operate properly, stop operation.

After mounting or maintenance, etc., connect the compressed air and power supplies, and perform appropriate function and leakage tests to confirm that the unit is mounted properly.

### 2. Instruction manual

Mount and operate the product after reading the manual care fully and understanding its contents. Also keep the manual where it can be referred to as necessary.

### 3. Painting and coating

Warnings or specifications printed or pasted on the product should not be erased, removed or covered up.

Furthermore, contact SMC before paining resin parts, as this may cause adverse effects depending on the solvent.

### Adjustment

### Caution

1. To perform the initial speed adjustment of a secondary side actuator, supply air from this valve's primary side and turn ON the pilot valve. Then, rotate the needle counter clockwise from the fully closed condition.





### AV2000/3000/4000/5000 Specific Product Precautions 2

Be sure to read before handling. Refer to page 7 for safety instructions.

Piping

### **A**Caution

### 1. Preparation before piping

Before piping is connected, it should be thoroughly blown out with air (flushing) or washed to remove chips, cutting oil and ot - her debris from inside the pipe.

### 2. Wrapping of pipe tape

When connecting pipes and fittings, etc., be sure that chips from the pipe threads and sealing material do not get inside the valve.

Further, when pipe tape is used, leave 1.5 to 2 thread ridges exposed at the end of the threads.



# 3. Tighten threads with the proper tightening torque.

When screwing fittings into valves, tighten with the torques gi  $\,$  - ven below.

#### Tightening torque for piping

<u> </u>	
Connection threads	Proper tightening torque N·m
Rc 1/4	12 to 14
Rc 3/8	22 to 24
Rc 1/2	28 to 30
Rc 3/4	28 to 30
Rc 1	36 to 38

### 4. Connection of piping to products

When connecting piping to a product, refer to its instruction manual to avoid mistakes regarding the supply port, etc.

### 5. F.R.L. module combination

When connecting to a modular F.R.L. combination (AC2000 to 6000), select one of the spacers, which are included. (Refer to page 6 for details.) However, modular combination with AC4000-06 is not possible.

Furthermore, connect soft start-up valves to the secondary side of the F.R.L. combination.

### 6. Primary side piping conditions

The nominal size of the piping material's or equipment's bore should be equal to or larger than the soft start-up valve's port size. The composite effective area of the primary side's (P port side's) piping or equipment should be equal to or larger than the values below.

Model	Composite effective area mm <sup>2</sup>
AV2000	5
AV3000	22
AV4000	35
AV5000	50

When the piping is restricted or the supply pressure is insufficient, the main valve will not switch and air leakage may occur from the R port.

### Indicator Light/Surge Voltage Suppressor

### **A**Caution



### **Electrical Connection**

### **∆**Caution

The internal connection of the DIN terminal is as shown below, therefore, connect to the power supply side as shown.



Terminal	1	2
DIN terminal	+	-

### Lubrication

### **▲**Caution

- **1.** The valve has been lubricated for life at the factory, and does not require any further lubrication.
- 2. In the event that it is lubricated, use Class 1 turbine oil (wit hout additives), ISO VG32.

However, once lubrication is applied it must be continued, as the original lubricant may be eliminated leading to mal - function.

Contact SMC regarding Class 2 turbine oil (with additives), ISO VG32.





### AV2000/3000/4000/5000 Specific Product Precautions 3

Be sure to read before handling. Refer to page 7 for safety instructions.

Air Supply

### **Warning** 1. Use clean air.

Do not use compressed air which contains chemicals, synthetic oils containing organic solvents, salts or corrosive gases, etc., as this can cause damage or malfunction.

## 

### 1. Install air filters.

Install air filters close to valves at their upstream side. A filtra tion degree of  $5\mu m$  or less should be selected.

2. Install an after-cooler, air dryer or water separator, etc.

Air that includes excessive drainage may cause malfunction of valves and other pneumatic equipment. To prevent this, install an after-cooler, air dryer or water separator, etc.

### **Operating Environment**

### **M** Warning

- 1. Do not use valves in atmospheres of corrosive gases, chemicals, salt water, water or steam, or where there is direct contact with any of these.
- 2. Do not use in an explosive atmosphere.
- 3. Do not use in locations subject to vibration or impact.
- 4. A protective cover, etc., should be used to shield valves from direct sunlight.
- 5. Shield valves from radiated heat generated by nearby heat sources.
- 6. Employ suitable protective measures in locations where there is contact with water droplets, oil or welding spatter, etc.
- 7. In a dusty environment or when valve switching noise is intrusive, take measures for the prevention of dust entry and for noise reduction, such as mounting a silencer on the R port.

Maintenance

### A Warning

1. Perform maintenance procedures as shown in the instruction manual.

If handled improperly, malfunction or damage of machinery or equipment may occur.

2. Equipment removal and supply/exhaust of compressed air

When equipment is removed, first confirm that measures are in place to prevent dropping of work pieces and run-away of equipment, etc. Then cut the supply pressure and power, and exhaust all compressed air from the system using its residual pressure release function.

### 3. Low frequency operation

Valves should be switched at least once every 30 days to prevent malfunction. (Use caution regarding the air supply.)

### 4. Manual override operation

When the manual override is operated, connected equipment will be actuated. Confirm safety before operating.

## **∆**Caution

### 1. Drainage removal

Remove drainage from air filters regularly. (Refer to specifica - tions.)

#### How to Find the Flow Rate (at air temperature of 20°C)

Choke flow: when  $(P_2 + 0.1)/(P_1 + 0.1) \le 0.5$ 

Q = 120 x S x (P1 + 0.1) x 
$$\sqrt{\frac{293}{273 + t}}$$

Subsonic flow: when  $(P_2 + 0.1)/(P_1 + 0.1) > 0.5$ 

Q = 240 x S x 
$$\sqrt{(P_1 - P_2)(P_2 + 0.1)} x \sqrt{\frac{293}{273 + t}}$$

- Q : Air flow rate [ /min (ANR)]
- S : Effective area (mm<sup>2</sup>)
- P1: Upstream pressure [MPa]
- P2: Downstream pressure [MPa]
- t : Air temperature
- Note) Formulas above apply to compressed air only. Use conventional formulas for water and steam.



### Austria

SMC Pneumatik GmbH (Austria). Girakstrasse 8, A-2100 Korneuburg Phone: 02262-62280. Fax: 02262-62285

Belgium SMC Pneumatics N.V./S.A. Nijverheidsstraat 20, B-2160 Wommelgem

Phone: 03-355-1464, Fax: 03-355-1466



SMC Czech.s.r.o. Kodanska 46, CZ-100 10 Prague 10 Phone: 02-67154 790, Fax: 02-67154 793

SMC Pneumatik A/S Jens Juuls vej 32, DK-8260 Viby J Phone: 45-70252900, Fax: 45-70252901

Denmark

Estonia Teknoma Eesti AS Mustamäe tee 5, EE-0006 Tallinn, Estonia

Phone: 259530, Fax: 259531



## France

SMC Pneumatique, S.A 1, Boulevard de Strasbourg, Parc Gustave Eiffel Bussy Saint Georges F-77607 Marne La Vallee Cedex 3 Phone: 01-6476 1000, Fax: 01-6476 1010

#### Germany SMC Pneumatik GmbH Boschring 13-15, D-63329 Egelsbach Phone: 06103-4020. Fax: 06103-402139

Greece S. Parianopoulus S.A 9. Konstantinoupoleos Street. GR-11855 Athens Phone: 01-3426076, Fax: 01-3455578

Hungary SMC Hungary Kft Budafoki ut 107-113, 1117 Budapest Phone: 01-204 4366, Fax: 01-204 4371

Ireland SMC Pneumatics (Ireland) Ltd. 2002 Citywest Business Campus, Naas Road, Saggart, Co. Dublin Phone: 01-403 9000, Fax: 01-464 0500

Italy SMC Italia S.p.A Via Garibaldi 62, I-20061 Carugate, (Milano) Phone: 02-92711, Fax: 02-92150394

Latvia Ottensten Latvia SIA Ciekurkalna Prima Gara Linija 11. LV-1026 Riga, Latvia Phone: 371-23-68625, Fax: 371-75-56748

Lithuania UAB Ottensten Lietuva Savanoriu pr.180, LT-2600 Vilnius, Lithuania Phone/Fax: 370-2651602

#### Netherlands SMC Pneumatics BV Postbus 308, 1000 AH Amsterdam

Phone: 020-5318888, Fax: 020-5318880

### Norway

SMC Pneumatics (Norway) A/S Wollsveien 13 C, granfoss Noeringspark N-134 Lysaker, Norway Phone: 22 99 6036. Fax: 22 99 6103

### Poland

Semac Co., Ltd. PL-05-075 Wesola k/Warszaway, ul. Wspolna 1A Phone: 022-6131847, Fax: 022-613-3028



Portugal SMC España (Sucursal Portugal), S.A. Rua de Engº Ferreira Dias 452, 4100 Porto Phone: 02-610-89-22. Fax: 02-610-89-36

Romania SMC Romania srl Vasile Stroescu 19, Sector 2, Bucharest Phone: 01-210-1354 . Fax: 01-210-1680



SMC Pneumatik LLC Centrako Business Centre 103, Bolshoy Prospect V.O., 199106 St. Petersburg Phone: 812-1195131, Fax: 812-1195129



SMC Slovakia s.r.o. Pribinova ul. C. 25, 819 02 Bratislava Phone: 0-563 3548, Fax: 07-563 3551



#### Slovenia SMC Slovenia d.o.o.

Grajski trg 15, 8360 Zuzemberk Phone: 068-88 044 Fax: 068-88 041



#### Spain SMC España, S.A. Zuazobidea 14, Pol. Ind. Jundiz, E-01015 Vitoria Phone: 945-184 100, Fax: 945-184 124



SMC Pneumatics Sweden A.B. Ekhagsvägen 29-31, S-14105 Huddinge Phone: 08-603 07 00, Fax: 08-603 07 10

Switzerland SMC Pneumatik AG Dorfstrasse 7, CH-8484 Weisslingen Phone: 052-396-3131, Fax: 052-396-3191



Perpa Tic. Merkezi Kat: 11 No: 1625, TR-80270 Okmeydani Istanbul Phone: 0212-221-1512, Fax: 0212-220-2381



SMC Pneumatics (UK) Ltd Vincent Avenue, Crownhill, Milton Keynes, MK8 0AN Phone: 01908-563888 Fax: 01908-561185



**OTHER SUBSIDIARIES WORLDWIDE:** 

ARGENTINA, AUSTRALIA, BOLIVIA, BRASIL, CANADA, CHILE, CHINA, HONG KONG, INDIA, MALAYSIA, MEXICO, NEW ZEALAND, PHILIPPINES, SINGAPORE, SOUTH KOREA, TAIWAN, THAILANDIA, USA, VENEZUELA For more information, please contact your local SMC Regional Centre

### **SMC UK Contact Numbers**

Head Office: SMC Pneumatics (UK) Ltd, Vincent Avenue, Crownhill, Milton Keynes MK8 0AN

### THE NATIONAL SALES CENTRE FOR ENGLAND & WALES **Internal Sales**

(Price, Delivery Information & Order Placement) Freephone: 0800 138 2930 Fax: 01908 555064 e-mail:sales@smcpneumatics.co.uk

**Customer Services** 

(Post-Order Resolution) Freephone: 0800 138 2931 Fax: 01908 555065 e-mail: customerservice@smcpneumatics.co.uk

**TECHNICAL CENTRE** 

Freephone: 0800 138 2932 Fax: 01908 555066 e-mail: technical@smcpneumatics.co.uk

SMC FAST RESPONSE

(Literature & Catalogue Requests) 0800 0262006

### **SMC SALES CENTRE FOR SCOTLAND & N. IRELAND**

Tel: 01236 781133 Fax: 01236 780611

SMC Pneumatics (UK) Ltd, 1 Carradale Crescent, Broadwood Business Park, Cumbernauld, Glasgow G69 9LE

### **SMC UK Distributors**

Birmingham JAMES LISTER Tel: 0121 5803800 Fax: 0121 553595

Blackburn BLACKBURN PNEUMATIC SYSTEMS LTD Tel: 01254 682232 Fax: 01254 682224

Bristol APPLIED AUTOMATION Tel: 0117 9827769 Fax: 0117 9235522 Bury St Edmunds PNEUMATIC LINES Tel: 01284 706239 Fax: 01284 761218

Cardiff WALES FLUID POWER Tel: 02920 494551 Fax: 02920 481955

**Plymouth** APPLIED AUTOMATION Tel: 01752 343300 Fax: 01752 341161

SMC CORPORATION 1-16-4 Shimbashi, Minato-ku, Tokio 105 JAPAN; Phone:03-3502-2740 Fax:03-3508-2480