

Enclosure KLIPPON K4

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-2083

www.weidmueller.com



For many years, the name Klippon® has stood for competence and quality in enclosures. The enclosures are ideal for turnkey customised solutions for standard industrial applications and for explosive-risk applications.

Improved products that meet all application requirements: this was Weidmüller's aim during the update of the Klippon® K housing series. Weidmüller delivers many types of aluminium enclosures; they are designed to fit precisely with a wide range of customer requirements and applications.

Our comprehensive product line provides the following advantages:

- Available in two different surfaces: natural and powder-coated (RAL 7001)
- Available normally with silicone or chloroprene gasket seal
- A uniform Torx-slotted screw head is used for over 19 different housing sizes.
- Mounting holes not within the sealed area
- High degree of protection: IP66, IP67 and IP68
- Impact resistance of up to 10 Joules
- The housings are certified by ATEX, GOST, GOST Ex, cULus, Russian Maritime Register, German Lloyd, as well as the empty housing standard.
- Alloy is resistant to salt water
- Standardised distributor housings with threaded holes and a variety of terminal configurations

General ordering data

Order No.	0342300000
Type	KLIPPON K4
Version	Enclosures, 82 mm, 72 mm, 130 mm, Aluminium AISi12
GTIN (EAN)	4008190054991
Qty.	1 pc(s).

Enclosure KLIPPON K4

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-2083
 www.weidmueller.com

Technical data

Dimensions

Length	72 mm	Width	130 mm
Height	82 mm	Mounting dimension - width	98 mm
Weight	620 g		

Cable glands, left

M12 (3)	5	M20 (3)	2
---------	---	---------	---

Cable glands, right

M12 (2)	5	M16 (2)	3
M20 (2)	2	M25 (2)	2
Side of enclosure	left, right		

Cable glands, top/bottom

M12	2	M16	2
M20	1	M25	1
M32	1	Side of enclosure	left, right

General information

Cover attachment	M4 torx stainless steel screws with slot	Enclosure attachment	Holes 5 mm
Impact resistance	10.00 J	Integral fixing	Threaded holes M5
Material	Aluminium AlSi12	Operating temperature, max.	85 °C
Operating temperature, min.	-40 °C	Protection degree	IP 66, IP 67
Seal material	Neoprene	Surface finish	untreated

horizontal assembly

WDU 2,5 / ZDU 2,5 / IDU 2,5	*	WDU 4 / ZDU 4	*
-----------------------------	---	---------------	---

vertical assembly

WDU 10 / ZDU 10 (2)	1x2	WDU 2,5 / ZDU 2,5 / IDU 2,5 (2)	1x5
WDU 4 / ZDU 4 (2)	1x4	WDU 6 / ZDU 6 (2)	1x3

Classifications

ETIM 2.0	EC000058	ETIM 3.0	EC000058
ETIM 4.0	EC000058	UNSPSC	31-26-15-02
eClass 4.1	27-14-12-06	eClass 5.1	27-14-91-07
eClass 6.0	27-14-91-07	eClass 7.0	27149107

Test certificates

Certificate No. (GERMLLOYD)	44536-07	Certificate No. (MARITREG)	09.04040.250
Certificate no. (cULus)	E197061VOL2SEC1		

Data sheet...

**Enclosure
KLIPPON K4**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-2083
www.weidmueller.com

Technical data

Approvals

Approvals

