

V23079B1208B301

✓ ACTIVE

TE Internal #: 4-1393788-1

TE Internal Description: V23079B1208B301

Small Signal Relay, Axicom P2 Standard

[View on TE.com >](#)



[All Small Signal Relay, Axicom P2 Standard \(23\)](#)

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

TE Part # 1-1422002-0
[V23079B2208B301](#)

Customers Also Bought

TE Part #7-1393224-9
[RY531012](#)

TE Part #9-160583-5
[250 PIDG FASTON REC](#)

TE Part #8-215464-0
[10P.MICRO-MATCH MOB](#)

TE Part #2-1393224-7
[RYA51012](#)

TE Part #2-1393222-0
[V23061A1005A302=MINISTARKSTROM](#)

TE Part #1676153-1
[RN 0805 10K 0.1% 10PPM CUT LENGTH](#)

TE Part #1-1393219-3
[PE014048](#)

TE Part #3-1462039-1
[IM26GR=IM RELAY 50mW 12V](#)

TE Part #7-2176453-3
[CPF 0201 32K4 0.1% 25ppm 1K RL](#)

TE Part #3-1437142-7
[FSN-22A-17=NOMEX FS STD](#)

Documents

Product Drawings

[V23079B1208B301](#)

English

[V23079B1208B301](#)

English

CAD Files



3D PDF

3D

Customer View Model

ENG_CVM_CVM_4-1393788-1_E.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_4-1393788-1_E.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_4-1393788-1_E.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Transportation, Storage, Handling, Assembly and Testing of Axicom Through Hole Terminal (THT) Relays

English

Transportation, Storage, Handling, Assembly and Testing of AXICOM THT Relays

English

AXICOM Latching Relays

English

P2 Relay Datasheet

English

Product Specifications

Definitions General Purpose Relays

English

Agency Approvals

UL

English