

SAFETY DATA SHEET 132-491 COMPUTER CLEANING SOLVENT

SECTION 1: IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

1.1. Product identifier

Product name 132-491 COMPUTER CLEANING SOLVENT
Product No. 000162084091

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses As product description

1.3. Details of the supplier of the safety data sheet

Supplier R S Components Limited
Birchington Road
Corby
Northants
NN17 9RS
+44(0)1536 402888 (8am-8pm)
+44(0)1536 401588
technical.help@rs-components.com

1.4. Emergency telephone number +44(0)1536 402888 (8am-8pm)
+44(0)1536 401588

SECTION 2: HAZARDS IDENTIFICATION

2.1. Classification of the substance or mixture

Classification (EC 1272/2008)

| | |
|-------------------------------|--|
| Physical and Chemical Hazards | Flam. Aerosol 1 - H222 |
| Human health | Skin Irrit. 2 - H315; STOT SE 3 - H336 |
| Environment | Aquatic Chronic 2 - H411 |

Classification (1999/45/EEC) Xi; R38. F+; R12. N; R51/53. R67.

The Full Text for all R-Phrases and Hazard Statements are Displayed in Section 16.

2.2. Label elements

Label In Accordance With (EC) No. 1272/2008



Signal Word Danger

Hazard Statements

| | |
|------|--|
| H222 | Extremely flammable aerosol. |
| H315 | Causes skin irritation. |
| H336 | May cause drowsiness or dizziness. |
| H411 | Toxic to aquatic life with long lasting effects. |

Precautionary Statements

| | |
|--------------|--|
| P102 | Keep out of reach of children. |
| P210 | Keep away from heat/sparks/open flames/hot surfaces. - No smoking. |
| P271 | Use only outdoors or in a well-ventilated area. |
| P261 | Avoid breathing vapour/spray. |
| P280 | Wear protective gloves. |
| P305+351+338 | IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. |
| P337+313 | If eye irritation persists: Get medical advice/attention. |
| P501 | Dispose of contents/container in accordance with local regulations. |

132-491 COMPUTER CLEANING SOLVENT

Supplementary Precautionary Statements

| | |
|----------|--|
| P211 | Do not spray on an open flame or other ignition source. |
| P251 | Pressurized container: Do not pierce or burn, even after use. |
| P264 | Wash contaminated skin thoroughly after handling. |
| P302+352 | IF ON SKIN: Wash with plenty of soap and water. |
| P304+340 | IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing. |
| P312 | Call a POISON CENTER or doctor/physician if you feel unwell. |
| P332+313 | If skin irritation occurs: Get medical advice/attention. |
| P403+233 | Store in a well-ventilated place. Keep container tightly closed. |
| P410+412 | Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122°F. |

Supplemental label information

| | |
|-------|---|
| H229: | Pressurised container: May burst if heated. |
|-------|---|

2.3. Other hazards**SECTION 3: COMPOSITION/INFORMATION ON INGREDIENTS****3.2. Mixtures**

| | | | |
|--|-------------------|--|---------|
| BUTANE | | | 5-10% |
| CAS-No.: 106-97-8 | EC No.: 203-448-7 | | |
| Classification (EC 1272/2008) Flam. Gas 1 - H220 | | Classification (67/548/EEC) F+;R12 | |
| ISOBUTANE | | | 1-5% |
| CAS-No.: 75-28-5 | EC No.: 200-857-2 | | |
| Classification (EC 1272/2008) Flam. Gas 1 - H220 | | Classification (67/548/EEC) F+;R12 | |
| NAPHTHA (PETROLEUM) , HYDROTREATED LIGHT | | | 60-100% |
| CAS-No.: 64742-49-0 | EC No.: 921-024-6 | Registration Number: 01-2119475514-35-xxxx | |
| Classification (EC 1272/2008) Flam. Liq. 2 - H225 Skin Irrit. 2 - H315 STOT SE 3 - H336 Asp. Tox. 1 - H304 Aquatic Chronic 2 - H411 | | Classification (67/548/EEC) Xn;R65. Xi;R38. F;R11. N;R51/53. R67. | |
| PROPAN-2-OL | | | 10-30% |
| CAS-No.: 67-63-0 | EC No.: 200-661-7 | | |
| Classification (EC 1272/2008) Flam. Liq. 2 - H225 Eye Irrit. 2 - H319 STOT SE 3 - H336 | | Classification (67/548/EEC) F;R11 Xi;R36 R67 | |

132-491 COMPUTER CLEANING SOLVENT

| | |
|---|---------------------------------------|
| PROPANE | 10-30% |
| CAS-No.: 74-98-6 | EC No.: 200-827-9 |
| Classification (EC 1272/2008) Flam. Gas 1 - H220 | Classification (67/548/EEC) F+;R12 |

The Full Text for all R-Phrases and Hazard Statements are Displayed in Section 16.

SECTION 4: FIRST AID MEASURES

4.1. Description of first aid measures

General information

Move the exposed person to fresh air at once. Get medical attention if any discomfort continues.

Inhalation

Move the exposed person to fresh air at once. When breathing is difficult, properly trained personnel may assist affected person by administering oxygen. Keep the affected person warm and at rest. Get prompt medical attention.

Ingestion

DO NOT INDUCE VOMITING! Rinse mouth thoroughly with water and give large amounts of milk or water to people not unconscious. Get medical attention if any discomfort continues.

Skin contact

Wash the skin immediately with soap and water. Get medical attention if any discomfort continues.

Eye contact

Make sure to remove any contact lenses from the eyes before rinsing. Promptly wash eyes with plenty of water while lifting the eye lids. Continue to rinse for at least 15 minutes. Get medical attention if any discomfort continues.

4.2. Most important symptoms and effects, both acute and delayed

4.3. Indication of any immediate medical attention and special treatment needed

SECTION 5: FIREFIGHTING MEASURES

5.1. Extinguishing media

Extinguishing media

Use: Powder. Dry chemicals, sand, dolomite etc. Water spray, fog or mist.

5.2. Special hazards arising from the substance or mixture

Unusual Fire & Explosion Hazards

Aerosol cans may explode in a fire.

5.3. Advice for firefighters

Special Fire Fighting Procedures

Containers close to fire should be removed or cooled with water. Use water to keep fire exposed containers cool and disperse vapours.

SECTION 6: ACCIDENTAL RELEASE MEASURES

6.1. Personal precautions, protective equipment and emergency procedures

6.2. Environmental precautions

6.3. Methods and material for containment and cleaning up

Wear necessary protective equipment. Extinguish all ignition sources. Avoid sparks, flames, heat and smoking. Ventilate. Let evaporate. Keep out of confined spaces because of explosion risk. If leakage cannot be stopped, evacuate area.

6.4. Reference to other sections

SECTION 7: HANDLING AND STORAGE

7.1. Precautions for safe handling

132-491 COMPUTER CLEANING SOLVENT

Keep away from heat, sparks and open flame. Avoid spilling, skin and eye contact. Ventilate well, avoid breathing vapours. Use approved respirator if air contamination is above accepted level.

7.2. Conditions for safe storage, including any incompatibilities

Aerosol cans: Must not be exposed to direct sunlight or temperatures above 50°C.

7.3. Specific end use(s)

SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

8.1. Control parameters

| Name | STD | TWA - 8 Hrs | | STEL - 15 Min | | Notes |
|--|-----|--------------|------------------------|---------------|------------------------|-------|
| | | | | | | |
| BUTANE | WEL | 600 ppm | 1450 mg/m ³ | 750 ppm | 1810 mg/m ³ | |
| ISOBUTANE | WEL | 800 ppm | | 800 ppm | | |
| NAPHTHA (PETROLEUM) , HYDROTREATED LIGHT | | | 1200 mg/m ³ | 60 ppm | 216 mg/m ³ | |
| PROPAN-2-OL | WEL | 400 ppm | 999 mg/m ³ | 500 ppm | 1250 mg/m ³ | |
| PROPANE | | Asphyxiating | Asphyxiating. | Asphyxiating | Asphyxiating. | |

WEL = Workplace Exposure Limit.

Ingredient Comments

WEL = Workplace Exposure Limits

8.2. Exposure controls

Protective equipment



Engineering measures

Provide adequate general and local exhaust ventilation.

Respiratory equipment

No specific recommendation made, but respiratory protection must be used if the general level exceeds the recommended occupational exposure limit. Use chemical cartridge protection with appropriate cartridge.

Hand protection

Use protective gloves.

Eye protection

Use approved safety goggles or face shield.

Other Protection

Wear appropriate clothing to prevent any possibility of liquid contact and repeated or prolonged vapour contact.

Hygiene measures

DO NOT SMOKE IN WORK AREA! Wash hands at the end of each work shift and before eating, smoking and using the toilet. Promptly remove any clothing that becomes contaminated. When using do not eat, drink or smoke.

SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

9.1. Information on basic physical and chemical properties

| | |
|-------------------------------|-----------------|
| Appearance | Aerosol. |
| Colour | Colourless. |
| Odour | Characteristic. |
| Flammability Limit - Lower(%) | 0.8 |
| Flammability Limit - Upper(%) | 9.0 |

9.2. Other information

SECTION 10: STABILITY AND REACTIVITY

132-491 COMPUTER CLEANING SOLVENT

10.1. Reactivity**10.2. Chemical stability**

Stable under normal temperature conditions.

10.3. Possibility of hazardous reactions**10.4. Conditions to avoid**

Avoid heat, flames and other sources of ignition. Avoid contact with: Strong oxidising agents. Strong alkalis. Strong mineral acids.

10.5. Incompatible materials**10.6. Hazardous decomposition products**

Fire creates: Vapours/gases/fumes of: Carbon monoxide (CO). Carbon dioxide (CO₂).

SECTION 11: TOXICOLOGICAL INFORMATION**11.1. Information on toxicological effects****Inhalation**

May cause irritation to the respiratory system. Vapours may cause headache, fatigue, dizziness and nausea. Prolonged inhalation of high concentrations may damage respiratory system. Irritating to respiratory system.

Ingestion

May cause discomfort if swallowed. May cause stomach pain or vomiting. Gastrointestinal symptoms, including upset stomach.

Skin contact

Prolonged or repeated exposure may cause severe irritation. Acts as a defatting agent on skin. May cause cracking of skin, and eczema. May cause allergic contact eczema. May cause sensitisation by skin contact. Irritating to skin.

Eye contact

Irritating to eyes. May cause chemical eye burns.

Route of entry

Inhalation. Skin and/or eye contact.

SECTION 12: ECOLOGICAL INFORMATION**Ecotoxicity**

Dangerous for the environment if discharged into watercourses.

12.1. Toxicity**12.2. Persistence and degradability****12.3. Bioaccumulative potential****12.4. Mobility in soil****12.5. Results of PBT and vPvB assessment****12.6. Other adverse effects****SECTION 13: DISPOSAL CONSIDERATIONS****13.1. Waste treatment methods**

Empty containers must not be burned because of explosion hazard. Dispose of waste and residues in accordance with local authority requirements.

SECTION 14: TRANSPORT INFORMATION

132-491 COMPUTER CLEANING SOLVENT

14.1. UN number

| | |
|----------------------|------|
| UN No. (ADR/RID/ADN) | 1950 |
| UN No. (IMDG) | 1950 |
| UN No. (ICAO) | 1950 |

14.2. UN proper shipping name

| | |
|----------------------|----------|
| Proper Shipping Name | AEROSOLS |
|----------------------|----------|

14.3. Transport hazard class(es)

| | |
|---------------------|----------------|
| ADR/RID/ADN Class | 2 |
| ADR/RID/ADN Class | Class 2: Gases |
| ADR Label No. | 2.1 |
| IMDG Class | 2.1 |
| ICAO Class/Division | 2.1 |
| Transport Labels | |

**14.4. Packing group**

| | |
|---------------------------|----------------|
| ADR/RID/ADN Packing group | Not Applicable |
| IMDG Packing group | Not Applicable |
| ICAO Packing group | Not Applicable |

14.5. Environmental hazards

Environmentally Hazardous Substance/Marine Pollutant
No.

14.6. Special precautions for user

| | |
|-----|----------|
| EMS | F-D, S-U |
|-----|----------|

14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code

SECTION 15: REGULATORY INFORMATION

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Uk Regulatory References

The Chemicals (Hazard Information and Packaging for Supply) Regulations 2002.

The Control of Substances Hazardous to Health Regulations 2002.

Statutory Instruments

The Control of Substances Hazardous to Health Regulations 2002.

The Chemicals (Hazard Information and Packaging for Supply) Regulations 2002.

Approved Code Of Practice

Classification and Labelling of Substances and Preparations Dangerous for Supply.

Guidance Notes

Workplace Exposure Limits EH40.

Introduction to Local Exhaust Ventilation HS(G)37.

CHIP for everyone HSG(108).

132-491 COMPUTER CLEANING SOLVENT

15.2. Chemical Safety Assessment**SECTION 16: OTHER INFORMATION**

| | |
|---------------------------|---|
| Revision Date | 06/10/2015 |
| Revision | 7 |
| Supersedes date | 18/02/2015 |
| Risk Phrases In Full | |
| R12 | Extremely flammable. |
| R65 | Harmful: may cause lung damage if swallowed. |
| R11 | Highly flammable |
| R36 | Irritating to eyes. |
| R38 | Irritating to skin. |
| R51/53 | Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment. |
| R67 | Vapours may cause drowsiness and dizziness. |
| Hazard Statements In Full | |
| H319 | Causes serious eye irritation. |
| H315 | Causes skin irritation. |
| H222 | Extremely flammable aerosol. |
| H220 | Extremely flammable gas. |
| H225 | Highly flammable liquid and vapour. |
| H304 | May be fatal if swallowed and enters airways. |
| H336 | May cause drowsiness or dizziness. |
| H411 | Toxic to aquatic life with long lasting effects. |

Disclaimer

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.