

PRODUCT-DETAILS

AF96-30-00-11

AF96-30-00-11 24-60V50/60HZ 20-60VDC Contactor



General Information

Extended Product Type	AF96-30-00-11
Product ID	1SBL407001R1100
EAN	3471523133211
Catalog Description	AF96-30-00-11 24-60V50/60HZ 20-60VDC Contactor
Long Description	<p>The AF96-30-00-11 is a 3 pole - 1000 V IEC or 600 UL contactor with screw terminals, controlling motors up to 45 kW / 400 V AC (AC-3) or 60 hp / 480 V UL and switching power circuits up to 130 A (AC-1) or 115 A UL general use. Thanks to the AF technology, the contactor has a wide control voltage range (24-60 V 50/60 Hz and 20-60 V DC), managing large control voltage variations, reducing panel energy consumptions and ensuring distinct operations in unstable networks. Furthermore, surge protection is built-in, offering a compact solution. AF contactors have a block type design, can be easily extended with add-on auxiliary contact blocks and an additional wide range of accessories.</p>

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85364900

Popular Downloads

Instructions and Manuals	1SBC101036M6801
Dimension Diagram	DNV_TAE00001AF-4

Dimensions

Product Net Width	70 mm
Product Net Depth / Length	116 mm
Product Net Height	125.5 mm
Product Net Weight	1.22 kg

Technical

Number of Main Contacts NO	3
Number of Main Contacts NC	0
Number of Auxiliary Contacts NO	0
Number of Auxiliary Contacts NC	0
Rated Operational Voltage	Main Circuit 1000 V
Rated Frequency (f)	Main Circuit 50 / 60 Hz
Conventional Free-air Thermal Current (I_{th})	acc. to IEC 60947-4-1, Open Contactors q = 40 °C 130 A
Rated Operational Current AC-1 (I_e)	(690 V) 40 °C 130 A (690 V) 60 °C 105 A (690 V) 70 °C 90 A
Rated Operational Current AC-3 (I_e)	(415 V) 60 °C 96 A (440 V) 60 °C 96 A (500 V) 60 °C 80 A (690 V) 60 °C 57 A (1000 V) 60 °C 30 A (380 / 400 V) 60 °C 105 A (220 / 230 / 240 V) 60 °C 105 A
Rated Operational Current AC-3e (I_e)	(415 V) 60 °C 96 A (440 V) 60 °C 96 A (500 V) 60 °C 80 A (690 V) 60 °C 57 A (380 / 400 V) 60 °C 105 A (220 / 230 / 240 V) 60 °C 105 A
Rated Operational Power AC-3 (P_e)	(415 V) 55 kW (440 V) 55 kW (500 V) 55 kW (690 V) 55 kW (1000 V) 40 kW (380 / 400 V) 45 kW (380 / 400 V) 55 kW (220 / 230 / 240 V) 25 kW (220 / 230 / 240 V) 30 kW
Rated Operational Power AC-3e (P_e)	(415 V) 55 kW (440 V) 55 kW (500 V) 55 kW (690 V) 55 kW (380 / 400 V) 45 kW (380 / 400 V) 55 kW (220 / 230 / 240 V) 25 kW (220 / 230 / 240 V) 30 kW
Rated Short-time Withstand Current Low Voltage (I_{cw})	at 40 °C Ambient Temp, in Free Air, from a Cold State 10 s 840 A at 40 °C Ambient Temp, in Free Air, from a Cold State 15 min 140 A at 40 °C Ambient Temp, in Free Air, from a Cold State 1 min 300 A at 40 °C Ambient Temp, in Free Air, from a Cold State 1 s 1200 A at 40 °C Ambient Temp, in Free Air, from a Cold State 30 s 450 A for 1 s -empty- A
Maximum Breaking Capacity	cos phi=0.45 (cos phi=0.35 for $I_e > 100$ A) at 440 V 1150 A cos phi=0.45 (cos phi=0.35 for $I_e > 100$ A) at 690 V 750 A
Maximum Electrical Switching Frequency	(AC-1) 600 cycles per hour (AC-2 / AC-4) 150 cycles per hour (AC-3) 1200 cycles per hour
Rated Insulation Voltage	acc. to IEC 60947-4-1 and VDE 0110 (Gr. C) 1000 V

(U _i)	acc. to UL/CSA 600 V
Rated Impulse Withstand Voltage (U _{imp})	8 kV
Maximum Mechanical Switching Frequency	3600 cycles per hour
Rated Control Circuit Voltage (U _c)	50 Hz 24 ... 60 V 60 Hz 24 ... 60 V DC Operation 20 ... 60 V
Operate Time	Between Coil De-energization and NC Contact Closing 19 ... 105 ms Between Coil De-energization and NO Contact Opening 17 ... 100 ms Between Coil Energization and NC Contact Opening 38 ... 95 ms Between Coil Energization and NO Contact Closing 42 ... 100 ms
Mounting on DIN Rail	TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Mounting by Screws (not supplied)	2 x M4 or 2 x M6 screws placed diagonally
Connecting Capacity Main Circuit	Flexible with Ferrule 1/2x 6 ... 50 mm ² Flexible with Insulated Ferrule 1/2x 6 ... 50 mm ² Rigid 1x 6 ... 70 mm ² Rigid 2x 6 ... 50 mm ²
Connecting Capacity Control Circuit	Flexible with Ferrule 1/2x 0.75 ... 2.5 mm ² Flexible with Insulated Ferrule 1x 0.75 ... 2.5 mm ² Flexible with Insulated Ferrule 2x 0.75 ... 1.5 mm ² Rigid 1/2x 1 ... 2.5 mm ²
Wire Stripping Length	Main Circuit 17 mm
Degree of Protection	acc. to IEC 60529, IEC 60947-1, EN 60529 Coil Terminals IP20 acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP10
Terminal Type	Screw Terminals

Technical UL/CSA

General Use Rating UL/CSA	(600 V AC) 115 A
Horsepower Rating UL/CSA	(120 V AC) Single Phase 7-1/2 hp (200 ... 208 V AC) Three Phase 30 hp (220 ... 240 V AC) Three Phase 40 hp (240 V AC) Single Phase 20 hp (440 ... 480 V AC) Three Phase 75 hp (550 ... 600 V AC) Three Phase 75 hp
Tightening Torque UL/CSA	Control Circuit 11 in-lb Main Circuit 53 in-lb

Environmental

Ambient Air Temperature	Close to Contactor Fitted with Thermal O/L Relay -40 ... 70 °C Close to Contactor without Thermal O/L Relay -40 ... 70 °C Close to Contactor for Storage -60 ... +80 °C
Climatic Withstand	Category B according to IEC 60947-1 Annex Q
Maximum Operating Altitude Permissible	Without Derating 3000 m
Resistance to Vibrations acc. to IEC 60068-2-6	5 ... 300 Hz 3 g closed position / 3 g open position
Resistance to Shock acc. to IEC 60068-2-27	Closed, Shock Direction: A 25 g Closed, Shock Direction: B1 25 g Closed, Shock Direction: B2 15 g Closed, Shock Direction: C1 25 g Closed, Shock Direction: C2 25 g Open, Shock Direction: B1 5 g
RoHS Status	Following EU Directive 2011/65/EU

Certificates and Declarations (Document Number)

ABS Certificate	ABS_20-2060694-PDA
BV Certificate	BV_2634H36994A

CB Certificate	CB_SE-96557M2
CCC Certificate	CCC_2013010304646569
CQC Certificate	CQC2013010304646569
Declaration of Conformity - CCC	2020980304001255
Declaration of Conformity - CE	1SBD250000U1000
Declaration of Conformity - UKCA	1SBD250031U1000
EAC Certificate	EAC_RU_FRME77B03447
Environmental Information	1SBD250168E1000 1SBC100222M0201
GL Certificate	DNV-GL_TAE00001AF-3
Instructions and Manuals	1SBC101036M6801
KC Certificate	KC_HW02016-15011C
LR Certificate	LRS_1300087E1
RINA Certificate	RINA_ELE084013XG
RMRS Certificate	RMRS_1802705280
RoHS Information	1SBD250000U1000
UL Certificate	UL_20130926-E312527_14_1
UL Listing Card	UL_E312527

Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	150 mm
Package Level 1 Depth / Length	150 mm
Package Level 1 Height	103 mm
Package Level 1 Gross Weight	1.34 kg
Package Level 1 EAN	3471523133211
Package Level 2 Units	box 8 piece
Package Level 2 Width	250 mm
Package Level 2 Depth / Length	300 mm
Package Level 2 Height	300 mm
Package Level 2 Gross Weight	10.72 kg
Package Level 3 Units	192 piece

Classifications

Object Classification Code	Q
ETIM 4	EC000066 - Magnet contactor, AC-switching
ETIM 5	EC000066 - Magnet contactor, AC-switching
ETIM 6	EC000066 - Power contactor, AC switching
ETIM 7	EC000066 - Power contactor, AC switching
ETIM 8	EC000066 - Power contactor, AC switching
eClass	V11.0 : 27371003
UNSPSC	39121529
E-Number (Finland)	3707135
E-Number (Sweden)	3210055

Categories

Low Voltage Products and Systems → Control Products → Contactors → Block Contactors

