



Connectors > PCB Connectors > Backplane Connectors > Rack & Panel Connectors



Connector Product Type: **Connector Assembly**

Connector & Housing Type: **Receptacle**

Rack & Panel Connector Shell Size: **2**

Sealable: **No**

Panel Mount Feature Type: **Clinch Nut**

Features

Product Type Features

Connector Product Type	Connector Assembly
Connector & Housing Type	Receptacle
Rack & Panel Connector Shell Size	2
Sealable	No

Configuration Features

Release Style	Front
---------------	-------

Body Features

Connector & Keying Code	9
Shell Finish	ENI per MIL-C-26074 Class 3 Grade 8

Contact Features

Contact Arrangement Code (Module C)	13C2
Contact Arrangement Code (Module B)	150
Contact Arrangement Code (Module A)	150

Mechanical Attachment

Clinch Nut Size	6-32
Clinch Nut Quantity	6
Panel Mount Feature Type	Clinch Nut
Connector Mounting Type	Board Mount



Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Also in the Series | AMP ARINC 600 Series



Connector Contacts(57)



Rack & Panel Connectors(54)



RF Contacts(2)

Customers Also Bought



TE Part #208972-1
CONN, NO 2 PLUG-NIC 600

TE Part #NB09542001
ATUM-16/4-0-STK

TE Part #AAB1705-00
91H1-13-06-1-TN-HE100

TE Part #C35095-000
NT-MIL-7/8-0-SP

TE Part #2081377-3
CA,FAKRA F TO M,RG174LL,NO SLIP, 1000MM

TE Part #AAB1715-00
91H1-13-06-4-J-HE100

TE Part #AAB1914-00
91H1-15-11-1-ZN-HE200

TE Part #246221-000
KTKK-2617

TE Part #YDTS26T15-19SAV001
PLUG ASSY

TE Part #601966-8
POSITIONER, K267-1

Documents

Product Drawings
ARINC600,RCPT ASSY,SZ 2,SPCL,MONOBLK
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_1218049-4_V.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_1218049-4_V.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_1218049-4_V.3d_stp.zip
English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages



1308940_Sec4_arinc600

English

ARINC 600 Next Generation Receptacle Connector

English