

M18 FSAGSV0125X-502X

M18 FUEL™ 125 MM SAFETY GRINDER WITH VARIABLE SPEED AND ONE-KEY™

- Dual trigger activation requires the user to have always both hands on the tool and automatically shuts down the tool whenever one hand is taken off
- RAPIDSTOP™ for fastest disc brake in less than 1 second and best user protection
- AUTOSTOP™ shuts down the tool to protect the user in bind-up situations or any unnatural movement
- Delivering corded performance similar to a 1200 W grinder
- Maximum control for every application with 4-mode push button, ideal for working with stainless steel and aluminium & for rust and paint removal
- Lowest vibration in its class – 3.27 m/s² for surface grinding
- ONE-KEY™ tool tracking & security offers a free of charge cloud-based tracking network and inventory management platform for your tools. ONE-KEY™ also features a remote locking functionality
- Multi-position & non-removable side handle, allowing the user to tilt and rotate the handle into 15 different positions for ideal handling & easy storage
- Non-removal guard, guard adjustment and cutting guard clip installation is tool-free
- Integrated FIXTEC™ system for tool-free wheel change
- Non-lockable safety paddle switch on the main handle and non-lockable trigger on the side handle
- Removable dust screen to prevent debris entrance, prolonging motor life



REDLITHIUM™



No load speed (rpm)	3500 - 8500
Weight with battery pack (EPTA) (kg)	3.0 (M18 B5)
Brake	Yes
Switch type	Deadman switch
FIXTEC™	Yes
Variable speed	Yes
Kit included	2 x M18 B5 Battery packs, M12-18 FC Charger, HD Box
Article Number	4933493553