

SAC-5P-M12MS/ 1,5-924/M12FS - Bus system cable



1405988

<https://www.phoenixcontact.com/in/products/1405988>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Bus system cable, CANopen®, DeviceNet™, 5-position, PVC, gray, shielded, Plug straight M12, coding: A, on Socket straight M12, coding: A, cable length: 1.5 m, Connector unshielded

Commercial data

Item number	1405988
Packing unit	1 pc
Minimum order quantity	50 pc
Note	Made to order (non-returnable)
Sales key	BF1
Product key	AF1IHE
GTIN	4046356800402
Weight per piece (including packing)	117.4 g
Weight per piece (excluding packing)	64.6 g
Customs tariff number	85444290
Country of origin	US

SAC-5P-M12MS/ 1,5-924/M12FS - Bus system cable



1405988

<https://www.phoenixcontact.com/in/products/1405988>

Technical data

Product properties

Product type	Data cable preassembled
Application	Standard, U.S. cables
Sensor type	CANopen®
Number of positions	5
No. of cable outlets	1
Shielded	yes
Coding	A

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Approvals

National Marine Electronics Association

Certificate	approved
-------------	----------

Interfaces

Bus system	CANopen®/DeviceNet™
Signal type/category	CANopen®
	DeviceNet™

Signaling

Status display	no
Status display present	No

Electrical properties

Insulation resistance	≥ 100 MΩ
Nominal voltage U_N	48 V AC
	60 V DC
Nominal current I_N	4 A
Transmission medium	Copper

Material specifications

Flammability rating according to UL 94	HB
Seal material	NBR
Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material for screw connection	Zinc die-cast, nickel-plated

SAC-5P-M12MS/ 1,5-924/M12FS - Bus system cable



1405988

<https://www.phoenixcontact.com/in/products/1405988>

Connector

Connection 1

Type	Plug straight M12
Number of positions	5
Coding type	A (Standard)

Connection 2

Type	Socket straight M12
Number of positions	5
Coding type	A (Standard)

Cable/line

Cable length	1.5 m
--------------	-------

CANopen®/DeviceNet™, PVC, gray [924]

Dimensional drawing	
Cable weight	64.51 kg/km
UL AWM Style	2464 (80°C/300 V)
Number of positions	4
Shielded	yes
Cable type	CANopen®/DeviceNet™, PVC, gray [924]
Conductor structure	2xAWG22 (Signal) + 2xAWG22 (Power)
Signal runtime	4.46 ns/m
Conductor structure signal line	19x 0.15 mm
AWG signal line	22
Conductor structure, voltage supply	19x 0.15 mm
AWG power supply	22
Conductor cross section	2x 0.34 mm² (Signal line) 2x 0.34 mm² (Power supply)
Wire diameter incl. insulation	1.27 mm ±0.05 mm (Signal line) 2.24 mm ±0.13 mm (Power supply)
External cable diameter	6.90 mm ±0.13 mm
Outer sheath, material	PVC
External sheath, color	gray
Conductor material	Bare Cu litz wires
Material wire insulation	Foamed PE (Signal line)

SAC-5P-M12MS/ 1,5-924/M12FS - Bus system cable



1405988

<https://www.phoenixcontact.com/in/products/1405988>

	PVC (Power supply)
Single wire, color	red-black, blue-white
Twisted pairs	2 cores to the pair
Type of pair shielding	Plastic-coated aluminum foil, aluminum side inside
Overall twist	2 pairs around a drain wire in the center to the core
Insulation resistance	$\geq 59.38 \Omega \cdot m$ (Signal line)
	$\geq 57.41 G\Omega \cdot km$ (Power supply)
Wave impedance	$120 \Omega \pm 12 \Omega$
Working capacitance	nom. 78.74 pF (per meter)
Minimum bending radius, flexible installation	15 x D
Smallest bending radius, movable installation	104 mm
Shield attenuation	0.95 dB (f = 125 kHz)
	1.64 dB (f = 500 kHz)
	2.30 dB (f = 1 MHz)
Flame resistance	FT4
Resistance to oil	yes
Other resistance	UV resistant
Special properties	UL standards PLTC and ITC
Ambient temperature (operation)	-30 °C ... 75 °C (cable, fixed installation)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
	IP67
	IP68
Ambient temperature (operation)	-25 °C ... 90 °C (Plug / socket)

Approvals

National Marine Electronics Association

Certificate	approved
-------------	----------

SAC-5P-M12MS/ 1,5-924/M12FS - Bus system cable



1405988

<https://www.phoenixcontact.com/in/products/1405988>


Drawings

Dimensional drawing




M12 x 1 plug, straight

Circuit diagram




Contact assignment of the M12 plug and the M12 socket

Schematic diagram



Pin assignment M12 socket, 5-pos., A-coded, socket side view

Schematic diagram



Pin assignment M12 male connector, 5-pos., A-coded, male side


SAC-5P-M12MS/ 1,5-924/M12FS - Bus system cable



1405988

<https://www.phoenixcontact.com/in/products/1405988>

Dimensional drawing



M12 x 1 socket, straight

SAC-5P-M12MS/ 1,5-924/M12FS - Bus system cable



1405988

<https://www.phoenixcontact.com/in/products/1405988>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/1405988>



UL Listed

Approval ID: FILE E 221474

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	125 V	4 A	-	-



cUL Listed

Approval ID: FILE E 221474

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	125 V	4 A	-	-

cULus Listed

SAC-5P-M12MS/ 1,5-924/M12FS - Bus system cable



1405988

<https://www.phoenixcontact.com/in/products/1405988>

Classifications

ECLASS

ECLASS-11.0	27060307
ECLASS-12.0	27060307
ECLASS-13.0	27060307

ETIM

ETIM 9.0	EC001855
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SAC-5P-M12MS/ 1,5-924/M12FS - Bus system cable



1405988

<https://www.phoenixcontact.com/in/products/1405988>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	Diazene-1,2-dicarboxamide (C,C'-azodi(formamide)) (ADCA)(CAS: 123-77-3)
SCIP	40a39ce8-8b0d-43fe-9c60-079d051c3e7d

EF3.0 Climate Change

CO2e kg	1.467 kg CO2e
---------	---------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.
A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420
info@phoenixcontact.co.in