



M4000 Advanced

M4000 passes the baton to deTem and deTec

SICK
Sensor Intelligence.



Technical data overview

Safety level	PL e, SIL 3, Type 4
Scanning range	70 m
Number of beams	2 ... 8 (depends on variant)
Beam separation	220 mm ... 600 mm (depends on variant)
Integrated laser alignment aid	- / ✓ (depends on variant)
End cap with integrated LED	- / ✓ (depends on variant)
Enclosure rating	IP65
Ambient operating temperature	-30 °C ... +55 °C

Product description

The M4000 safety light-beam sensor and matching device and mirror columns have been used successfully in numerous industries for many decades. The knowledge gained from this flows into the further development of successor solutions.

Now is the time to switch: deTem and deTec offer more functionality, flexibility and investment certainty.

Switch now from the M4000 to deTem and deTec – the future of safety light-beam sensors and safety light curtains.

Discover the successor now:

deTem safety light-beam sensor

deTec safety light curtain

Find out more in the flyer

Contact us

At a glance

- Type 4 (IEC 61496), SIL3 (IEC 61508), PL e (EN ISO 13849)
- Robust housing with three mounting grooves
- Wide scanning range, up to 70 m
- External device monitoring (EDM), restart interlock, application diagnostic output, SDL interface
- Muting in combination with the UE403 muting switching amplifier
- 7-segment display
- Configuration and diagnostics via PC
- Optional integration features: laser alignment aid, LED

Your benefits

- The wide scanning range allows the device to be customized according to the application
- Robust design with a high level of resistance to environmental changes ensures high machine availability, even under special ambient conditions
- Mounting grooves on three housing sides ensure more mounting flexibility and simplify machine integration
- Customer-friendly interfaces and status display simplify commissioning and maintenance
- For 2- and 4-sensor muting, the on-site connection of the muting signals significantly minimizes wiring costs and simplifies commissioning and maintenance
- Reduced downtime due to 360° visible LED, diagnostics displays and configuration memory in the UE403 muting switching amplifier

Fields of application

- Access protection with and without muting
- Machine tools industry
- Automotive industry, robotics industry and automatic machining centers
- Storage and conveyor, packaging machinery, palletizer systems and stackers
- Wood machining, large weaving machines and stone setting systems

Ordering information

Other models and accessories → www.sick.com/M4000_Advanced

Number of beams	Beam separation	Sender		Receiver	
		Type	Part no.	Type	Part no.
2	500 mm	M40S-025003AA0	1200060	M40E-025003RB0	1200065
				M40E-025023RB0	1200062
		M40S-025003EA0	1202667	M40E-025003WB0	1202707
		M40S-025013AA0	1200057	M40E-025013RB0	1200058
			M40E-025033RB0	1200110	
	600 mm	M40S-026003AA0	1200070	M40E-026003RB0	1200096
				M40E-026023RB0	1200079
		M40S-026013AA0	1200078	M40E-026013RB0	1200105
			M40E-026033RB0	1200111	
3	220 mm	M40S-032203AA0	1200063	M40E-032203RB0	1200097
				M40E-032223RB0	1200066
	400 mm	M40S-034003AA0	1200061	M40E-034003RB0	1200064
				M40E-034023RB0	1200067
		M40S-034003EA0	1202668	M40E-034003WB0	1202708
		M40S-034013AA0	1200069	M40E-034013RB0	1200106
			M40E-034033RB0	1200068	
	450 mm	M40S-034503AA0	1200071	M40E-034503RB0	1200098
				M40E-034523RB0	1200081
		M40S-034513AA0	1200082	M40E-034513RB0	1200107
			M40E-034533RB0	1200112	
4	220 mm	M40S-042203AA0	1200072	M40E-042203RB0	1200099
				M40E-042223RB0	1210279
	300 mm	M40S-043003AA0	1200073	M40E-043003RB0	1200100
				M40E-043023RB0	1200109
M40S-043013AA0		1200080	M40E-043013RB0	1200108	
		M40E-043033RB0	1200113		
5	220 mm	M40S-052203AA0	1200074	M40E-052203RB0	1200101
				M40E-052223RB0	1208161
6	220 mm	M40S-062203AA0	1200075	M40E-062203RB0	1200102
				M40E-062223RB0	1203850
7	220 mm	M40S-072203AA0	1200076	M40E-072203RB0	1200103
				M40E-072223RB0	1201247
8	220 mm	M40S-082203AA0	1200077	M40E-082203RB0	1200104
				M40E-082223RB0	1206683

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com