

## OFYS-RT-U2000



### Strong points

- Fast and easy installation
- Easy to use
- Reliable power protection

### General characteristics

- No configuration needed on first startup.
- 19" Rack & Rack/Tower convertible UPS.
- True online double conversion technology (VFI).
- Clear and uncluttered LCD interface.
- Up to 7 UPS output sockets.

### Compliance with standards

- IEC 62040-1
- IEC 62040-2
- IEC 62040-3

### Access to resources (ex: manuals)

OFYS RT is a single-phase UPS range designed to protect professional IT infrastructures, ensuring cost competitive solutions.

### Technical Characteristics

Length of the product unit [mm]	89
Width of the product unit [mm]	438
Depth of the product unit [mm]	410
Weight [kg]	18.2
Depth [mm]	410
Height [mm]	89
In/out	1/1
Output voltage	230
Rated frequency	50/50
Width [mm]	438
Sn [kVA]	2
Pn [kW]	1.8
Conf	C1
Input voltage	230
Rate (min)	2
Rate (max)	2
Life Time	03-05
Typical Backup Time [min]	8
Configuration	UPS Single Unit(s) with Bypass

### Classification

UNSPSC	39121011
ETIM Class	EC000382
IGCC	4149

### Commerce

Description	OFYS RT 2000VA VFI UPS 1/1 PF=0,9 WITH BATTERY INTEGRATED
Effective date	2022-02-22
Offer Life Cycle Code	40
Country of origin	CN

### ETIM - Electrical characteristics

Input voltage [V]	180..280
Primary frequency [Hz]	40..70
Number of phases primary	1
Output voltage [V]	200..240
Secondary frequency [Hz]	50..60
Output effective power [W]	1800
Output apparent power [VA]	2000
Number of phases secondary	1
SNMP	Yes
Voltage type	AC
Max. voltage distortion output (linear load) [%]	3
Output power factor	0.9

### ETIM - Mechanical characteristics

Height [mm]	89
-------------	----

Width [mm]	440
Depth [mm]	410
Weight [kg]	18.2
Construction type	482.6 mm (19 inch) device
Modular	No
Input connection	C14
Number of output connections C13	6

#### **ETIM - Technical features**

USB interface	Yes
With communication interface RS-232	Yes
Suitable for network-management	Yes
USV- technology	Online
Overall efficiency [%]	89
Efficiency in eco-mode [%]	94
Potential free switch contact	Yes
Auto shut down function	Yes

#### **Logistics**

GTIN/EAN	8027122770392
Customs number	8504409590

#### **Norms**

Conformity to standards	IEC
-------------------------	-----