




MTA 156

TE Internal #: 4-641210-0
PCB Mount Header, Right Angle, Wire-to-Board, 10 Position, 3.96 mm [.156 in] Centerline, Partially Shrouded, Gold (Au), Through Hole - Solder, MTA 156

[View on TE.com >](#)

Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Type: **PCB Mount Header**
PCB Mount Orientation: **Right Angle**
Connector System: **Wire-to-Board**
Number of Positions: **10**
Number of Rows: **1**

Features

Product Type Features

Mixed & Hybrid Header	No
Connector Shape	Rectangular
PCB Connector Type	PCB Mount Header
Connector System	Wire-to-Board
Header Type	Partially Shrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
Connector Product Type	Connector Assembly

Configuration Features

Connector Contact Load Condition	Fully Loaded
Number of Columns	10
Number of Loaded Positions	10
Number of Power Positions	10
PCB Mount Orientation	Right Angle



Number of Positions	10
Number of Rows	1

Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

Body Features

Primary Product Color	Natural
-----------------------	---------

Contact Features

Contact Underplating Material	Nickel
Contact Underplating Material Thickness	1.27 µm[50 µin]
Contact Size	1.14mm
Contact Mating Area Plating Material Thickness	.76 µm[30 µin]
Mating Square Post Dimension	1.14 mm[.045 in]
Contact Base Material	Copper Alloy
PCB Contact Termination Area Plating Material	Tin
PCB Contact Termination Area Plating Material Finish	Matte
PCB Contact Termination Area Plating Material Thickness	3.81 – 8.89 µm[150 – 350 µin]
Contact Shape & Form	Square
Contact Layout	Inline
Contact Mating Area Length	10.16 mm[.4 in]
Contact Mating Area Plating Material	Gold (Au)
Contact Type	Tab
Contact Current Rating (Max)	14.24 A

Termination Features

Square Termination Post & Tail Dimension	1.14 mm[.045 in]
Termination Post & Tail Length	3.18 mm[.125 in]
Termination Method to PCB	Through Hole - Solder

Mechanical Attachment

Panel Mount Feature	Without
Mating Retention Type	Friction Lock
Mating Retention	With
PCB Mount Retention	Without
PCB Mount Alignment	Without



Connector Mounting Type	Board Mount
Mating Alignment	Without

Housing Features

Mating Entry Location	Side
Housing Material	Thermoplastic Polyester - Glass-Filled
Right Angle Bending Side	Front
Centerline (Pitch)	3.96 mm[.156 in]

Dimensions

Connector Width	10.79 mm[.425 in]
Connector Height	7.62 mm[.3 in]
Connector Length	39.62 mm[1.56 in]
PCB Thickness (Recommended)	1.57 mm[.062 in]

Usage Conditions

Operating Temperature (Max)	105 °C[221 °F]
Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

Compatible With Agency/Standards Products	CSA, UL
UL Rating	Recognized
Compatible With Approved Standards Products	UL E28476
Glow Wire Rating	Standard Part - Not Glow Wire
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	500
Packaging Method	Package

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JAN 2025
(247)
Candidate List Declared Against: JAN 2025
(247)
Does not contain REACH SVHC

Halogen Content

Not Low Halogen - contains Br or Cl > 900 ppm.



Solder Process Capability

Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 4-641229-0 10P MTA156 CONN ASSY 22AWG LF	 TE Part # 1-640551-0 10P MTA156 COVER	 TE Part # 4-644662-0 10P MTA156 CONN ASSY 22AWG LF	 TE Part # 4-644460-0 10P MTA156 CONN ASSY 18AWG ORA
 TE Part # 4-641218-0 10P MTA156 CONN ASSY 20AWG LF	 TE Part # 1-643071-0 10P MTA156 FD-THRU COVER	 TE Part # 4-641217-0 10P MTA156 CONN ASSY 18AWG ORA	 TE Part # 4-644718-0 10P MTA156 CONN ASSY 18AWG OR



TE Part # 1-643067-0
10P MTA156 MOLDED COVER

TE Part # 1-640251-0
10P SL156 HSG W/O LCK RAMP

TE Part # 1-640643-0
10P MTA156 COVER F/T

TE Part # 4-644663-0
10P MTA156 CONN ASSY 20AWG LF

TE Part # 4-641227-0
10P MTA156 CONN ASSY 18AWG LF

TE Part # CAT-103156-WBHSM
Receptacle Housing: Wire-to-Board, with Mating Alignment, SL156

Also in the Series | MTA 156

Connector Caps & Covers(89)

Connector Contacts(4)

Connector Hardware(2)

Insertion & Extraction Tools(1)

PCB Headers & Receptacles(677)

Power Contacts(3)

Rectangular Power Connectors(1178)

Wire-to-Board Headers & Receptacles (677)

Customers Also Bought

TE Part #2-917807-3
DYNAMIC D-5200M REC HSG 6P Y-Y

TE Part #1825027-5
FSMRA2JH04=R/A,TACT PB SW,160G

TE Part #5-1437175-5
FSP-24A

TE Part #CAT-104MTA-PRUSH
PCB Header: Polyester, Right Angle, Unshrouded






TE Part #6609047-3
15VT1=F7334 S0




TE Part #5-147105-5
10 MODIV VRT DR SFMNT 30AU



TE Part #7-2176092-1
RP 2A 0.25W 4K12 0.1% 25PPM 1K RL



TE Part #1-1546306-5
15P.374" DR BARRIER STRIP



TE Part #8-966140-6
TAB HEADER 2.8 X 0.8 MM 21 POS

Documents

Product Drawings

10P MTA156 HDR FLRA FB 30AU LF

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_4-641210-0_AB.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_4-641210-0_AB.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_4-641210-0_AB.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Agency Approvals

UL

English