

WMTS (18X4)R YE - Cable marker



1352330

<https://www.phoenixcontact.com/in/products/1352330>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable marker, Roll, yellow, unlabeled, can be labeled with: THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMaster 300/600, THERMOMARK X1.2, mounting type: insert, cable diameter range: 0.6 ... 45 mm, Number of individual labels: 3000, text field height: 4 mm, text field width: 18 mm

Your advantages

- The WMTS ... range of marking material off the roll includes markers for wire marking with threading and insertion aid for the marking sleeves from the PATG/PATO ... system
- Thanks to their special shape, the WMTS ... insert labels remain securely inside the sleeve once inserted
- Quick and inexpensive marking with THERMOMARK ... roll printers from Phoenix Contact
- When combined with the right ink ribbon, the marking is highly resistant to solvents and mechanical influences

Commercial data

Item number	1352330
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	BG2211
GTIN	4063151674816
Weight per piece (including packing)	447.3 g
Weight per piece (excluding packing)	447.6 g
Country of origin	DE

WMTS (18X4)R YE - Cable marker



1352330

<https://www.phoenixcontact.com/in/products/1352330>

Technical data

Product properties

Product type	Conductor marking
Type	Roll

Marking

Number of individual labels	3000
Number of individual labels per row	1
Identification technology	Thermal transfer for rolls

Dimensions

Width	4 mm
Text field width	18.00 mm
Text field height	4.00 mm
Length	18 mm

Material specifications

Color	yellow (RAL 1018)
Material	PET
Components	halogen-free

Cable/line

External cable diameter	0.6 mm ... 45 mm
-------------------------	------------------

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

Scratch test for the determining scratch resistance

Specification	DIN EN ISO 1518-1:2019-10 (following)
Requirements	≥ 5 N
Result	Test passed

Tesafilm test

Specification	DIN EN ISO 2409:2013 (following)
Result	Test passed

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h

WMTS (18X4)R YE - Cable marker



1352330

<https://www.phoenixcontact.com/in/products/1352330>

Temperature resistance

Specification	ANSI/UL 969-2018:03 (following)
Test duration	240 h
Rating 125 °C (150 °C)	Test passed

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropyl [CAS No. 67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Specification	ISO 175:2010 (following)
Test duration	168 h
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Diesel [CAS No. 68476-34-6]	Test passed
IRM 901	Test passed
IRM 902	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	ISO 22479:2019-05
Result	Test passed
Procedure	Method B
Cycles	2

Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed
Test duration	96 h

Ambient conditions

Ambient temperature (operation)	-25 °C ... 80 °C
Recommended ambient temperature (storage/transport)	20 °C ... 25 °C
Recommended humidity (storage/transport)	40 % ... 50 % (Storage in a dry and dark place in the original packaging is recommended)
Shelf life	2 years

Mounting

WMTS (18X4)R YE - Cable marker



1352330

<https://www.phoenixcontact.com/in/products/1352330>

Mounting type	insert
---------------	--------

WMTS (18X4)R YE - Cable marker

1352330

<https://www.phoenixcontact.com/in/products/1352330>



Classifications

ECLASS

ECLASS-11.0	27281106
ECLASS-12.0	27281106
ECLASS-13.0	27281106

ETIM

ETIM 9.0	EC001288
----------	----------

WMTS (18X4)R YE - Cable marker

1352330

<https://www.phoenixcontact.com/in/products/1352330>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

WMTS (18X4)R YE - Cable marker

1352330

<https://www.phoenixcontact.com/in/products/1352330>



Accessories

THERMOMARK ROLL 2.0 - Thermal transfer printer

1085260

<https://www.phoenixcontact.com/in/products/1085260>



Thermal transfer printer for material off the roll, incl. Euro/US power cable and USB cable. Operating instructions printed in German and English. 1 roll of labels EML (20x8)R white = 1000 labels, ink ribbon = 50 m

THERMOMARK-RIBBON 110-WMTB HF - Ink ribbon

5148007

<https://www.phoenixcontact.com/in/products/5148007>



Ink ribbon, for roll printer for printing product groups WMTB HF..., WMS-2 HF..., TMT..., EMT..., EMLF..., PML-..., length: 300 m, roll length: 300 m, width: 110 mm, color: black

WMTS (18X4)R YE - Cable marker

1352330

<https://www.phoenixcontact.com/in/products/1352330>



PATG 0/18 - Conductor marker carrier

0820507

<https://www.phoenixcontact.com/in/products/0820507>



Conductor marker carrier, transparent, unlabeled, mounting type: slide-on, cable diameter range: 0.6 ... 1.2 mm, text field height: 4 mm, text field width: 18 mm

PATG 1/18 - Conductor marker carrier

0820510

<https://www.phoenixcontact.com/in/products/0820510>



Conductor marker carrier, transparent, unlabeled, mounting type: slide-on, cable diameter range: 1.5 ... 2.5 mm, text field height: 4 mm, text field width: 18 mm

WMTS (18X4)R YE - Cable marker

1352330

<https://www.phoenixcontact.com/in/products/1352330>



PATG 2/18 - Conductor marker carrier

0820523

<https://www.phoenixcontact.com/in/products/0820523>



Conductor marker carrier, transparent, unlabeled, mounting type: slide-on, cable diameter range: 2 ... 4 mm, text field height: 4 mm, text field width: 18 mm

PATG 3/18 - Conductor marker carrier

0820536

<https://www.phoenixcontact.com/in/products/0820536>



Conductor marker carrier, transparent, unlabeled, mounting type: slide-on, cable diameter range: 4 ... 7 mm, text field height: 4 mm, text field width: 18 mm

WMTS (18X4)R YE - Cable marker

1352330

<https://www.phoenixcontact.com/in/products/1352330>



PATG 4/18 - Conductor marker carrier

0820549

<https://www.phoenixcontact.com/in/products/0820549>



Conductor marker carrier, transparent, unlabeled, mounting type: slide-on, cable diameter range: 6 ... 10 mm, text field height: 4 mm, text field width: 18 mm

PATG 5/18 - Conductor marker carrier

0828059

<https://www.phoenixcontact.com/in/products/0828059>



Conductor marker carrier, transparent, unlabeled, mounting type: slide-on, cable diameter range: 10 ... 14 mm, text field height: 4 mm, text field width: 18 mm

WMTS (18X4)R YE - Cable marker

1352330

<https://www.phoenixcontact.com/in/products/1352330>



PATG 6/18 - Conductor marker carrier

0828062

<https://www.phoenixcontact.com/in/products/0828062>



Conductor marker carrier, transparent, unlabeled, mounting type: slide-on, cable diameter range: 14 ... 22 mm, text field height: 4 mm, text field width: 18 mm

PATO 1/18 - Conductor marker carrier

0823740

<https://www.phoenixcontact.com/in/products/0823740>



Conductor marker carrier, transparent, unlabeled, mounting type: clip on, cable diameter range: 2 ... 3.5 mm, text field height: 4 mm, text field width: 18 mm

WMTS (18X4)R YE - Cable marker

1352330

<https://www.phoenixcontact.com/in/products/1352330>



PATO 2/18 - Conductor marker carrier

0823753

<https://www.phoenixcontact.com/in/products/0823753>



Conductor marker carrier, transparent, unlabeled, mounting type: clip on, cable diameter range: 2.8 ... 4.4 mm, text field height: 4 mm, text field width: 18 mm

THERMOMARK ROLLMASTER 300 - Thermal transfer printer

0804501

<https://www.phoenixcontact.com/in/products/0804501>



Thermal transfer printer for material off the roll, incl. Euro/US power cable and USB cable. Support CD includes user manuals in several languages, links to firmware, drivers, and planning and marking software. Operating instructions printed in German and English. 1 roll of labels EML (20x8)R white = 1000 labels, ink ribbon = 50 m

WMTS (18X4)R YE - Cable marker

1352330

<https://www.phoenixcontact.com/in/products/1352330>



THERMOMARK ROLLMASTER 600 - Thermal transfer printer

0804663

<https://www.phoenixcontact.com/in/products/0804663>



Thermal transfer printer for material off the roll, incl. Euro/US power cable and USB cable. Support CD includes user manuals in several languages, links to firmware, drivers, and planning and marking software. Operating instructions printed in German and English. 1 roll of labels EML (20x8)R white = 1000 labels, ink ribbon = 50 m

THERMOMARK ROLL - Thermal transfer printer

5146477

<https://www.phoenixcontact.com/in/products/5146477>



Thermal transfer printer, 300 dpi, incl. European power cable, US power cable, and USB cable. DVD with CLIP PROJECT advanced planning and marking software, user manuals in various languages, Windows® printer driver, and firmware. German/English user manual in DIN A5 format, EML (20x8)R roll of labels, white, with 1000 labels, and ink ribbon: 50 m

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.
A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420
info@phoenixcontact.co.in