


angle seat valve

VZXA-B-TS6-20-M2-V13T-12.8-K-46-17-V4

Part number: 8060528

FESTO

Modular, pneumatically actuated angle seat valve in stainless steel.
Under seat version, safety position closed, G thread, nominal width DN20.



Data sheet

| Feature | Value |
|---|---|
| Design structure | Poppet valve with piston actuator |
| Type of actuation | pneumatic |
| Assembly position | Any |
| Mounting type | Line installation |
| Line connection | G $\frac{3}{4}$ threaded collar to DIN ISO 228 |
| Valve function | 2/2 |
| Flow direction | non reversible |
| Medium pressure | 0 ... 12.8 bar |
| Type of reset | mechanical spring |
| Type of piloting | With external control |
| Pneumatic connection | Female thread G1/8 |
| Operating pressure | 5 ... 10 bar |
| Medium | Vapour Mineral oil-based hydraulic oil Inert gases Mineral oil Water Filtered compressed air, degree of filtration 200 μ m Neutral fluids |
| Flow direction | Below valve seat, for gaseous and liquid media |
| Control of the medium | On/off operation |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:4:4] |
| Max. viscosity | 600 mm ² /s |
| Medium temperature | -10 ... 180 °C |
| Ambient temperature | 0 ... 60 °C |
| Flow rate Kv | 13.3 m ³ /h |
| Materials note | Contains PWIS substances Conforms to RoHS |
| Material process valve housing | Stainless steel casting |
| Material number, process valve housing | 1.4409 |
| Material seals | FPM |
| Material spindle seal | PTFE |
| Material seat seal | PTFE |
| Product weight | 1,910 g |
| Authorisation | CRN |
| CE mark (see declaration of conformity) | to EU directive for machinery |
| Certificate issuing department | CRNOC20829.5C TÜV 968/V 1039.00/18 |
| Safety Integrity Level (SIL) | SIL 2 |
| Probability of Failure per Hour in [1/h]. | 1.36E-07 |
| PFD (Probability of Failure on Demand) | 5.95E-04 |
| Actuator size | 46 mm |
| Stroke | 17 mm |

| Feature | Value |
|-----------------------------------|---------------------------------|
| Control function | Closed via spring force, NC |
| Position detection | With mechanical indicator |
| Material drive housing | Stainless steel casting |
| Material number, actuator housing | 1.4408 |
| Storage temperature | -10 ... 60 °C |
| Protection class | IP65 IP67 IP69K |
| Material piston rod | High alloy steel, non-corrosive |
| Material cover | Stainless steel casting |