

18V Scarifier Brushless LXT®

DUV320

320 mm, 30 L

Model DUV320 is a 320mm Scarifier powered by an 18V LXT® Li-Ion battery.

Revitalise your lawn through aeration and dethatching, these two practices are essential for promoting and managing healthy lawns. Features and Benefits: Electric brake, Anti-restart function, IPX4 compatibility, Working depth adjustment, Warning lamp.



Technical specifications

Voltage LXT	✓
Nominal Battery Voltage	18 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Working width	320 mm
No load speed	3300 min ⁻¹
Rear Wheel Diameter	16 cm
Front Wheel Diameter	16 cm
Working Depth	-8 - +4 mm
Collecting Box Capacity	30 L
Sound Power Level (L _{WA})	89 dB(A)
Sound Pressure Level (L _{pA})	75 dB(A)
Product net weight	9,7 kg
Noise Uncertainty (K Factor)	3 dB(A)
Tool weight with battery	10,1 - 10,4 kg
Product Dimensions (L x W x H):	1035 x 565 x 995

User benefits

- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Electric brake for maximum productivity and increased operator safety
- Lightweight for easy portability
- Foldable handle

Link to product - www.makita.uk.com



Related products

Other

User manual

Parts drawing