

**5935VI/2MB**
**Assortment of 133 tools for industrial maintenance in EVA foam trays**

Industrial maintenance

|  |  | art.       |
|--|-----------------------------------------------------------------------------------|------------|
|  | <b>059351316</b>                                                                  | 5935VI/2MB |

- n. 21 **42:** combination wrenches  
6-7-8-9-10-11-12-13-14-15-16-17-18-19-20-21-22-24-27-30-32 mm
- n. 8 **55:** double open end wrenches 6x7-8x9-10x11-12x13-14x15  
16x17-18x19-20x22 mm
- n. 1 **1048N:** slip joint pliers, slip-proof PVC coated handles 250 mm
- n. 19 **920A:** 1/2" square drive hexagon sockets ○  
10-11-12-13-14-15-16-17-18-19-20-21-22-23-24-26-27-30-32 mm
- n. 1 **920AN/125:** 1/2" wobble extension bar 125 mm
- n. 1 **920AN/250:** 1/2" wobble extension bar 150 mm
- n. 1 **920/25:** 1/2" drive universal joint
- n. 1 **920/42:** 1/2" drive sliding T-handle
- n. 1 **920/55:** 1/2" reversible ratchet Ⓢ
- n. 1 **111E:** Adjustable wrench 250 mm
- n. 1 **1052:** self - locking pliers 240 mm
- n. 1 **1084BM:** Heavy-duty diagonal cutting nippers ⚡ 160 mm
- n. 1 **1150BM:** combination pliers bright chrome-plated, bi-material handles =  
180 mm
- n. 1 **1166BM:** Extra-long needle nose pliers ● 160 mm
- n. 1 **1032:** circlip pliers straight, internal ⊙ 180 mm
- n. 1 **1034:** circlip pliers bent, internal ⊙ 170 mm
- n. 1 **1036:** circlip pliers straight, external ● 175 mm
- n. 1 **1038:** circlip pliers bent, external ● 175 mm
- n. 13 **900:** 1/4" hexagon sockets ○ 4-4,5-5-5,5-6-7-8-9-10-11-12-13-14 mm
- n. 1 **900/20:** 1/4" drive extension bar 50 mm
- n. 1 **900/21:** 1/4" drive extension bar 150 mm
- n. 1 **900/25:** 1/4" drive universal joint
- n. 1 **900BG/30:** 1/4" drive spinner handle
- n. 1 **900/55N:** 1/4" reversible ratchet Ⓢ
- n. 1 **900/42:** 1/4" drive swivel T-handle
- n. 7 **1260:** screwdrivers for slotted head screws ●  
2,5x50-3x75-3,5x100-4x100-5,5x125-6,5x150-8x200 mm
- n. 2 **1260N:** screwdrivers for slotted head screws, extra-short series ●  
4x30-6,5x30 mm
- n. 7 **1262:** screwdrivers for cross head Phillips® screws ⊕  
PH0x60-PH0x100-PH1x80-PH1x120-PH2x100-PH2x150-PH3x150 mm
- n. 2 **1262N:** screwdrivers for cross head Phillips® screws, extra - short series ⊕  
PH1x30-PH2x30 mm
- n. 1 **1253:** mains testing screwdriver ● 4x30-6,5x30 mm
- n. 9 **96BPC/SC9:** ball head offset hexagon key wrenches ○
- n. 6 **951:** T-handle wrenches with hexagon male ends ○ 2,5-3-4-5-6-8 mm
- n. 5 **31:** pin punches Ø 2-3-4-5-6 mm
- n. 1 **32:** centre punch Ø 4 mm

