





LOC	DIST	REVISIONS				
AJ	16	REV	DATE	BY	APP'D	
		A	REVISED PER EC 0514-0150-05	05OCT2005	REH	JH



- 1 ZINC PER QQ-Z-363.
- 2 POLYMETHYLPENTENE, GENERAL PURPOSE.
- 3 BERYLLIUM COPPER PER QQ-C-530.
- 4 BRASS PER ASTM-B-453.
- 5 BRASS PER ASTM-B-16.
- 6 NICKEL PLATE PER QQ-N-290, 3.81 μm [.000150] MINIMUM THICK.
- 7 TIN PLATE PER ASTM-B-545, 3.81 μm [.000150] MINIMUM THICK.
- 8 GOLD PLATE PER ASTM-B-488, 0.76 μm [.000030] MINIMUM THICK.
9. SEE INSTRUCTION SHEET 408-2769.



RECOMMENDED PANEL CUTOUT



PCB CONFIGURATION

2.03±0.13 [.080±.005]	2.29±0.13 [.090±.005]	5414907-3
2.03±0.13 [.080±.005]	2.79±0.25 [.110±.010]	5414907-2
3.48±0.25 [.137±.010]	4.11±0.43 [.162±.017]	5414907-1

B	A	PART NUMBER
---	---	-------------

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. ALCORTA - 26APR2005			Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: mm [INCHES]		CHK J. HAVENER	26APR2005	NAME		
		APP'D J. LIPPERT	26APR2005	JACK, RIGHT ANGLE, 75 OHM, LOW PROFILE, PCB, BNC —		
		PRODUCT SPEC				
		APPLICATION SPEC				
		WEIGHT				
MATERIAL SEE NOTES 1 - 5		TOLERANCES UNLESS OTHERWISE SPECIFIED:		SIZE A1		CAGE CODE 00779
				DRAWING NO 5414907		RESTRICTED TO
				SCALE 5:1		SHEET 1 OF 1
				REV A		