




Connectors > Connector Accessories > Connector Strain Relief



Strain Relief Accessory Type: **Ferrule**

Primary Product Material: **Copper**

Packaging Method: **Carton**

Features

Product Type Features

Compatible With RF Cable Type	RG 178, RG 178A, RG 178B, RG 196, RG 196A
Strain Relief Accessory Type	Ferrule

Body Features

Primary Product Plating Material	Tin
Primary Product Material	Copper

Dimensions

Compatible Insulation Diameter Range	2.11 mm[.083 in]
--------------------------------------	------------------

Packaging Features

Packaging Method	Carton
------------------	--------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC



Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #534237-3
05 MODII VRT SR CE 100/115



TE Part #ANT-W63WS4-SMA
Antenna Blade Wifi6 Swivel SMA



TE Part #200517-9
34 POS. SHIELD ASSY.



TE Part #1766283-1
CONTACT,PIN,#4,M5



TE Part #1624000-3
SC30-10-2525-10 10UH AMMO 1000




TE Part #ANT-916-CW-RCS
Antenna 1/4 Wave R-Angle 916MHz RPS



TE Part #4-1879378-1
TLR 2512 2.0W R0025 1% 150PPM 2K RL



TE Part #6766615-1
293-0091-01100=HSG ASSY W/CLIPS RL



TE Part #226537-1
SUB MIN PIN MULTIMATE



TE Part #6648434-1
CONTACT,SKT,SIZE 1/4 (712-81-01107)

Documents

Product Drawings

FERRULE COAXICON SUB-MIN



English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-332057-0_F.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-332057-0_F.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-332057-0_F.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

AMP Circular Connectors for Commercial Signal & Power Applications

English

COAXICON Contacts

English

Coaxial Contacts

English

M_SERIES_PIN_AND_SOCKET_CONNECTORS

English

Product Specifications

Product Specification

English

Instruction Sheets

Instruction Sheet (non U.S.)

English

TYPICAL ASSEMBLY

English

Agency Approvals

Agency Approval Document

English