

Portable Bandsaw XGT®

PB002G

40Vmax • 127 mm • 0 - 3,2 m/s

Powerful XGT® Battery powered Bandsaw

Efficient portable bandsaw for spark-free metal cutting. With high cutting speed you get high cutting efficiency. Powerful BL motor enables the high cutting speed.



Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	40 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Max. Cutting Capacity in Steel Pipe	127 x 127 mm
Blade Diametre	13 x 0,5 x 1140 mm
Blade rapidity	0 - 3,2 m/s
Electronic brake	✓
Sound Pressure Level (L _{pA})	78 dB(A)
Product net weight	5,9 kg
Noise Uncertainty (K Factor)	3 dB(A)
Tool weight with battery	6,6 - 7,8 kg
Product Dimensions (L x W x H):	510 x 218 x 314 mm
Vibration Level, Cutting metal	≤ 2,5 m/s ²
Vibration Uncertainty (K Factor), Cutting metal	1,5 m/s ²
Brushless Motor	✓

User benefits

- LED light illuminates the work site
- The rubber coating on the handle ensures a firm working grip
- Electric brake for maximum productivity and increased operator safety

Link to product - www.makitauk.com



Related products

Other

User manual

Parts drawing