

2 41X46

Double ended ring spanner

Code	ETIM
6019770	EC002188
EAN	UNSPSC
4010886601976	27-11-17-05
Country of origin	eCl@ss
Germany	21-04-01-06
Customs tariff number	
82041100	



Article description

- Acc. to DIN 838, ISO 3318, ISO 1085, ISO 10104
- Rings deep offset, strong but thin walls
- Vanadium steel 31CrV3, chrome-plated
- Satin non-glare finish
- Carefully forged and professionally machined:
- Ring: thin-walled, 5° deep offset from shaft, with UD profile for gentle transmission of force
- High bending strength - does not fracture or splinter when overloaded, thus minimising the risk of injury
- Overloading indicated by deformation
- For extremely deep or inset bolts
- Top-grade industrial quality for the hardest of continuous use

Article information

Contents (Qty of pieces)	1	Width of head 2 [mm]	68,9 mm
Version/Execution	Rings deep offset, strong but thin walls	Head height 2 [mm]	22,2 mm
Net weight [kg]	1,535 kg	Head height 1 [mm]	20,4 mm
Total length [mm]	495 mm	Width of head 1 [mm]	62,0 mm
Total width [mm]	70 mm	Width across flats [mm]	41x46
Total height [mm]	53 mm	Width across flats 2 [mm]	46
Surface	chrome-plated	Height of offset 1	42,8 mm
Material	31CrV3	Ring profile	UNIT-DRIVE
Standard	DIN 838 ISO 3310 ISO 1085 ISO 10104	Ring offset	5°
Width across flats 1 [mm]	41		