



**M12 FUEL™**

## M12 FCIWF12G3-502X

### M12 FUEL™ 1/2" COMPACT IMPACT WRENCH WITH FRICTION RING

Best in class power: 542 Nm of fastening and 745 Nm of nut-busting torque to tackle most common applications

A weight of 1 kg without battery and a length of 122 mm means better access to tight spaces and less user fatigue

3,000 RPMs for exceptional application speed

4-Mode DRIVE CONTROL allows the user to shift into four different speed and torque settings to maximise application versatility

Trigger mode selection for easy one hand selection of speed settings

Tri-LEDs for shadowless work area illumination

The DNA of our FUEL™ platform redefines the balance of cordless technologies. MILWAUKEE®'s POWERSTATE™ brushless motor, REDLITHIUM™ battery pack and REDLINK PLUS™ electronic intelligence delivering outstanding power, run time and durability

Flexible battery system: works with all MILWAUKEE® M12™ batteries



**REDLITHIUM™**



|                                      |                                                  |
|--------------------------------------|--------------------------------------------------|
| No load speed (rpm)                  | 0-930/ 0-2100/ 0-3000/ 0-1300                    |
| Impact rate (ipm)                    | 0-1,500 / 0-3,000 / 0-3,300 / -                  |
| Tool reception                       | 1/2" square                                      |
| Weight with battery pack (EPTA) (kg) | 1.5 (M12 HB5)                                    |
| Kit included                         | 2 x M12 HB5 Battery packs, C12 C Charger, HD Box |
| Article number                       | 4933493455                                       |