



Relays & Contactors > Relay Accessories



Relay Socket Type: **Solder**
Body Material: **Polyester**
Product Mount Type: **Board Mount**
Pole Configuration: **4**
Relay Accessory Type: **Socket**

Features

Product Type Features

Relay Accessory Type	Socket
----------------------	--------

Body Features

Body Material	Polyester
---------------	-----------

Contact Features

Contact Material	Spring Brass
Contact Plating Material	Tin
Terminal Style	Solder
Relay Socket Type	Solder
Pole Configuration	4

Termination Features


Number of Pins	16
Termination Post & Tail Length	5.33 mm[.21 in]

Mechanical Attachment

Product Mounting Feature Type	Side lock
Product Mount Type	Board Mount

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)






EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # 9-1393768-4
R10-R2P4-J2.5K=R10




TE Part # 2027515-5
R10-E1P4-SS2.2K = R10




TE Part # 1-2027011-0
R10-E2W4-S1.8K=RELAY,7.5A,4C, AGCDO,24VDC



TE Part # 3-1393159-6
20C250=SPRING,HOLD-DOWN,R10,.0



TE Part # 4-1393159-5
20C301=SPRING



TE Part # 1-2027515-3
R10-E1P4-V2.5K=R10

Also in the Series | Potter & Brumfield R10



AC Relays(9)

DC Relays(96)

Electromechanical Relays(105)

General Purpose Signal Relays(105)

PCB Headers & Receptacles(1)

Plug-In Relays(77)

Relay Accessories(27)

Customers Also Bought

TE Part #5-1617758-0
FCB-205-0224M=M83536/2-024M

TE Part #2-1630186-1
HSA50 R22 5%

TE Part #234064-E
STVBTL BUT 100 CSI 2026 207 * J 2 34093

TE Part #2-1879623-4
H4 250R 0.5% 25PPM

TE Part #2213775-9
AV16 SPM 0.4VA POWER LED BLUE 12V

TE Part #530604-002
22759/32-24-2

TE Part #1SNA114533R0000
EBS8A.G

TE Part #5061850001
TMS-SCE-1/2-2.0-9

TE Part #5206472-1
CABLE CLAMP KIT,SZ 3

TE Part #2176231-1
3522 10R 1% 3W

Documents



CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-1393143-7_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-1393143-7_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-1393143-7_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

R10 Sockets & Accessories

English

Product Specifications

Definitions General Purpose Relays

English