V1 29.03.2022



## Ball joint vice SPANNFIX for clamping on

Art.-No. 9-205

**Description** Ball joint vice SPANNFIX for clamping on

## **Features**

Precision ball joint rotatable 360°

steplessly lockable quick release

Quality product 100% Made in Germany

for clamping to the workbench (table thickness max 80 mm)

50 mm plastic jaws with grip

clamping width 70 mm

clamping depth 38 mm

clamping pressure 1470 N

inclination angle +/-45°

spare parts: jaws

article 9-900-E50 (pair)

more jaws search field input 9-900

cast aluminum, powder-coated, dark gray metallic

Dimensions approx. 310 × 170 × 75 mm

weight 1450 g



Maximum torque: ball Ø 40 mm approx. 24 Nm, ball Ø 60 mm approx. 100 Nm

clamp-base: table top thickness max. 80 mm

Cast aluminum parts powder coated

Steel parts chrome-plated, rust-free

With the adjusting screw on the lower seat of the ball, the movement of the ball can be adjusted from loose to very firm.

For safety-relevant parts, please note that we cannot give a guarantee of the holding forces without knowing your specific application. The ball may behave differently under different physical conditions than it does in our test laboratory in an optimal test environment.

## Parts list

