


06130035

RCK 13 - Self centring

2D Technical Drawing

Dynamic 3D View
Technical Specifications

Part number (CODE)	06130035
Ød (DD) mm	35
ØD (D) mm	60
L1 (L1) mm	17
L2 (L2) mm	22
L3 (L3) mm	28
L (L) mm	34
Maximum torque Mt (MT) Nm	1050
Clamping pressure - Shaft (CPS) N/mm ²	270
Clamping pressure - Hub (CPH) N/mm ²	155
Clamping screws DIN 912 MAT. 12.9 - Num. (CSN)	8
Clamping screws DIN 912 MAT. 12.9 - Type (CST)	M6x20
Clamping screws DIN 912 MAT. 12.9 - Torque (CSTQ) Nm	14
Extraction thread - Type (ETT)	M6
Extraction thread - Num. (ETN)	4
Weight (WEIGHT) kg	0.40