

# PRODUCT DATASHEET

## P CLAS A ADV 60 DIM 6.5 W/840 E27

PARATHOM Retrofit CLASSIC A DIM | Dimmable LED lamps, classic bulb shape

---

### AREAS OF APPLICATION

- Perfect for decorative installations
- Domestic applications
- General illumination
- Outdoor applications only in suitable luminaires

---

### PRODUCT BENEFITS

- Design, dimensions, luminous flux comparable to an incandescent or halogen lamp
- Very low energy consumption
- Robust against vibrations
- No UV and near-IR radiation in the light beam
- Instant 100 % light, no warm-up time
- Can be easily fitted instead of ordinary light bulbs
- Lower thermal output (compared with the standard reference product)

---

### PRODUCT FEATURES

- Professional LED lamps for line voltage
- Dimmable
- Base: E27
- Mercury-free lamps
- Lifetime: up to 15,000 h



**TECHNICAL DATA**

Electrical data

<b>Rated wattage</b>	6.50 W
<b>Nominal wattage</b>	6.50 W
<b>Nominal voltage</b>	220...240 V
<b>Operating frequency</b>	50...60 Hz
<b>Power factor <math>\lambda</math></b>	> 0.90
<b>Claimed equiv. conventional lamp power</b>	60 W


Photometrical data

<b>Nominal luminous flux</b>	806 lm
<b>Rated luminous flux</b>	806 lm
<b>Rated color temperature</b>	4000 K
<b>Color rendering index Ra</b>	$\geq 80$
<b>Lumen main.fact.at end of nom.life time</b>	0.70
<b>Light color (designation)</b>	Cool White
<b>Standard deviation of color matching</b>	$\leq 6$ sdc <sub>m</sub>

Light technical data

<b>Warm-up time (60 %)</b>	< 0.50 s
<b>Starting time</b>	< 0.5 s

— Dimensions & weight



<b>Overall length</b>	105.0 mm
<b>Diameter</b>	60.0 mm
<b>Outer bulb</b>	A60
<b>Length</b>	105.0 mm

Lifespan

Nominal lamp life time	15000 h
Rated lamp life time	15000 h
Number of switching cycles	100000
Lumen maintenance at end of service life	0.70

## Additional product data

Base (standard designation)	E27
Mercury content	0.0 mg
Mercury-free	Yes
Design / version	Frosted
Show WEEE picto	Yes
Product remark	All technical parameters apply to the entire lamp/Due to the complex production process for light-emitting diodes, the typical values shown for the technical LED parameters are purely statistical values that do not necessarily match the actual technical parameters of each individual product, which can vary from the typical value/LED lamps contain several electronic components. Under unfavourable conditions these can lead to acoustic noise. In case of resonance even low noise can cause audible effect. Possible factors influencing this are the installation, the design of the lamp holder and the luminaire (acoustic resonance effect) as well as the dimmer or the transformer (harmonics or electronic resonance)

## Capabilities

Dimmable	Yes
----------	-----

## Certificates &amp; standards

Energy efficiency class	A++
Energy consumption	7 kWh/1000h

## Country specific categorizations

ILCOS	DRAA/F-6,5-840-220-240-E27-60
Order reference	LEDPCLA60D 6,5W

## LOGISTICAL DATA

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4058075808270	P CLAS A ADV 60 DIM 6.5 W/840 E27	Shipping carton box 10	315 mm x 131 mm x 126 mm	5.20 dm <sup>3</sup>	567.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

## DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.