

PARATHOM PAR16

LED reflector lamps PAR16 with retrofit pin base



Areas of application

- Spotighting for accents
- Display cabinets and shop windows
- Retail outlets and exhibition rooms
- Spotighting heat-sensitive objects such as food, plants, etc.
- Outdoor applications only in suitable luminaires
- Directional light sources
- Hospitality
- Shops

Product benefits

- Excellent price/performance ratio
- Very low energy consumption
- Extremely long life
- Robust against vibrations
- No UV and near-IR radiation in the light beam
- Professional thermal management
- Efficient generation of white light
- Alternative to line-voltage halogen lamps
- Ideal for economical spotighting

Product features

- Professional LED lamps for line voltage
- Not dimmable
- Good color rendering ($R_a \geq 80$) and color stability throughout the life of the lamp
- Base: GU10
- Lifetime: up to 15,000 h



Product family datasheet

- Mercury-free lamps
- High color consistency

Product family datasheet

Technical data

Product description	Electrical data			Photometrical data						Light technical data	
	Nominal wattage	Nominal voltage	Claimed equiv. conventional lamp power	Luminous intensity	Nominal luminous flux	Rated luminous flux	Color temperature	Color rendering index Ra	Light color (designation)	Beam angle	Warm-up time (60 %)
PARATHOM PAR16 20 36° 1.6 W/827 GU10 ¹⁾	1.60 W	220...240 V	20 W	350 cd	110 lm	110 lm	2700 K	80	Warm White	24 °	< 0.50 s
PARATHOM PAR16 35 36° 3 W/827 GU10 ¹⁾	3.00 W	220...240 V	35 W	565 cd	230 lm	230 lm	2700 K	80	Warm White	36 °	0.30 s
PARATHOM PAR16 35 36° 3 W/840 GU10 ¹⁾	3.00 W	220...240 V	35 W	565 cd	230 lm	230 lm	4000 K	80	Cool White	36 °	0.30 s
PARATHOM PAR16 35 36° 3 W/830 GU10 ¹⁾	3.00 W	220...240 V	35 W	565 cd	230 lm	230 lm	3000 K	80	Warm White	36 °	0.30 s
PARATHOM PAR16 35 120° 3 W/827 GU10 ¹⁾	3.00 W	220...240 V		83 cd	200 lm	200 lm	2700 K	80	Warm White	120 °	0.30 s
PARATHOM PAR16 35 120° 3 W/840 GU10 ¹⁾	3.00 W	220...240 V		83 cd	210 lm	210 lm	4000 K	80	Cool White	120 °	0.30 s
PARATHOM PAR16 35 36° 3.9 W/827 GU10 ¹⁾	3.90 W	220...240 V	35 W	600 cd	230 lm	230 lm	2700 K	80	Warm White	36 °	< 0.50 s
PARATHOM PAR16 20 35° 5 W/740 GU10 ¹⁾	5.00 W	220...240 V	20 W	600 cd	230 lm	230 lm	4000 K	75	Cool White	35 °	0.00 s
PARATHOM PAR16 50 36° 5 W/840 GU10 ¹⁾	5.00 W	220...240 V	50 W	850 cd	350 lm	350 lm	4000 K	80	Cool White	36 °	0.30 s
PARATHOM PAR16 50 36° 5 W/827 GU10 ¹⁾	5.00 W	220...240 V	50 W	850 cd	350 lm	350 lm	2700 K	80	Warm White	36 °	0.30 s
PARATHOM PAR16 50 36° 5 W/830 GU10 ¹⁾	5.00 W	220...240 V	50 W	850 cd	350 lm	350 lm	3000 K	80	Warm White	36 °	0.30 s
PARATHOM PAR16 50 120° 5 W/840 GU10 ¹⁾	5.00 W	220...240 V			330 lm	330 lm	4000 K	80	Cool White	120 °	0.30 s
PARATHOM PAR16 50 120° 5 W/827 GU10 ¹⁾	5.00 W	220...240 V		130 cd	310 lm	310 lm	2700 K	80	Warm White	120 °	0.30 s

Product family datasheet

Product description	Electrical data			Photometrical data						Light technical data	
	Nominal wattage	Nominal voltage	Claimed equiv. conventional lamp power	Luminous intensity	Nominal luminous flux	Rated luminous flux	Color temperature	Color rendering index Ra	Light color (designation)	Beam angle	Warm-up time (60 %)
PARATHOM PAR16 50 36° 5,5 W/827 ¹⁾	5.50 W	220...240 V	50 W		350 lm	350 lm	2700 K	80		36 °	< 0.50 s
PARATHOM PAR16 50 36° 5,5 W/840 ¹⁾	5.50 W	220...240 V	50 W		350 lm	350 lm	4000 K	80	Cool White	36 °	0.20 s
PARATHOM PAR16 65 36° 5.5 W/827 GU10 ¹⁾	5.50 W	220...240 V	65 W	1164 cd	460 lm	460 lm	2700 K	80	Warm White	36 °	0.30 s
PARATHOM PAR16 65 36° 5.5 W/830 GU10 ¹⁾	5.50 W	220...240 V	65 W	1164 cd	460 lm	460 lm	3000 K	80	Warm White	36 °	0.30 s
PARATHOM PAR16 80 36° 6.7 W/830 GU10 ¹⁾	6.70 W	220...240 V	80 W	1439 cd	575 lm	575 lm	3000 K	80	Warm White	36 °	0.30 s
PARATHOM PAR16 83 36° 8 W/827 GU10 ¹⁾	8.00 W	230 V	83 W		600 lm	600 lm	2700 K	80		36 °	1.00 s
PARATHOM PAR16 35 36° 2.6 W/827 GU10 ¹⁾	2.60 W	220...240 V	35 W	565 cd	230 lm	230 lm	2700 K	≥80	Warm White	36 °	1.00 s
PARATHOM PAR16 35 36° 2.6 W/840 GU10 ¹⁾	2.60 W	220...240 V	35 W	565 cd	230 lm	230 lm	4000 K	≥80	Cool White	36 °	1.00 s
PARATHOM PAR16 50 36° 4.3 W/827 GU10 ¹⁾	4.30 W	220...240 V	50 W	850 cd	350 lm	350 lm	2700 K	≥80	Warm White	36 °	1.00 s
PARATHOM PAR16 50 36° 4.3 W/840 GU10 ¹⁾	4.30 W	220...240 V	50 W	850 cd	350 lm	350 lm	4000 K	≥80	Cool White	36 °	1.00 s
PARATHOM PAR16 50 120° 4.3 W/827 GU10 ¹⁾	4.30 W	220...240 V	50 W	130 cd	350 lm	350 lm	2700 K	≥80	Warm White	120 °	1.00 s
PARATHOM PAR16 50 120° 4.3 W/840 GU10 ¹⁾	4.30 W	220...240 V	50 W	130 cd	330 lm	330 lm	4000 K	≥80	Cool White	120 °	1.00 s
PARATHOM PAR16 80 36° 6.9 W/827 GU10 ¹⁾	6.90 W	220...240 V	80 W	1164 cd	575 lm	575 lm	2700 K	≥80	Warm White	36 °	1.00 s
PARATHOM PAR16 80 36° 6.9 W/840 GU10 ¹⁾	6.90 W	220...240 V	80 W	1439 cd	575 lm	575 lm	4000 K	≥80	Cool White	36 °	1.00 s

Product family datasheet

Product description	Dimensions & weight		Lifespan			Additional product data			Capabilities
	Overall length	Diameter	Nominal lamp life time	Number of switching cycles	Lumen main. fact. at end of nom. life time	Base (standard designation)	Mercury content	Mercury-free	Dimmable
PARATHOM PAR16 20 36° 1.6 W/827 GU10 ¹⁾	58.0 mm	50.0 mm	15000 h	100000	0.70	GU10	0.0 mg	Yes	No
PARATHOM PAR16 35 36° 3 W/827 GU10 ¹⁾	58.0 mm	49.6 mm	15000 h	100000	0.70	GU10	0.0 mg	Yes	No
PARATHOM PAR16 35 36° 3 W/840 GU10 ¹⁾	58.0 mm	49.6 mm	15000 h	100000	0.70	GU10	0.0 mg	Yes	No
PARATHOM PAR16 35 36° 3 W/830 GU10 ¹⁾	58.0 mm	49.6 mm	15000 h	100000	0.70	GU10	0.0 mg	Yes	No
PARATHOM PAR16 35 120° 3 W/827 GU10 ¹⁾	58.0 mm	49.6 mm	15000 h	100000	0.70	GU10	0.0 mg	Yes	No
PARATHOM PAR16 35 120° 3 W/840 GU10 ¹⁾	58.0 mm	49.6 mm	15000 h	100000	0.70	GU10	0.0 mg	Yes	No
PARATHOM PAR16 35 36° 3.9 W/827 GU10 ¹⁾	58.0 mm	50.0 mm	15000 h	100000	0.70	GU10	0.0 mg	Yes	No
PARATHOM PAR16 20 35° 5 W/740 GU10 ¹⁾	57.0 mm	50.0 mm	25000 h	100000	0.70	GU10	0.0 mg	Yes	No
PARATHOM PAR16 50 36° 5 W/840 GU10 ¹⁾	58.0 mm	49.6 mm	15000 h	100000	0.70	GU10	0.0 mg	Yes	No
PARATHOM PAR16 50 36° 5 W/827 GU10 ¹⁾	58.0 mm	49.6 mm	15000 h	100000	0.70	GU10	0.0 mg	Yes	No
PARATHOM PAR16 50 36° 5 W/830 GU10 ¹⁾	58.0 mm	49.6 mm	15000 h	100000	0.70	GU10	0.0 mg	Yes	No
PARATHOM PAR16 50 120° 5 W/840 GU10 ¹⁾	58.0 mm	50.0 mm	15000 h	100000	0.70	GU10	0.0 mg	Yes	No
PARATHOM PAR16 50 120° 5 W/827 GU10 ¹⁾	58.0 mm	49.6 mm	15000 h	100000	0.70	GU10	0.0 mg	Yes	No
PARATHOM PAR16 50 36° 5,5 W/827 ¹⁾	58.0 mm	50.0 mm	15000 h	100000	0.70	GU10	0.0 mg	Yes	No

Product family datasheet

Product description	Dimensions & weight		Lifespan			Additional product data			Capabilities
	Overall length	Diameter	Nominal lamp life time	Number of switching cycles	Lumen main. fact. at end of nom. life time	Base (standard designation)	Mercury content	Mercury-free	Dimmable
PARATHOM PAR16 50 36° 5.5 W/840 ¹⁾	58.0 mm	50.0 mm	15000 h	100000	0.70	GU10	0.0 mg	Yes	No
PARATHOM PAR16 65 36° 5.5 W/827 GU10 ¹⁾	58.0 mm	49.6 mm	15000 h	100000	0.70	GU10	0.0 mg	Yes	No
PARATHOM PAR16 65 36° 5.5 W/830 GU10 ¹⁾	58.0 mm	49.6 mm	15000 h	100000	0.70	GU10	0.0 mg	Yes	No
PARATHOM PAR16 80 36° 6.7 W/830 GU10 ¹⁾	58.0 mm	49.6 mm	15000 h	100000	0.70	GU10	0.0 mg	Yes	No
PARATHOM PAR16 83 36° 8 W/827 GU10 ¹⁾	58.0 mm	50.0 mm	30000 h	100000	0.70	GU10	0.0 mg	Yes	No
PARATHOM PAR16 35 36° 2.6 W/827 GU10 ¹⁾	55.0 mm	51.0 mm	15000 h	100000	0.70	GU10	0.0 mg	Yes	No
PARATHOM PAR16 35 36° 2.6 W/840 GU10 ¹⁾	55.0 mm	51.0 mm	15000 h	100000	0.70	GU10	0.0 mg	Yes	No
PARATHOM PAR16 50 36° 4.3 W/827 GU10 ¹⁾	55.0 mm	51.0 mm	15000 h	100000	0.70	GU10	0.0 mg	Yes	No
PARATHOM PAR16 50 36° 4.3 W/840 GU10 ¹⁾	55.0 mm	51.0 mm	15000 h	100000	0.70	GU10	0.0 mg	Yes	No
PARATHOM PAR16 50 120° 4.3 W/827 GU10 ¹⁾	55.0 mm	51.0 mm	15000 h	100000	0.70	GU10	0.0 mg	Yes	No
PARATHOM PAR16 50 120° 4.3 W/840 GU10 ¹⁾	55.0 mm	51.0 mm	15000 h	100000	0.70	GU10	0.0 mg	Yes	No
PARATHOM PAR16 80 36° 6.9 W/827 GU10 ¹⁾	55.0 mm	51.0 mm	15000 h	100000	0.70	GU10	0.0 mg	Yes	No
PARATHOM PAR16 80 36° 6.9 W/840 GU10 ¹⁾	55.0 mm	51.0 mm	15000 h	100000	0.70	GU10	0.0 mg	Yes	No

Product family datasheet


Product description	Certificates & standards		Country specific categorizations
	Energy consumption	Energy efficiency class	ILCOS
PARATHOM PAR16 20 36° 1.6 W/827 GU10 ¹⁾	2 kWh/1000h	A+	DRPAR-2,5-100-240-GU10-50/36
PARATHOM PAR16 35 36° 3 W/827 GU10 ¹⁾	3 kWh/1000h	A++	DRPAR-3/827-220/240-GU10-50/36
PARATHOM PAR16 35 36° 3 W/840 GU10 ¹⁾	3 kWh/1000h	A++	DRPAR-3/840-220/240-GU10-50/36
PARATHOM PAR16 35 36° 3 W/830 GU10 ¹⁾	3 kWh/1000h	A++	DRPAR-3/830-220/240-GU10-50/36
PARATHOM PAR16 35 120° 3 W/827 GU10 ¹⁾	3 kWh/1000h	A+	DRPAR-3/827-230-GU10-50/36
PARATHOM PAR16 35 120° 3 W/840 GU10 ¹⁾	3 kWh/1000h	A++	DRPAR-3/840-230-GU10-50/36
PARATHOM PAR16 35 36° 3.9 W/827 GU10 ¹⁾	4 kWh/1000h	A+	DRPAR-4,5-100-240-GU10-50/36
PARATHOM PAR16 20 35° 5 W/740 GU10 ¹⁾			DRPAR-5-220/240-GU10-50/35
PARATHOM PAR16 50 36° 5 W/840 GU10 ¹⁾	5 kWh/1000h	A+	DRPAR-5/840-220/240-GU10-50/36
PARATHOM PAR16 50 36° 5 W/827 GU10 ¹⁾	5 kWh/1000h	A+	DRPAR-5/827-220/240-GU10-50/36
PARATHOM PAR16 50 36° 5 W/830 GU10 ¹⁾	5 kWh/1000h	A+	DRPAR-5/830-220/240-GU10-50/36
PARATHOM PAR16 50 120° 5 W/840 GU10 ¹⁾	5 kWh/1000h	A+	DRPAR-5/840-230-GU10-50/120
PARATHOM PAR16 50 120° 5 W/827 GU10 ¹⁾	5 kWh/1000h	A+	DRPAR-5/827-230-GU10-50/120
PARATHOM PAR16 50 36° 5,5 W/827 ¹⁾	6 kWh/1000h	A+	

Product family datasheet


Product description	Certificates & standards		Country specific categorizations
	Energy consumption	Energy efficiency class	ILCOS
PARATHOM PAR16 50 36° 5,5 W/840 ¹⁾	5 kWh/1000h	A+	
PARATHOM PAR16 65 36° 5.5 W/827 GU10 ¹⁾	6 kWh/1000h	A+	DRPAR-5,5/827-230-GU10-50/36
PARATHOM PAR16 65 36° 5.5 W/830 GU10 ¹⁾	6 kWh/1000h	A+	DRPAR-5,5/830-230-GU10-50/36
PARATHOM PAR16 80 36° 6.7 W/830 GU10 ¹⁾	7 kWh/1000h	A+	DRPAR-6,7/830-230-GU10-50/36
PARATHOM PAR16 83 36° 8 W/827 GU10 ¹⁾	8 kWh/1000h	A+	
PARATHOM PAR16 35 36° 2.6 W/827 GU10 ¹⁾	3 kWh/1000h	A+	DRPAR-2,6/827-220-240-GU10-50/36
PARATHOM PAR16 35 36° 2.6 W/840 GU10 ¹⁾	3 kWh/1000h	A+	DRPAR-2,6/840-220-240-GU10-50/36
PARATHOM PAR16 50 36° 4.3 W/827 GU10 ¹⁾	5 kWh/1000h	A+	DRPAR-4,3/827-220-240-GU10-50/36
PARATHOM PAR16 50 36° 4.3 W/840 GU10 ¹⁾	5 kWh/1000h	A+	DRPAR-4,3/840-220-240-GU10-50/36
PARATHOM PAR16 50 120° 4.3 W/827 GU10 ¹⁾	5 kWh/1000h	A+	DRPAR-4,3/827-220-240-GU10-50/36
PARATHOM PAR16 50 120° 4.3 W/840 GU10 ¹⁾	5 kWh/1000h	A+	DRPAR-4,3/840-220-240-GU10-50/36
PARATHOM PAR16 80 36° 6.9 W/827 GU10 ¹⁾	7 kWh/1000h	A+	DRPAR-6,9/827-220-240-GU10-50/36
PARATHOM PAR16 80 36° 6.9 W/840 GU10 ¹⁾	7 kWh/1000h	A+	DRPAR-6,9/840-220-240-GU10-50/36

¹⁾ All technical parameters apply to the entire lamp/Due to the complex production process for light-emitting diodes, the typical values shown for the technical LED parameters are purely statistical values that do not necessarily match the actual technical parameters of each individual product, which can vary from the typical value


Product family datasheet




PARATHOM PAR16 20 36° 1.6 W/827
GU10



PARATHOM PAR16 35 36° 3 W/827
GU10, PARATHOM PAR16 35 36° 3
W/840 GU10, PARATHOM PAR16 35
36° 3 W/830 GU10, PARATHOM
PAR16 50 36° 5 W/827 GU10,
PARATHOM PAR16 50 120° 5 W/840
GU10




PARATHOM PAR16 35 120° 3 W/827
GU10, PARATHOM PAR16 35 120° 3
W/840 GU10, PARATHOM PAR16 50
36° 5 W/840 GU10, PARATHOM
PAR16 50 36° 5 W/830 GU10,
PARATHOM PAR16 50 120° 5 W/827
GU10, PARATHOM PAR16 50 36° 5,5
W/840




PARATHOM PAR16 35 36° 3.9 W/827
GU10


Product family datasheet




PARATHOM PAR16 20 35° 5 W/740
GU10



PARATHOM PAR16 65 36° 5.5 W/827
GU10, PARATHOM PAR16 65 36° 5.5
W/830 GU10, PARATHOM PAR16 80
36° 6.7 W/830 GU10




PARATHOM PAR16 35 36° 2.6 W/827
GU10, PARATHOM PAR16 35 36° 2.6
W/840 GU10, PARATHOM PAR16 50
36° 4.3 W/827 GU10, PARATHOM
PAR16 50 36° 4.3 W/840 GU10,
PARATHOM PAR16 80 36° 6.9 W/827
GU10, PARATHOM PAR16 80 36° 6.9
W/840 GU10



PARATHOM PAR16 50 120° 4.3 W/827
GU10, PARATHOM PAR16 50 120° 4.3
W/840 GU10

Product family datasheet



PARATHOM PAR16 20 36° 1.6 W/827
GU10, PARATHOM PAR16 35 36° 3.9
W/827 GU10

Application advice

For more detailed application information and graphics please see product datasheet.

Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4052899910362	PARATHOM PAR16 20 36° 1.6 W/827 GU10	Shipping carton box 10	275 mm x 116 mm x 78 mm	2.49 dm ³	767.00 g
4052899943797	PARATHOM PAR16 35 36° 3 W/827 GU10	Shipping carton box 10	267 mm x 111 mm x 77 mm	2.28 dm ³	503.00 g

Product family datasheet

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4052899943810	PARATHOM PAR16 35 36° 3 W/840 GU10	Shipping carton box 10	267 mm x 111 mm x 77 mm	2.28 dm ³	502.00 g
4052899943803	PARATHOM PAR16 35 36° 3 W/830 GU10	Shipping carton box 10	267 mm x 111 mm x 77 mm	2.28 dm ³	503.00 g
4052899943889	PARATHOM PAR16 35 120° 3 W/827 GU10	Shipping carton box 10	267 mm x 111 mm x 77 mm	2.28 dm ³	506.00 g
4052899943896	PARATHOM PAR16 35 120° 3 W/840 GU10	Shipping carton box 10	267 mm x 111 mm x 77 mm	2.28 dm ³	518.00 g
4052899910379	PARATHOM PAR16 35 36° 3.9 W/827 GU10	Shipping carton box 10	275 mm x 116 mm x 78 mm	2.49 dm ³	769.00 g
4008321973634	PARATHOM PAR16 20 35° 5 W/740 GU10	Shipping carton box 10	114 mm x 78 mm x 271 mm	2.41 dm ³	612.00 g
4052899943841	PARATHOM PAR16 50 36° 5 W/840 GU10	Shipping carton box 10	267 mm x 111 mm x 77 mm	2.28 dm ³	508.00 g
4052899943827	PARATHOM PAR16 50 36° 5 W/827 GU10	Shipping carton box 10	267 mm x 111 mm x 77 mm	2.28 dm ³	520.00 g
4052899943834	PARATHOM PAR16 50 36° 5 W/830 GU10	Shipping carton box 10	267 mm x 111 mm x 77 mm	2.28 dm ³	518.00 g
4052899943940	PARATHOM PAR16 50 120° 5 W/840 GU10	Shipping carton box 10	267 mm x 111 mm x 77 mm	2.28 dm ³	502.00 g
4052899943933	PARATHOM PAR16 50 120° 5 W/827 GU10	Shipping carton box 10	267 mm x 111 mm x 77 mm	2.28 dm ³	519.00 g
4052899180697	PARATHOM PAR16 50 36° 5,5 W/827	Shipping carton box 10	267 mm x 111 mm x 77 mm	2.28 dm ³	857.00 g
4052899180727	PARATHOM PAR16 50 36° 5,5 W/840	Shipping carton box 10	267 mm x 111 mm x 77 mm	2.28 dm ³	780.00 g
4052899943858	PARATHOM PAR16 65 36° 5.5 W/827 GU10	Shipping carton box 10	267 mm x 111 mm x 77 mm	2.28 dm ³	822.00 g

Product family datasheet

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4052899943865	PARATHOM PAR16 65 36° 5.5 W/830 GU10	Shipping carton box 10	267 mm x 111 mm x 77 mm	2.28 dm ³	823.00 g
4052899943872	PARATHOM PAR16 80 36° 6.7 W/830 GU10	Shipping carton box 10	267 mm x 111 mm x 77 mm	2.28 dm ³	665.00 g
4052899203549	PARATHOM PAR16 83 36° 8 W/827 GU10	Shipping carton box 10	267 mm x 111 mm x 77 mm	2.28 dm ³	1120.00 g
4052899958050	PARATHOM PAR16 35 36° 2.6 W/827 GU10	Shipping carton box 10	257 mm x 110 mm x 70 mm	1.98 dm ³	545.00 g
4052899958067	PARATHOM PAR16 35 36° 2.6 W/840 GU10	Shipping carton box 10	257 mm x 110 mm x 70 mm	1.98 dm ³	545.00 g
4052899958104	PARATHOM PAR16 50 36° 4.3 W/827 GU10	Shipping carton box 10	257 mm x 110 mm x 70 mm	1.98 dm ³	545.00 g
4052899958128	PARATHOM PAR16 50 36° 4.3 W/840 GU10	Shipping carton box 10	257 mm x 110 mm x 70 mm	1.98 dm ³	549.00 g
4052899958111	PARATHOM PAR16 50 120° 4.3 W/827 GU10	Shipping carton box 10	257 mm x 110 mm x 70 mm	1.98 dm ³	545.00 g
4052899958142	PARATHOM PAR16 50 120° 4.3 W/840 GU10	Shipping carton box 10	257 mm x 110 mm x 70 mm	1.98 dm ³	548.00 g
4052899958173	PARATHOM PAR16 80 36° 6.9 W/827 GU10	Shipping carton box 10	257 mm x 110 mm x 70 mm	1.98 dm ³	545.00 g
4052899958180	PARATHOM PAR16 80 36° 6.9 W/840 GU10	Shipping carton box 10	257 mm x 110 mm x 70 mm	1.98 dm ³	545.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

References / Links

Product family datasheet

For further products and actual information concerning LED lamps see

▶ www.ledvance.com/ledlamps

For Guarantee see

▶ www.ledvance.com/guarantee

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.