


Titan anatomical tweezers 150 mm form 22b with guide pin serrated

Art.-No.	5-037
Description	Titan anatomical tweezers 150 mm form 22b with guide pin serrated
Application	Electronics, SMD/THT assembly, precision mechanics, watchmakers, jewelers, medical technology.
Specification	with serration
Material	Titan
Surface/Coating	matt finish
Features	antibacterial, antimagnetic, heat-resistant, solder-repellent:acid-resistant, non-reflecting, stainless, seawater resistant
Surface resistance	/
Shape	NB: Normal tips bent
Icon No.	NB2

Dimensions and weight

A = 45 mm
 B = 18 mm
 C = 10 mm
 Ai = /
 angle = 60°

length 150 mm
 weight 12 g



Application and technical data

Tweezers are made entirely of TITAN (light metal) and meet the highest technical requirements. Melting point 1941 K (1668°C), thermal conductivity 22W, electrical conductivity 2.5×10^6 .