

## LEDVANCE® Linear

### Indoor luminaires | LED surface-mounted luminaire



#### Area of application

- General indoor illumination
- Corridors, entrance lighting
- Accent lighting, public areas
- Cove lighting
- Shelves, furniture integration or under cabinet lighting
- Seamless linear lighting


#### Product benefits

- Compact dimensions
- Easy to install in two different mounting angles
- Energy savings of up to 45% compared to conventional linear luminaires
- Complete mounting and connecting accessories included
- Connect up to 10 luminaires in series
- On/off switch on luminaire
- Different lengths available
- For seamless lines of light
- Available certificates: CE, CB, TUEV SUED

#### Product features

- Luminaire efficacy: up to 100 lm/W
- Luminous flux: up to 1450lm
- Available with color temperature: 3000K, 4000K
- Beam angle: 140°
- Type of protection: IP20
- White polycarbonate housing and diffuser
- Ambient operating temperature: -20...+40 °C
- Lifetime (L70/B50): up to 30000h
- 3-years guarantee

Technical data



Product description	GTIN (EAN)	Nominal wattage [W]	Nominal voltage [V]	Power factor [λ]	Luminous flux [lm]	Luminaire efficacy [lm/W]	Colour temperature [K]	CRI index [Ra]
Linear LED 300 4W/3000K 230V IP20	4058075000247	4W	230V	> 0.5	400	100	3000K	>80
Linear LED 300 4W/4000K 230V IP20	4058075000261	4W	230V	> 0.5	450	110	4000K	>80
Linear LED 600 8W/3000K 230V IP20	4058075000285	8W	230V	> 0.5	800	100	3000K	>80
Linear LED 600 8W/4000K 230V IP20	4058075000308	8W	230V	> 0.5	800	100	4000K	>80
Linear LED 1200 14W/3000K 230V IP20	4058075000322	14W	230V	> 0.5	1400	100	3000K	>80
Linear LED 1200 14W/4000K 230V IP20	4058075000346	14W	230V	> 0.5	1500	100	4000K	>80

Product description	Beam angle	Rated life time L70 / B50 [h]	Type of protection IP rating	Protection class	Product size l x w or ø [mm]	Height h [mm]	Body colour
Linear LED 300 4W/3000K 230V IP20	140°	30000	20	II	313 x 28	36	white
Linear LED 300 4W/4000K 230V IP20	140°	30000	20	II	313 x 28	36	white
Linear LED 600 8W/3000K 230V IP20	140°	30000	20	II	573 x 28	36	white
Linear LED 600 8W/4000K 230V IP20	140°	30000	20	II	573 x 28	36	white
Linear LED 1200 14W/3000K 230V IP20	140°	30000	20	II	1173 x 28	36	white
Linear LED 1200 14W/4000K 230V IP20	140°	30000	20	II	1173 x 28	36	white

Packaging information

Product description	GTIN (EAN)	Dimensions EAN10 l x w x h [mm]	Gross weight EAN 10 [g]	Volume [dm <sup>3</sup> ]	Packaging unit [Pieces/unit]
Linear LED 300 4W/3000K 230V IP20	4058075000247	520 x 40 x 30	183	0.94	25
Linear LED 300 4W/4000K 230V IP20	4058075000261	520 x 40 x 30	183	0.94	25
Linear LED 600 8W/3000K 230V IP20	4058075000285	780 x 40 x 30	385	1.37	25
Linear LED 600 8W/4000K 230V IP20	4058075000308	780 x 40 x 30	385	1.37	25
Linear LED 1200 14W/3000K 230V IP20	4058075000322	1380 x 40 x 30	558	2.38	25
Linear LED 1200 14W/4000K 230V IP20	4058075000346	1380 x 40 x 30	558	2.38	25

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.