





PCMR32-10-10-A

Ruland PCMR32-10-10-A, 10mm x 10mm Four Beam Coupling, Aluminum, Clamp Style, 31.8mm OD, 38.1mm Length



Description

Ruland PCMR32-10-10-A is a clamp style four beam coupling with 10mm x 10mm bores, 31.8mm OD, and 38.1mm length. It is machined from a single piece of material and feature two sets of two spiral cuts. This gives it higher torque capacity, lower windup, and larger body sizes than single beam couplings. PCMR32-10-10-A is zero-backlash and has a balanced design for reduced vibration at high speeds of up to 6,000 RPM. This four beam spiral coupling is zero-backlash and has a balanced design for reduced vibration at high speeds of up to 6,000 RPM. All hardware is metric and tests beyond DIN 912 12.9 standards for maximum torque capabilities. PCMR32-10-10-A is made from 7075 aluminum for lightweight and low inertia. It is machined from bar stock that is sourced exclusively from North American mills and RoHS3 and REACH compliant. PCMR32-10-10-A is manufactured in our Marlborough, MA factory under strict controls using proprietary processes.

Product Specifications

Bore (B1)	10 mm	Small Bore (B2)	10 mm
Shaft Penetration B1	17.6 mm	Shaft Penetration B2	17.6 mm
Outer Diameter (OD)	31.8 mm	Bore Tolerance	+0.025 mm / -0.000 mm
Length (L)	38.1 mm	Cap Screw	M4
Screw Material	Alloy Steel	Hex Wrench Size	3.0 mm
Screw Finish	Black Oxide	Seating Torque	4.6 Nm
Number of Screws	2 ea	Static Torque	6.78 Nm
Angular Misalignment	3°	Dynamic Torque Non-Reversing	3.39 Nm
Parallel Misalignment	0.38 mm	Dynamic Torque Reversing	1.70 Nm
Axial Motion	0.25 mm	Torsional Stiffness	0.62 Deg/Nm
Moment of Inertia	$9.948 \times 10^{-6} \text{ kg-m}^2$	Maximum Speed	6,000 RPM
Material Specification	7075-T651 Extruded and Drawn Aluminum Bar	Temperature	-40°F to 225°F (-40°C to 107°C)
Finish Specification	Bright	Manufacturer	Ruland Manufacturing
Country of Origin	USA	Weight (lbs.)	0.1450
Recommended Shaft Tolerance	+0.000 mm / -0.013 mm	Tariff Code	8483.60.8000
Note 1	Torque ratings are at maximum misalignment.		
Note 2	Performance ratings are for guidance only. The user must determine suitability for a particular application.		
Note 3	Torque ratings for the couplings are based on the physical limitations/failure point of the machined beams. Under normal/typical conditions the hubs are capable of holding up to the rated torque of the machined beams. In some cases, especially when the smallest standard bores are used or where shafts are undersized, slippage on the shaft is possible below the rated torque of the machined beams. Please consult technical support for more assistance.		
Prop 65	⚠ WARNING This product can expose you to the chemical Ethylene Thiourea, known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov .		

Installation Instructions

1. Align the bores of the PCMR32-10-10-A four beam coupling on the shafts that are to be joined and determine if the misalignment parameters are within the limits of the coupling. (Angular Misalignment: 3°, Parallel Misalignment: 0.38 mm, Axial Motion: 0.25 mm)
2. Fully tighten the M4 screw on one hub to the recommended seating torque of 4.6 Nm using a 3.0 mm hex torque wrench.
3. Before tightening the screws on the second hub, rotate the coupling by hand to allow it to reach its free length.
4. Tighten the screws on the second hub to the recommended seating torque. Make sure the coupling remains axially relaxed and the misalignment angle remains centered along the length of the coupling.

5. The shafts may extend into the relieved portion of the bore as long as it does not exceed the shaft penetration length of 17.6 mm.
-