



Application Tooling > Spare & Wear Tooling



Applicator & Product Style: OCEAN

Features

Other

|                            |       |
|----------------------------|-------|
| Applicator & Product Style | OCEAN |
|----------------------------|-------|

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

|                                               |                                                                                                                               |
|-----------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                     |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                     |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                       |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2025 (247)<br>Candidate List Declared Against: JAN 2025 (247)<br>Does not contain REACH SVHC |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free                                           |
| Solder Process Capability                     | Not applicable for solder process capability                                                                                  |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

TE Part # 7-4151410-7

[OCEAN\\_2.0\\_SPARE\\_PART\\_KIT-042F063O](#)

TE Part # 2836399-2

[OCEAN\\_2.0\\_Applicator-S-042F070F-RSA](#)

TE Part # 2836399-1

[OCEAN\\_2.0\\_Applicator-S-042F070F-RSM](#)

TE Part # 7-2837445-7

[OCEAN\\_2.0\\_SPARE\\_PART\\_KIT-042F062O](#)

TE Part # 7-2836399-7

[OCEAN\\_2.0\\_SPARE\\_PART\\_KIT-042F070F](#)

TE Part # 2837445-2

[OCEAN\\_2.0\\_Applicator-S-042F062OA-RSA](#)

Customers Also Bought

TE Part #103688-9

[10 MTE RCPT HSG SR PLAIN .100](#)

TE Part #1-456408-8

[CRIMPER, WIRE .110 "F"](#)

TE Part #350561-1

[UMNL PIN 24-18 .0126 PTPBR](#)

TE Part #6-87756-7

[MOD IV REC STP INT'L SPEC REEL](#)

TE Part #160344-2

[RING TONGUE 20-16 AWG .025 X .840](#)

TE Part #173977-3

[CT CONN MT REC ASSY 3P](#)

TE Part #3-644043-2

[02P MTA100 CONN ASSY LF](#)

TE Part #3-643815-6

[06P MTA100 CONN ASSY POL RIB](#)

TE Part #53120-1

[SOLIS SP SPD 22-16COM22-18MIL6](#)

TE Part #2119641-1

[FEED CAM, AIR FEED](#)



Documents

Datasheets & Catalog Pages  
CRIMPING WHERE FORM MEETS FUNCTION  
English

Instruction Sheets  
Instruction Sheet (U.S.)  
English