

# Eaton 189732

Catalog Number: 189732

Eaton Moeller series NZM - Molded Case Circuit Breaker.  
Undervoltage release for NZM2/3, configurable relays, 2NO, 1  
early-make auxiliary contact, 1NO, 24AC, Push-in terminals

### General specifications



Product Name	Catalog Number
Eaton Moeller series NZM release	189732
EAN	Product Length/Depth
4015081877270	115 mm
Product Height	Product Width
65 mm	75 mm
Product Weight	Compliances
0.08 kg	IEC
	UL/CSA
	RoHS conform

### Certifications

UL489  
UL listed  
CSA (File No. 22086)  
UL (File No. E140305)  
CSA (Class No. 1437-01)  
UL (Category Control Number DIHS)  
CE marking  
IEC60947  
CSA-C22.2 No. 5-09  
CSA certified

## Product specifications

### Used with

PXR20(25) NZM3(-4)-..X...

PXR20(25) NZM2(-4)-..X...

### Type

Accessory Undervoltage release Undervoltage release with early-make auxiliary contact and two relays

### Special features

For interlock circuits, load-shedding circuits, make-before-break interruption of shunt trip for primary breaker use Instantaneous shut-off NZM breaker at control voltage below 35-70% Us For emergency-stop devices with an emergency-stop button For breaker's signaling commands/different states 2 relays/unit Trip unit config of activation criteria Config by communication/breaker display/front USB port/Eaton Power Xpert Protection Manager Switched off under-voltage trip: accidental contact with breaker's primary contacts is prevented when switched on Auxiliary contact make-before-break activation when manual switching on and off: ~20 ms(NZM2/3)/90 ms(NZM4) For use with electronic trip breakers except NZM...-XR... Under-voltage trip relay modules incompatible with NZM...-XHIV, NZM...-XU..., NZM...-XA. Trip unit controlled relay coil Push-in clamp relay contacts for control wiring. Relays use for controlling remote operator at Us=208-204 V AC Incompatible with PXR10 NZM-AX

### 10.10 Temperature rise

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

### 10.11 Short-circuit rating

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

### 10.12 Electromagnetic compatibility

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

### 10.13 Mechanical function

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

### 10.2.2 Corrosion resistance

Meets the product standard's requirements.

### 10.2.3.1 Verification of thermal stability of enclosures

Meets the product standard's requirements.

## Resources

### Brochures

[eaton-feerum-the-whole-grain-solution-success-story-en-us.pdf](#)

[eaton-digital-nzm-brochure-br013003en-en-us.pdf](#)

### Catalogs

[eaton-digital-nzm-catalog-ca013003en-en-us.pdf](#)

### Declarations of conformity

[DA-DC-03\\_NZM2](#)

### Installation instructions

[eaton-circuit-breaker-voltage-release-nzm2-3-il012141zu.pdf](#)

### Installation videos

[Introduction of the new digital circuit breaker NZM](#)

[The new digital NZM Range](#)

### Technical data sheets

[eaton-nzm-technical-information-sheet](#)

### Wiring diagrams

[eaton-circuit-breaker-nzm-mccb-wiring-diagram-002.eps](#)

[eaton-circuit-breaker-nzm-mccb-wiring-diagram.eps](#)

#### 10.2.3.2 Verification of resistance of insulating materials to normal heat

Meets the product standard's requirements.

#### 10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects

Meets the product standard's requirements.

#### 10.2.4 Resistance to ultra-violet (UV) radiation

Meets the product standard's requirements.

#### 10.2.5 Lifting

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.2.6 Mechanical impact

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.2.7 Inscriptions

Meets the product standard's requirements.

#### 10.3 Degree of protection of assemblies

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.4 Clearances and creepage distances

Meets the product standard's requirements.

#### 10.5 Protection against electric shock

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.6 Incorporation of switching devices and components

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.7 Internal electrical circuits and connections

Is the panel builder's responsibility.

#### 10.8 Connections for external conductors

Is the panel builder's responsibility.

#### 10.9.2 Power-frequency electric strength

Is the panel builder's responsibility.

#### 10.9.3 Impulse withstand voltage

Is the panel builder's responsibility.

#### 10.9.4 Testing of enclosures made of insulating material

Is the panel builder's responsibility.

#### Electric connection type

Screw connection

Fitted with:

Early-make auxiliary contact and 2 relays

Frame

NZM2/3

Pollution degree

2

Minimum command time - max

15 ms

Minimum command time - min

10 ms

Number of contacts (normally open contacts)

3

Number of relays

2

Reaction time

19 ms

Pick-up power consumption at AC (undervoltage release)

1.5 VA

Pick-up power consumption at DC (undervoltage release)

0.8 W

Voltage tolerance - max

1.1

Voltage tolerance - min

.85

Rated control supply voltage (Us) at AC, 50 Hz - max

24 V

Rated control supply voltage (Us) at AC, 50 Hz - min

24 V

Rated control supply voltage (Us) at AC, 60 Hz - max

24 V

Rated control supply voltage (Us) at AC, 60 Hz - min

24 V

Rated insulation voltage (Ui)

250 V

Strip length

8 mm (relay contact connection)

Switching capacity (reference value) - min

0.1 mA / 0.1 VDC

Rated impulse withstand voltage (Uimp)

4 kV AC

Suitable for

Motor safety switch

Off-load switch

Connection type

With push in terminal

Voltage type

AC

Drop-out voltage of undervoltage release AC/DC - max

0.7 x Us

Overvoltage category

II

Rated operational current

1 A (24 V AC-1, relay contacts)

1 A (24 V DC-1, relay contacts)

1 A (110 V AC-1, relay contacts)

1 A (230 V AC-1, relay contacts)

Drop-out voltage of undervoltage release AC/DC - min

0.35 x Us

Power consumption

1.5 VA (sealing AC)

0.8 W (sealing DC)

Rated control supply voltage (Us) at DC - max

0 V

Rated control supply voltage (Us) at DC - min

0 V

Number of contacts (normally closed contacts)

0

Number of contacts (change-over contacts)

0

Undelayed short-circuit release - min

0 A

Undelayed short-circuit release - max

0 A

Terminal capacity (stranded cable)

0.25 mm<sup>2</sup> - 0.75 mm<sup>2</sup> (1x) for undervoltage release

0.25 mm<sup>2</sup> - 1.5 mm<sup>2</sup> (1x) for undervoltage release with insulated

end sleeve in accordance with DIN46224 / 4

0.25 mm<sup>2</sup> - 0.75 mm<sup>2</sup> (1x) for undervoltage release with  
uninsulated end sleeve in accordance with DIN46228 / 1

0.25 mm<sup>2</sup> - 1.5 mm<sup>2</sup> (1x) at shunt release

24 - 16 AWG (1x) for undervoltage release

0.25 mm<sup>2</sup> - 1.5 mm<sup>2</sup> (1x) for undervoltage release

24 - 16 AWG (1x) at shunt release

#### Terminal capacity (solid cable)

0.2 mm<sup>2</sup> - 1.5 mm<sup>2</sup> (1x) for undervoltage release

0.2 mm<sup>2</sup> - 1.5 mm<sup>2</sup> (1x) at shunt release

#### Rated control voltage (relay contacts)

24 V AC

24 V DC

240 V AC



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are  
property of their respective  
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)