



Connectors > Terminal Blocks & Strips > Terminal Block & Strip Accessories > Terminal Block & Strip Conducting Accessories



Conducting Accessory Type: **Jumper Bar**

Number of Poles: **4**

PCB Mount Retention Type: **Screw**

Primary Product Color: **Orange**

Product Spacing: **16 mm [.63 in]**

Features

Product Type Features

Conducting Accessory Type	Jumper Bar
---------------------------	------------

Configuration Features

Number of Poles	4
-----------------	---

Electrical Characteristics

Power Loss	4 W
Dielectric Withstanding Voltage (Max)	2200 V
Operating Voltage Rating (UL & CSA) (Max) - Main Circuit	600 V
Impulse Withstanding Voltage Rating (IEC)	8000 V
Current Rating (IEC)	125 A
Current Rating (CSA)	150 A
Voltage Rating (IEC)	1000 V
Voltage Rating (CSA)	600 V
Short-Time Withstanding Current Rating @ 1s	4200 A

Body Features

--	--



Plastic & Resin Material Type	Polyamide
Product Weight	22 g[.776 oz]
Primary Product Color	Orange

Contact Features

Contact Current Rating (Max)	125 A
------------------------------	-------

Mechanical Attachment

Tightening Torque	10.6 in-lbs
PCB Mount Retention Type	Screw

Dimensions

Product Width	16 mm[.629 in]
Product Depth	23.4 mm[.921 in]
Product Height	59.5 mm[2.343 in]
Tool Size	5.5 mm[.217 in]
Product Spacing	16 mm[.63 in]

Usage Conditions

Installation Temperature Range	-5 – 40 °C[23 – 104 °F]
Operating Temperature Range	-55 – 110 °C[-67 – 230 °F]

Industry Standards

IP Rating	IP20
-----------	------

Product Compliance

For compliance documentation, visit the product page on TE.com>







EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1SNA400195R2200 M35/16	 TE Part # 1SNK516011R0000 ZS50	 TE Part # 1SNA400194R2100 M35/16	 TE Part # 1SNK516060R0000 ZS50-YL
 TE Part # 1SNK516030R0000 ZS35-OR	 TE Part # 1SNK516063R0000 ZS50-RD	 TE Part # 1SNK516021R0000 ZS50-BL	 TE Part # 1SNA400196R2300 M35/16
 TE Part # 1SNA115124R0700 M35/16	 TE Part # 1SNK516064R0000 ZS50-BK	 TE Part # 1SNK516151R0000 ZS50-PE	TE Part # 1SNL516010R0000 C35/16

1SNK916304R0000

Jumper Bar, 4 Pole, Orange, 16 mm [.63 in] Spacing, -55 – 110 °C [-67 – 230 °F], ENTRELEC SNK



TE Part # 1SNK516010R0000
ZS35

TE Part # 1SNA125124R0100
M35/16.N

TE Part # 1SNK516020R0000
ZS35-BL

TE Part # 1SNA105124R1600
M35/16

TE Part # 1SNK900101R0000
CS

Also in the Series | ENTRELEC SNK

Modular Terminal Blocks(319)

Terminal Block & Strip Conducting Accessories(67)

Terminal Block & Strip Insulating Accessories(31)

Customers Also Bought

TE Part #1SNK516020R0000
ZS35-BL

TE Part #1SNK516062R0000
ZS35-BK

TE Part #1SNK516150R0000
ZS35-PE

TE Part #5111448-1
010 UNIV I/O 30DP SLOT

TE Part #1SNK505211R0000
ZS4-D1

TE Part #1SNK516010R0000
ZS35

TE Part #1SNK705210R0000
ZK2.5-D2

TE Part #1SNK900103R0000
CS-R1

1SNK916304R0000

Jumper Bar, 4 Pole, Orange, 16 mm [.63 in] Spacing, -55 – 110 °C [-67 – 230 °F],
ENTRELEC SNK



Documents

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1SNK916304R0000_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1SNK916304R0000_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1SNK916304R0000_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Catalogue - ENTRELEC terminal-blocks-sna-series](#)

English

JB16-4

English

[SNK SERIES TERMINAL BLOCKS](#)

English

[ENTRELEC Terminal Blocks Catalogue \(RUS\)](#)

[ENTRELEC Terminal Block - Master Catalog](#)

[ENTRELEC Terminal Block - Master Catalog](#)

English