



MTA 156

TE Internal #: 3-641435-4  
Connector Assembly, Plug, Insulation Displacement (IDC), Wire-to-Wire, Tin (Sn), UL 94V-2, MTA 156, Rectangular Wire & Cable  
Connectors & Housings

[View on TE.com >](#)

Connectors > Rectangular Connectors > Standard Rectangular Connectors



Connector Product Type: **Connector Assembly**  
Connector & Housing Type: **Plug**  
Mating Alignment: **With**  
Mating Alignment Type: **Polarization**  
Mating Retention: **With**

Features

Product Type Features

|                                    |                    |
|------------------------------------|--------------------|
| Compatible With Discrete Wire Type | Stranded           |
| Connector Product Type             | Connector Assembly |
| Connector & Housing Type           | Plug               |
| Connector System                   | Wire-to-Wire       |
| Sealable                           | No                 |
| Connector & Contact Terminates To  | Wire & Cable       |

Configuration Features

|                           |   |
|---------------------------|---|
| Number of Power Positions | 4 |
| Number of Positions       | 4 |
| Number of Rows            | 1 |

Electrical Characteristics

|                   |         |
|-------------------|---------|
| Operating Voltage | 600 VAC |
|-------------------|---------|

Body Features

|                  |     |
|------------------|-----|
| Cable Exit Angle | 90° |
|------------------|-----|



|                                                 |                               |
|-------------------------------------------------|-------------------------------|
| Primary Product Color                           | Orange                        |
| Contact Features                                |                               |
| Contact Underplating Material                   | Nickel                        |
| Contact Underplating Material Thickness         | 50 µm[1.27 µin]               |
| Wire Contact Termination Area Plating Material  | Tin                           |
| Contact Mating Area Plating Material Thickness  | 2.03 µm[80 µin]               |
| Contact Layout                                  | Inline                        |
| Contact Base Material                           | Copper Alloy                  |
| Wire Contact Termination Area Plating Thickness | 2.03 µm[80 µin]               |
| Contact Type                                    | Pin                           |
| Contact Mating Area Plating Material Finish     | Matte                         |
| Contact Mating Area Plating Material            | Tin (Sn)                      |
| Contact Retention Within Housing                | With                          |
| Contact Current Rating (Max)                    | 7 A                           |
| Termination Features                            |                               |
| Termination Method to Wire & Cable              | Insulation Displacement (IDC) |
| Mechanical Attachment                           |                               |
| Strain Relief                                   | With                          |
| Panel Mount Feature                             | Without                       |
| Contact Retention Type Within Housing           | Locking Lance                 |
| Mating Alignment                                | With                          |
| Mating Alignment Type                           | Polarization                  |
| Mating Retention                                | With                          |
| Mating Retention Type                           | Latch                         |
| Connector Mounting Type                         | Cable Mount (Free-Hanging)    |
| Housing Features                                |                               |
| Housing Material                                | Nylon                         |
| Wire & Cable IDC Installation Type              | Closed End                    |
| Centerline (Pitch)                              | 3.96 mm[.156 in]              |
| Dimensions                                      |                               |
| Compatible Insulation Diameter Range            | 2.41 mm[.095 in]              |
| Connector Height                                | 12.37 mm                      |



|           |        |
|-----------|--------|
| Wire Size | 18 AWG |
|-----------|--------|

|                  |          |
|------------------|----------|
| Connector Length | 19.81 mm |
|------------------|----------|

Usage Conditions

|                             |                            |
|-----------------------------|----------------------------|
| Operating Temperature Range | -55 – 105 °C[-67 – 221 °F] |
|-----------------------------|----------------------------|

Operation/Application

|                     |       |
|---------------------|-------|
| Circuit Application | Power |
|---------------------|-------|

Industry Standards

|                                           |         |
|-------------------------------------------|---------|
| Compatible With Agency/Standards Products | CSA, UL |
|-------------------------------------------|---------|

|           |            |
|-----------|------------|
| UL Rating | Recognized |
|-----------|------------|

|                                             |           |
|---------------------------------------------|-----------|
| Compatible With Approved Standards Products | UL E28476 |
|---------------------------------------------|-----------|

|            |                    |
|------------|--------------------|
| CSA Rating | Certified, LR 7189 |
|------------|--------------------|

|                  |                               |
|------------------|-------------------------------|
| Glow Wire Rating | Standard Part - Not Glow Wire |
|------------------|-------------------------------|

|                        |          |
|------------------------|----------|
| UL Flammability Rating | UL 94V-2 |
|------------------------|----------|

Packaging Features

|                    |      |
|--------------------|------|
| Packaging Quantity | 1500 |
|--------------------|------|

|                  |         |
|------------------|---------|
| Packaging Method | Package |
|------------------|---------|

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

|                              |           |
|------------------------------|-----------|
| EU RoHS Directive 2011/65/EU | Compliant |
|------------------------------|-----------|

|                             |           |
|-----------------------------|-----------|
| EU ELV Directive 2000/53/EC | Compliant |
|-----------------------------|-----------|

|                                               |                                         |
|-----------------------------------------------|-----------------------------------------|
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
|-----------------------------------------------|-----------------------------------------|

|                                        |                                                                                                                                |
|----------------------------------------|--------------------------------------------------------------------------------------------------------------------------------|
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JAN 2025 (247)<br>Candidate List Declared Against: JUNE 2024 (241)<br>Does not contain REACH SVHC |
|----------------------------------------|--------------------------------------------------------------------------------------------------------------------------------|

|                 |                                                                                     |
|-----------------|-------------------------------------------------------------------------------------|
| Halogen Content | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free |
|-----------------|-------------------------------------------------------------------------------------|

|                           |                                              |
|---------------------------|----------------------------------------------|
| Solder Process Capability | Not applicable for solder process capability |
|---------------------------|----------------------------------------------|

Product Compliance Disclaimer







This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these






limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

|                                                                                                                                                    |                                                                                                                                                     |                                                                                                                                                      |                                                                                                                                                         |
|----------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------|
|  <p>TE Part # 3-640600-4<br/>04P MTA156 CONN ASSY 20AWG LF</p>   |  <p>TE Part # 3-640427-4<br/>04P MTA156 CONN ASSY 20AWG YEL</p>  |  <p>TE Part # 770598-4<br/>04P SL156 HSG W/O LCK RAMP</p>        |  <p>TE Part # 3-644860-4<br/>04P MTA156 CONN ASSY 18AWG LF</p>      |
|  <p>TE Part # 3-640428-4<br/>04P MTA156 CONN ASSY 22AWG RED</p> |  <p>TE Part # 58074-1<br/>MTA 50/100/156 MANUAL TOOL FRAME</p>  |  <p>TE Part # 3-640429-4<br/>04P MTA156 CONN ASSY 24AWG WHT</p> |  <p>TE Part # 3-640602-4<br/>04P MTA156 CONN ASSY 24AWG LF</p>     |
|  <p>TE Part # 640643-4<br/>04P MTA156 COVER F/T</p>             |  <p>TE Part # 643071-4<br/>04P MTA156 FD-THRU COVER</p>         |  <p>TE Part # 640551-4<br/>04P MTA156 COVER</p>                 |  <p>TE Part # 58082-1<br/>MTA 156 CRIMP HEAD PRODUCTION POSTED</p> |
|  <p>TE Part # 643067-4<br/>04P MTA156 CMOLDED COVER</p>         |  <p>TE Part # 3-640599-4<br/>04P MTA156 CONN ASSY 18AWG ORA</p> |  <p>TE Part # 3-640426-4<br/>04P MTA156 CONN ASSY 18AWG ORA</p> |  <p>TE Part # 3-640430-4<br/>04P MTA156 CONN ASSY 26AWG BLU</p>    |







TE Part # 3-640601-4  
04P MTA156 CONN ASSY 22AWG LF



TE Part # CAT-103156-WBHSM  
Receptacle Housing: Wire-to-Board, with Mating Alignment, SL156


Also in the Series | MTA 156



Connector Caps & Covers(89)




Connector Contacts(4)



Connector Hardware(2)



Insertion & Extraction Tools(1)




PCB Headers & Receptacles(677)



Power Contacts(3)



Rectangular Power Connectors(1178)



Wire-to-Board Headers & Receptacles (677)


Customers Also Bought



TE Part #3-1123722-6  
3.96 EP PLUG HSG 6P(BLUE)



TE Part #926308-1  
8P UNIV.M-N-L.CAP



TE Part #626328-2  
FF 250 RECEPTACLE 4.0-6.0 MM2 TPBR




TE Part #640051-1  
RING TONGUE .164 18-14 AWG SST




TE Part #3-641435-9  
09P MTA156 CONN ASSY ORNG



TE Part #3-640426-4  
04P MTA156 CONN ASSY 18AWG ORA



TE Part #880646-5  
PL REC 0.5-1.0 MM2 0.40 X 52.32 PTPBR



TE Part #925552-1  
AM WIRE PIN 20-17 .013 BR



Documents

Product Drawings

04P MTA156 CONN ASSY ORNG

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_3-641435-4\_K.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_3-641435-4\_K.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_3-641435-4\_K.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Agency Approvals

UL

English

UL

English