



Part Number : [1200680190](#)

Product Description : Micro-Change (M12) In-Line Splitter, 4 Pole, 1 x 4-Pole Male (Straight) to 2 x 3-Pole Female (Straight), 22 AWG PVC Cable, 1.0m Length

Series Number : 120068

Status : Active

Product Category : Industrial Tees and Splitters

Engineering Number : 884A30K03M010



Documents & Resources

Drawings

[1200680190 sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

UKCA - Declaration of Conformity

Part Details

General

Status	Active
Category	Industrial Tees and Splitters
Series	120068
Description	Micro-Change (M12) In-Line Splitter, 4 Pole, 1 x 4-Pole Male (Straight) to 2 x 3-Pole Female (Straight), 22 AWG PVC Cable, 1.0m Length
IP Rating	IP67
Product Name	Micro-Change (M12)
Type	Splitter - In-line
UPC	78678845021

Agency

CSA	LR6837
UL	E152210

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC/DC

Physical

Color - Cable Jacket	Yellow
Drop Connector	N/A
Drop Gender	N/A
Keyway	Single
LED Indicator	None

Left Trunk Connector	Micro-Change (M12)
Left Trunk Gender	Male
Leg 1 Length	1.0m
Leg 2 Length	1.0m
Material - Cable Jacket	TPE
Material - Connector Body	TPE
Material - Coupling Nut	Nickel-plated Brass
Net Weight	232.828/g
Poles	3 Female/4 Male
Right Trunk Connector	Micro-Change (M12)
Right Trunk Gender	Female
Temperature Range - Operating	-30°C TO +80°C