

553443-3 ✓ ACTIVE

CHAMP


TE Internal #: 553443-3

36 Position D-Shaped Connector, Receptacle, Cable-to-Board, Board Mount, 2.16 mm [.085 in] Centerline, Printed Circuit Board, Signal

[View on TE.com >](#)



Connectors > D-Shaped Connectors > D-Sub Receptacle Assembly: Vertical, Action Pin, 2.16mm



Number of Positions: **36**

Connector & Housing Type: **Receptacle**

Connector System: **Cable-to-Board**

Connector Mounting Type: **Board Mount**

Centerline (Pitch): **2.16 mm [.085 in]**

[All D-Sub Receptacle Assembly: Vertical, Action Pin, 2.16mm \(10\)](#)

Features

Product Type Features

Connector & Housing Type	Receptacle
Connector System	Cable-to-Board
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Positions	36
Number of Rows	2
PCB Mount Orientation	Vertical

Body Features

Primary Product Color	Black
Connector Profile	Standard

Contact Features

Contact Mating Area Plating Material Thickness	.76 µm
Contact Mating Area Plating Material	Gold (Au)
Contact Base Material	Copper Alloy
Contact Shape & Form	Spring
Contact Current Rating (Max)	3 A
Contact Options	Installed



Termination Features

Rectangular Termination Post & Tail Width	.66 mm[.026 in]
Rectangular Termination Post & Tail Thickness	.48 mm[.018 in]
Termination Method to PCB	Through Hole - Press-Fit
Termination Post & Tail Length	4.58 mm

Mechanical Attachment

Panel Attachment Style	Rear Mount
Mounting Hole Diameter	3.3 mm
Connector Mounting Type	Board Mount
PCB Mount Retention	With
PCB Mount Retention Type	Action/Compliant Tail
Mating Retention	Without

Housing Features

Housing Material	Polyester
Centerline (Pitch)	2.16 mm[.085 in]

Dimensions

PCB Thickness (Recommended)	1.57 – 3.18 mm[.062 – .125 in]
Row-to-Row Spacing	4.06 mm[.16 in]

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Shielded	No
Circuit Application	Signal

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Quantity	30
Packaging Method	Tray

Product Compliance

For compliance documentation, visit the product page on [TE.com](https://www.te.com)>




EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUL 2019 (201) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 5552243-1
ASSY, PLUG, 64 POS, VERT MTG


Customers Also Bought



TE Part #536475-1
096 EURO TYPE C PIN MFBL ASSY



TE Part #1589451-8
USS015B2 = STRIP CON



TE Part #1589700-5
SSM025B2H = SMT CONN



TE Part #3-1658548-9
FPH-2301G=FLXPAC HDR P 23 RA LF




TE Part #1-2842236-6
16P,2MM,SHRD HDR,DRVT,0.1AU,TB



TE Part #1589336-1
335-0005 = HARDWARE



TE Part #8-435470-1
DIP SW ASSY-BLK EXT ACT-4POS



TE Part #1589567-5
STM06511242B44 = SMT CONN

Documents

Product Drawings

[ASSY RCPT,ACTION PIN,CHAMP-LOK](#)

English

CAD Files

Customer View Model

[ENG_CVM_CVM_553443-3_Z.2d_dxf.zip](#)

English

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_553443-3_Z.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_553443-3_Z.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English

[Application Specification](#)

English

[CHAMP Action Pin Connectors](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

[AMP CHAMP ACTION PIN Connectors \(Preloaded\)](#)

English

Agency Approvals

[CSA Certificate](#)

English

553443-3

36 Position D-Shaped Connector, Receptacle, Cable-to-Board, Board Mount, 2.16 mm [.085 in] Centerline, Printed Circuit Board, Signal

