

## FEATURES

- Nitrile rubber O-Ring cord
- Diameter of 2.4 mm
- Length of 8.5 m
- Minimum operating temperature of -30°C (special consideration is required for use below this temperature)
- Maximum operating temperature of +120°C (continuous) or +150°C (intermittent)

## RS PRO Nitrile Rubber O-Ring Cord, 2.4mm Diam., 8.5m Long

RS Stock No.: 159-1484



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

### Product Description

This nitrile rubber O-Ring cord from RS PRO gives you a quick and reliable way to seal machine components. At 2.4 mm in diameter and 8.5 m in length, it's easy to cut the cord to different lengths to produce multiple seals of different sizes.

As nitrile rubber can withstand extreme temperatures, you can use this cord at temperatures as low as -30°C and as high as +120°C. It can also hold up at intermittent high temperatures of up to +150°C. The cord works by creating a reliable vacuum between surfaces. It's quick and easy to make a circular, gasket that guards against air or fluid leaks in various types of machinery and equipment.

### General Specifications

Material	Nitrile Rubber
----------	----------------

### Mechanical Specifications

Diameter	2.4mm
Length	8.5m

### Operation Environment Specifications

Operating Temperature Range	-30°C to 120°C
-----------------------------	----------------

### Approvals

Compliance/Certifications	EN61340
---------------------------	---------

