

ECO SST CL B 20 W 240 V E14

CLASSIC ECO SUPERSTAR B | Halogen lamps, classic mini-candle shape



Areas of application

- General illumination
- Dining table lighting
- Entrance lighting
- Restaurants, hotels and similar prestigious applications

Product benefits

- Simple direct replacement for conventional incandescent lamps
- The same pleasant quality of light as that of an incandescent lamp
- Instant 100 % light, no warm-up time
- Contains no mercury
- UV filter

Product features

- Average life: 2,000 h
- 100 % dimmable
- Perfect color rendering ($R_a : 100$)



Product datasheet

Technical data

Electrical data

Nominal wattage	20.00 W
Nominal voltage	240 V
Rated wattage	20.00 W
Claimed equiv. conventional lamp power	25 W
Power factor λ	1.00
Energy consumption	20 kWh/1000h


Photometrical data

Nominal luminous flux	235 lm
Color temperature	2700 K
Light color as per EN 12464-1	Warm White
Rated luminous flux	235 lm
Color rendering index Ra	100
Lumen main.fact.at end of nom.life time	0.80

Light technical data

Starting time	0.0 s
Warm-up time (60 %)	0.00 s

Dimensions & weight



Product line drawing

Diameter	35.0 mm
Overall length	104.0 mm
Length	97.0 mm

Product datasheet

Light center length (LCL)	67.0 mm
Outer bulb	B35

Colors & materials


Lamp mercury content	0.0 mg
Mercury-free	Yes

Lifespan

Nominal lamp life time	2000 h
Rated lamp life time	2000 h
Number of switching cycles	50000 ¹⁾

¹⁾ At 1 min on / 3 min off

Additional product data



Spectral power distribution

Base (standard designation)	E14
-----------------------------	-----

Capabilities

Burning position	Any
Dimmable	Yes

Certificates & standards

Product datasheet

Energy efficiency class	D
--------------------------------	---

Country specific categorizations

ILCOS	HSGSB/C/UB-20-240-E14-67
Order reference	64541 B ECO20W2

Country specific information

Product code	METEL code	SEG-No.	STK number	UK Org
4008321934307	OSRH64541BES240V	-	4730004	-

Product datasheet

Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (height x width x length)	Volume	Gross weight
4008321934307	ECO SST CL B 20 W 240 V E14	Folding carton box 1	36 mm x 36 mm x 102 mm	0.13 dm ³	20.00 g
4008321934451	ECO SST CL B 20 W 240 V E14	Shipping carton box 20	152 mm x 110 mm x 184 mm	3.08 dm ³	570.00 g
4052899196629	ECO SST CL B 20 W 240 V E14	Bundle 3	- x - x -		
4052899196636	ECO SST CL B 20 W 240 V E14	Shipping carton box 5808	852 mm x 799 mm x 1199 mm	816.22 dm ³	144642.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

References / Links

For an extended range for non-EU countries see

▶ www.osram.com

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.