



Multi Purpose



Light Duty

## Antimicrobial Protection for High-Traffic Touch Points

- The only industrial glove designed with Ionic+™, an EPA-registered antimicrobial technology
- Leverages the antimicrobial power of silver to protect gloves from microbial impacts
- All day comfort with high dexterity in a light-weight breathable design
- Self-Sanitizing 360° antimicrobial protection of both the liner and coating



### Industries

- Manufacturing
- Logistics
- Transportation
- Recycling and Waste Disposal
- Hospitality
- Housekeeping
- Sales

### Applications

- Assembly line
- Packaging
- Delivery of finished equipment
- Event Management/Waitstaff
- Cleaning/Maintenance/Repair
- Drivers/Operators/Inspectors
- Shared surfaces/tools/touchscreens
- Cashiers/Clerks/Money Handling

# HyFlex®

ADVANCED MECHANICAL PROTECTION

## 11-100

With Antimicrobial Technology\*

### Key Features

- The only industrial glove designed with Ionic+™, an EPA-registered antimicrobial technology - EPA Registration #70927-6
- Self-Sanitizing 360° antimicrobial protection of both the liner and coating
- Ionic+™ is permanent and lasts the life of the product
- Touchscreen compatible for use with a wide range of devices
- Compliant with EU Biocides Regulation 528/2012 for treated articles
- Designed so coating does not inhibit antimicrobial action
- Protects glove from bacterial-related odor, stain, and fabric degradation

### Vulcanization Chemical Accelerators

- Natural rubber proteins

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

### Performance Standards & Regulatory Compliance

#### REACH Compliant



### Technologies



ionic+ Antimicrobial Technology



Touchscreen Compatible



**ZONZ™**  
Comfort Fit Technology

### Specifications

BRAND   STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COLOR	PACKAGE
HyFlex® 11-100	<b>Finishing:</b> Palm Coated <b>Coating Material:</b> Foam Nitrile <b>Liner Material:</b> Conductive Fiber, Nylon, Ionic+® active antimicrobial liner <b>Cuff Style:</b> Knitwrist	15	6, 7, 8, 9, 10	204-274 mm 8.03-10.78 inches	Grey	<ul style="list-style-type: none"> <li>• 12 pairs in a bag; 12 bags in a carton</li> </ul>

### For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 210  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Australia

Ansell Limited  
Level 3,678 Victoria Street,  
Richmond, Vic, 3121  
Australia  
T: +61 1800 337 041  
F: +61 1800 803 578

#### Asia Pacific Region

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
Prima 6, Prima Avenue  
Block 3512, Jaijan Teknokrat 6  
T: +603 8310 6688  
F: +603 8310 6699

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306,  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

#### Canada

Ansell Canada  
105 Lauder  
Cowansville, QC J2K 2K8  
Canada  
T: +1 800 363 8340  
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2021 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

