



NU310EW
Single-Row Cylindrical Roller Bearings

Boundary Dimensions

d	50	mm	Bore diameter
D	110	mm	Outside diameter
B	27	mm	Width
FW	65	mm	Raceway diameter of inner ring
r (min.)	2	mm	Chamfer dimension
r1 (min.)	2	mm	Chamfer dimension

Basic Load Ratings

Cr	135000	N	Basic dynamic load rating
C0r	113000	N	Basic static load rating

Speeds

Thermal Speed Rating (Oil-bath)	6700	min-1	Oil-bath lubrication subject to conditions outlined in ISO 15312
Mechanical (forced-circulation oil)	10000	min-1	Properly designed and controlled forced-circulation oil lubrication
Grease	5000	min-1	Grease lubrication
Oil (Oil-bath)	6000	min-1	Oil-bath lubrication

Abutment and Fillet Dimensions

da (min.)	59	mm	Diameter of shaft abutment
db (min.)	59	mm	Diameter of shaft / spacer sleeve abutment
db (max.)	63	mm	Diameter of shaft / spacer sleeve abutment
dc (min.)	67	mm	Diameter of shaft abutment
dd (min.)	73	mm	Diameter of shaft abutment
Da (max.)	101	mm	Diameter of housing abutment
ra (max.)	2	mm	Radius of shaft or housing fillet
rb (max.)	2	mm	Radius of shaft or housing fillet

Mass

Mass approx.	1149	kg	Mass approx.
--------------	------	----	--------------

