

# Eaton EBH00O3TS5

Catalog Number: EBH00O3TS5

Eaton Bussmann series low voltage NH fuse base, Switch disconnecter, low voltage, 160 A, AC 690 V, NH00, AC23B, 3P, IEC, panel mounting, for connection of round conductors



### General specifications

Product Name	Catalog Number
Eaton Bussmann series low voltage NH fuse base	EBH00O3TS5
	EAN
	5027590335164
Product Length/Depth	Product Height
110 mm	200 mm
Product Width	Product Weight
95 mm	653 g
Compliances	Certifications
CE	IEC/EN 60947-1
	IEC 60947-3

## Product specifications

### Type

Fuse accessory

### Application

Motor control centres, distribution boards, Cable distribution cabinets

### Amperage Rating

160 A

### Rated operational power at AC-23A, 400 V, 50 Hz

0.064 kW

### Rated permanent current (Iu)

160 A

### Rated uninterrupted current (Iu)

160 A

### Conditioned rated short-circuit current Iq

0.08 kA

### With error protection

No

### Number of poles

Three-pole

### Rated operation power at AC-23, 400 V

0.064 kW

### Rated short-time withstand current (Icw)

80 A

### Electrical connection type of main circuit

Cable clamp

### Actuator position

Front side

### Actuator type

Cover grip

### Construction size

NH00

### Fuse shape

Horizontal

### Suitable for

Front mounting

NH00

## Resources

### Catalogs

[eaton-product-overview-for-machinery-catalogue-ca08103003zen-en-us.pdf](#)

[CA134002EN](#)

### Declarations of conformity

[CE fuse switch disconnectors, EBC, EBV and EBH series](#)

[UKCA fuse switch disconnectors, EBC, EBV and EBH series](#)

### Technical data sheets

[10275 EBV Vertical fuse switch-disconnector](#)

### Technical service bulletins

[10293 EBH Horizontal switch-disconnector](#)

Suitable for fuses

NH00

Cable entry type

Other

Mounting method

DIN rail

60 mm busbar mounting

Voltage rating

690

Degree of protection (front side)

IP30

Electrical connection type

Cable clamp

Rated operating voltage (Ue) at AC - max

690 V



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.  
All other trademarks are property of their respective owners.



Eaton.com/socialmedia