


Geberit Mapress Copper bend with plain end



Example image



APPLICATION PURPOSES

- For cold and hot potable water
- For cooling and heating water without antifreeze agent
- For cooling and heating water with antifreeze agent
- For district heating water ≤ 120 °C
- For service water and process water
- For compressed air (oil purity class 0–3)

- For negative pressure
- For inert gases (e.g. nitrogen)
- For technical building systems, industry and shipbuilding

- Seal ring made of CIIR, black, up to $\varnothing \leq 54$ mm
- Seal ring made of EPDM, black, from $\varnothing > 54$ mm
- Pressing socket with transparent protection plug

CHARACTERISTICS

- Pressing indicator
- Leaky if unpressed up to $\varnothing \leq 54$ mm

TECHNICAL DATA

Product material	Cu-DHP copper CW024A (EN 1412)
------------------	--------------------------------

Art. no.	DN	d, $\varnothing$ mm	arc °	L cm	H cm	Z cm
60701	10	12	45	2.6	3.5	0.9
60702	12	15	45	2.8	3.8	0.8
60703	15	18	45	2.9	3.9	0.9
60704	20	22	45	3.2	4.4	1.1
60705	25	28	45	3.7	4.5	1.4

Art. no.	DN	d _ø mm	arc °	L cm	H cm	Z cm
60706	32	35	45	4	4.9	1.4
60707	40	42	45	4.7	5.7	1.7
60708	50	54	45	5.7	6.8	2.2
60710	65	66.7	45	9.2	10.1	4.2
60711	65	76.1	45	10.3	11.1	5
60712	80	88.9	45	11.7	12.8	5.7
60713	100	108	45	14.3	15.8	6.8
60301	10	12	90	3.1	4.5	1.4
60302	12	15	90	3.8	5.1	1.8
60303	15	18	90	4.2	5.3	2.2
60304	20	22	90	4.7	6	2.6
60305	25	28	90	5.7	6.5	3.4
60306	32	35	90	6.5	7.4	3.9

Art. no.	DN	d _ø mm	arc °	L cm	H cm	Z cm
60307	40	42	90	7.6	8.6	4.6
60308	50	54	90	9.5	10.6	6
60310	65	66.7	90	14.1	15	9.1
60311	65	76.1	90	15.7	16.6	10.4
60312	80	88.9	90	18.5	19.5	12.5
60313	100	108	90	22.9	24	15.4