

Eaton 269187

Catalog Number: 269187

Eaton Moeller series NZM - Molded Case Circuit Breaker. Circuit-breaker, 3p, 200A, N2-AF200-NA

General specifications



Product Name

Eaton Moeller series NZM molded case
circuit breaker thermo-magnetic

Catalog Number

269187

EAN

4015082691875

Product Length/Depth

149 mm

Product Height

195 mm

Product Width

105 mm

Product Weight

2.399 kg

Compliances

RoHS conform

Certifications

Specially designed for North America
UL (Category Control Number DIVQ)
CSA-C22.2 No. 5-09
IEC/EN 60947
CSA (File No. 22086)
CSA (Class No. 1432-01)
UL 489
CE marking
UL/CSA
IEC
IEC 60947-2
UL listed
UL (File No. E31593)
CSA certified

Product specifications

Type

Circuit breaker

Special features

Maximum back-up fuse, if the expected short-circuit currents at the installation location exceed the switching capacity of the circuit breaker (Rated short-circuit breaking capacity I_{cn})
Rated current = rated uninterrupted current: 200 A
Switches conform to UL/CSA as well as the IEC regulations. IEC switching performance values are contained on the rating plate.
Fixed overload releases Ir

Application

Branch circuits, feeder circuits
Use in unearthed supply systems at 690 V

Amperage Rating

200 A

Voltage rating

690 V - 690 V

Circuit breaker frame type

NZM2

Features

Protection unit
Motor drive optional

10.10 Temperature rise

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

10.11 Short-circuit rating

Is the panel builder's responsibility. The specifications for the

Resources

Brochures

[eaton-digital-nzm-brochure-br013003en-en-us.pdf](#)

[eaton-feerum-the-whole-grain-solution-success-story-en-us.pdf](#)

Catalogs

[eaton-digital-nzm-catalog-ca013003en-en-us.pdf](#)

[Compact circuit-breakers and switch-disconnectors up to 1600 A](#)

Characteristic curve

[eaton-circuit-breaker-nzm-mccb-characteristic-curve-050.eps](#)

[eaton-circuit-breaker-current-nzm-mccb-characteristic-curve-004.eps](#)

[eaton-circuit-breaker-nzm-mccb-characteristic-curve-039.eps](#)

Declarations of conformity

[DA-DC-03_N2](#)

Drawings

[eaton-circuit-breaker-switch-nzm-mccb-dimensions-017.eps](#)

[eaton-circuit-breaker-nzm-mccb-dimensions-019.eps](#)

[eaton-circuit-breaker-switch-nzm-mccb-3d-drawing.eps](#)

eCAD model

[ETN.269187.edz](#)

Installation videos

[The new digital NZM Range](#)

[Introduction of the new digital circuit breaker NZM](#)

mCAD model

[DA-CS-nzm2_3p](#)

[DA-CD-nzm2_3p](#)

Technical data sheets

[eaton-nzm-technical-information-sheet](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)

switchgear must be observed.

10.12 Electromagnetic compatibility

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.13 Mechanical function

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

10.2.2 Corrosion resistance

Meets the product standard's requirements.

10.2.3.1 Verification of thermal stability of enclosures

Meets the product standard's requirements.

10.2.3.2 Verification of resistance of insulating materials to normal heat

Meets the product standard's requirements.

10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects

Meets the product standard's requirements.

10.2.4 Resistance to ultra-violet (UV) radiation

Meets the product standard's requirements.

10.2.5 Lifting

Does not apply, since the entire switchgear needs to be evaluated.

10.2.6 Mechanical impact

Does not apply, since the entire switchgear needs to be evaluated.

10.2.7 Inscriptions

Meets the product standard's requirements.

10.3 Degree of protection of assemblies

Does not apply, since the entire switchgear needs to be evaluated.

10.4 Clearances and creepage distances

Meets the product standard's requirements.

10.5 Protection against electric shock

Does not apply, since the entire switchgear needs to be evaluated.

10.6 Incorporation of switching devices and components

Does not apply, since the entire switchgear needs to be evaluated.

10.7 Internal electrical circuits and connections

Is the panel builder's responsibility.

10.8 Connections for external conductors

Is the panel builder's responsibility.

10.9.2 Power-frequency electric strength

Is the panel builder's responsibility.

10.9.3 Impulse withstand voltage

Is the panel builder's responsibility.

10.9.4 Testing of enclosures made of insulating material

Is the panel builder's responsibility.

Pollution degree

3

Mounting Method

DIN rail (top hat rail) mounting optional

Built-in device fixed built-in technique

Fixed

Climatic proofing

Damp heat, constant, to IEC 60068-2-78

Damp heat, cyclic, to IEC 60068-2-30

Equipment heat dissipation, current-dependent

48 W

Utilization category

A (IEC/EN 60947-2)

Isolation

500 V AC (between auxiliary contacts and main contacts)

300 V AC (between the auxiliary contacts)

Ambient operating temperature - max

70 °C

Ambient operating temperature - min

-25 °C

Ambient storage temperature - max

70 °C

Ambient storage temperature - min

-40 °C

Low-voltage HBC fuse - max

355 A gG/gL

Number of auxiliary contacts (change-over contacts)

0

Number of auxiliary contacts (normally closed contacts)

0

Number of auxiliary contacts (normally open contacts)

0

Protection against direct contact

Finger and back-of-hand proof to DIN EN 50274/VDE 0106 part 110

Degree of protection

IP20 (basic degree of protection, in the operating controls area)

IP20

Direction of incoming supply

As required

Electrical connection type of main circuit

Screw connection

Lifespan, mechanical

20000 operations

Overvoltage category

III

Rated operational current

300 A (380/400 V AC-1, making and breaking capacity)

300 A (415 V AC-1, making and breaking capacity)

200 A (690 V AC-1, making and breaking capacity)

200 A (660-690 V AC-3, making and breaking capacity)

Degree of protection (IP), front side

IP66 (with door coupling rotary handle)

IP40 (with insulating surround)

Degree of protection (terminations)

IP00 (terminations, phase isolator and strip terminal)

IP10 (tunnel terminal)

Number of poles

Three-pole

Terminal capacity (copper strip)

Min. 2 segments of 16 mm x 0.8 mm at rear-side connection
(punched)

Max. 10 segments of 16 mm x 0.8 mm at rear-side connection
(punched)

Min. 2 segments of 9 mm x 0.8 mm at box terminal

Max. 10 segments of 16 mm x 0.8 mm at box terminal

Lifespan, electrical

5000 operations at 690 V AC-3

7500 operations at 690 V AC-1

6500 operations at 400 V AC-3

6500 operations at 415 V AC-3

10000 operations at 400 V AC-1

Functions

System and cable protection

Current limiting circuit breaker

Shock resistance

20 g (half-sinusoidal shock 20 ms)

Position of connection for main current circuit

Front side

Rated operational current for specified heat dissipation (In)

200 A

Power loss

48 W

Release system

Thermomagnetic release

Short-circuit total breaktime

< 10 ms

Rated short-time withstand current (t = 0.3 s)

1.9 kA

Rated short-time withstand current (t = 1 s)

1.9 kA

Short-circuit release non-delayed setting - max

2000 A

Short-circuit release non-delayed setting - min

1200 A

Terminal capacity (control cable)

16 mm² - 18 mm² (2x)

14 mm² - 18 mm² (1x)

Terminal capacity (copper busbar)

Min. 16 mm x 5 mm direct at switch rear-side connection

M8 at rear-side screw connection

Max. 20 mm x 5 mm direct at switch rear-side connection

Terminal capacity (copper solid conductor/cable)

16 mm² (1x) at tunnel terminal

6 mm² - 12 mm² (1x) at box terminal

6 mm² - 11 mm² (1x) direct at switch rear-side connection

Terminal capacity (aluminum solid conductor/cable)

16 mm² (1x) at tunnel terminal

Terminal capacity (copper stranded conductor/cable)

4 mm² - 350 mm² (1x) at box terminal

4 mm² - 3/0 mm² (1x) direct at switch rear-side connection

4 mm² - 350 mm² (1x) at tunnel terminal

Handle type

Rocker lever

Short delay current setting (I_{sd}) - max

0 A

Short delay current setting (I_{sd}) - min

0 A

Instantaneous current setting (I_i) - max

10 A

Instantaneous current setting (I_i) - min

6 A

Number of operations per hour - max

120

Overload current setting (I_r) - max

200 A

Overload current setting (I_r) - min

200 A

Rated short-circuit breaking capacity I_{cs} (IEC/EN 60947) at 230 V, 50/60 Hz

85 kA

Rated short-circuit breaking capacity I_{cs} (IEC/EN 60947) at 400/415 V, 50/60 Hz

50 kA

Rated short-circuit breaking capacity I_{cs} (IEC/EN 60947) at 440 V, 50/60 Hz

35 kA

Rated short-circuit breaking capacity I_{cs} (IEC/EN 60947) at 525 V, 50/60 Hz

25 kA

Rated short-circuit breaking capacity I_{cs} (IEC/EN 60947) at 690 V, 50/60 Hz

5 kA

Rated short-circuit making capacity I_{cm} at 400/415 V, 50/60 Hz

105 kA

Rated short-circuit making capacity I_{cm} at 440 V, 50/60 Hz

74 kA

Rated short-circuit making capacity I_{cm} at 525 V, 50/60 Hz

53 kA

Rated short-circuit making capacity I_{cm} at 690 V, 50/60 Hz

40 kA

Standard terminals

Screw terminal

Rated operating voltage U_e (UL) - max

600Y/347 V, 480 V

Rated short-circuit making capacity I_{cm} at 240 V, 50/60 Hz

187 kA

Rated impulse withstand voltage (U_{imp}) at auxiliary contacts

6000 V

Rated impulse withstand voltage (U_{imp}) at main contacts

8000 V

Rated insulation voltage (U_i)

1000 V AC



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia