

Features

- 5G/LTE
- 4x4 MIMO
- 617-6000 MHz
- 7 dBi
- Wi-Fi 6E
- Directional
- IP68
- -40°C to 80°C

RS PRO Multi-Band Antennas

Antenna Directional for

RS PRO 2768465

RS Stock No.: 0434524



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

INTEGRATED MULTI-BAND LTE & 5G PANEL ANTENNA + WI-FI OMNI ANTENNA + PLACE TO INSTALL RS PRO 2768465 (ALL-IN-ONE)

Directional all-in-one antenna for **RS PRO 2768465** is a high performance directional antenna designed for use in a variety of wireless communication applications. This all-in-one product consists of multi-band 5G and Wi-Fi antennas, integrated in IP68 enclosure. It offers 7.5 dBi gain and wide beam width, which makes it suitable for use in both urban and rural environments.

The set contains a Passive PoE splitter, allowing you to split data and power from a single Ethernet cable and maintain gigabit transfer speeds while protecting the LAN port from damage caused by overvoltage, short circuit or improper connection.

Wi-Fi 6E support!

5G / LTE SPECIFICATION

FREQUENCY	0.617 - 0.96 GHz 1.7 - 2.7 GHz 3.3 - 4.6 GHz 4.7 - 6.0 GHz
GAIN	0.617 - 0.96 GHz: 6 dBi 1.7 - 2.7 GHz: 7 dBi 3.3 - 4.6 GHz: 7 dBi 4.7 - 6.0 GHz: 5.5 dBi
SUPPORTED LTE BANDS	1, 2, 3, 4, 5, 7, 8, 9, 10, 12, 13, 14, 17, 18, 19, 20, 22, 25, 26, 27, 28, 29, 30, 33, 34, 35, 36, 37, 38, 39, 40, 41, 42, 43, 44, 46, 47, 48, 49, 52, 53, 65, 66, 67, 68, 69, 71, 85, 103, 106
SUPPORTED 5G BANDS	n1, n2, n3, n5, n7, n8, n12, n13, n14, n18, n20, n25, n26, n28, n29, n30, n34, n38, n39, n40, n41, n46, n47, n48, n53, n65, n66, n67, n71, n77, n78, n80, n81, n82, n83, n84, n85, n86, n89, n90, n95, n97, n98, n100, n101, n256
VSWR	<2.00, max <3.00
BEAMWIDTH	80°/80° ±15°
POLARIZATION	X (+/-45degrees)
IMPEDANCE	50 Ω

5G / LTE SPECIFICATION

FREQUENCY	0.617 - 0.96 GHz 1.7 - 2.7 GHz 3.3 - 4.6 GHz 4.7 - 6.0 GHz
GAIN	0.617 - 0.96 GHz: 6 dBi 1.7 - 2.7 GHz: 7 dBi 3.3 - 4.6 GHz: 7 dBi 4.7 - 6.0 GHz: 5.5 dBi
SUPPORTED LTE BANDS	1, 2, 3, 4, 5, 7, 8, 9, 10, 12, 13, 14, 17, 18, 19, 20, 22, 25, 26, 27, 28, 29, 30, 33, 34, 35, 36, 37, 38, 39, 40, 41, 42, 43, 44, 46, 47, 48, 49, 52, 53, 65, 66, 67, 68, 69, 71, 85, 103, 106
SUPPORTED 5G BANDS	n1, n2, n3, n5, n7, n8, n12, n13, n14, n18, n20, n25, n26, n28, n29, n30, n34, n38, n39, n40, n41, n46, n47, n48, n53, n65, n66, n67, n71, n77, n78, n80, n81, n82, n83, n84, n85, n86, n89, n90, n95, n97, n98, n100, n101, n256
VSWR	<2.00, max <3.00
BEAMWIDTH	80°/80° ±15°
POLARIZATION	X (+-45degrees)
IMPEDANCE	50 Ω

WI-FI SPECIFICATION

FREQUENCY	2.40 - 2.50 GHz 5.0 - 7.125 GHz
GAIN	2.40 - 2.50 GHz : 6 dBi 5.0 - 7.125 GHz : 7.5 dBi
VSWR	<1.70, max <2.00
BEAMWIDTH	360°/25° ±5°
POLARIZATION	Vertical
IMPEDANCE	50 Ω

MECHANICAL SPECIFICATION

MATERIALS	ABS, aluminum, PTFE, Fiberglass
CONNECTOR TYPE	RJ45
INGRESS PROTECTION	IP68
DIMENSIONS	486.0 x 292.2 x 105.6 mm 19.13 x 11.50 x 4.16 inch
WEIGHT	2.8 kg 6.17 lbs
OPERATING TEMPERATURE	From -40°C to 80°C From -40°F to 176°F
POLARIZATION	X (+45degrees)
IMPEDANCE	50 Ω


MOUNTING KIT SPECIFICATION

DIMENSIONS	9.9 x 10.5 x 14.8 cm 3.9 x 4.13 x 5.83 inch
REGULATION RANGE	+/- 30°
MAST DIAMETER RANGE	25 - 60mm 0.98-2.36 inch
MATERIAL	Polyamide with fiberglass + galvanized steel U-Bolts
WEIGHT	0.87kg
MOUNTING PLACE	Wall or mast or ceiling


5G/LTE PLOTS

SPECIFICATION	<p>Category: Passive Components</p> <p>Subcategory: Antennas</p> <p>Type: Multi-Band Antennas, WiFi Antennas, GPS antenna</p> <p>Brand: RS PRO</p> <p>Frequency Range: 617 – 6000 MHz</p> <p>RF Protocols: 5G, LTE, WiFi6 E</p> <p>Gain: 7.5 Bbi</p> <p>Internal/External : External</p> <p>Atena Directivity: Directional</p> <p>Antenna Mounting type: Ceiling, Wall/Pole</p> <p>Mounting Type: Bracket Mount, Pole Mount, Pole Mount, Wall Mount</p> <p>Antena Physical Form: Panel, Square,</p>
----------------------	---


5G/LTE PLOTS




PORT 1&3 - 5G/LTE from 650MHz to 950MHz




PORT 1&3 - 5G/LTE from 1.71GHz to 2.17GHz




PORT 1&3 - 5G/LTE from 2.3GHz to 2.7GHz




PORT 1&3 - 5G/LTE from 3.3GHz to 3.8GHz




PORT 1&3 - 5G/LTE from 4.2GHz to 4.6GHz




PORT 1&3 - 5G/LTE from 5.0GHz to 5.9GHz




PORT 2&4 - 5G/LTE from 650MHz to 950MHz




PORT 2&4 - 5G/LTE from 1.71GHz to 2.17GHz




PORT 2&4 - 5G/LTE from 2.3GHz to 2.7GHz




PORT 2&4 - 5G/LTE from 3.3GHz to 3.8GHz





PORT 2&4 - 5G/LTE from 4.2GHz to 4.6GHz



PORT 2&4 - 5G/LTE from 5.0GHz to 5.9GHz



WI-FI PLOTS



Wi-Fi 2.4GHz and 5GHz and 6GHz

