



2 Piece Combo Kit LXT

DLX2539ST

18V

Includes: DHP490 Combi Drill and DTD157 Impact Driver



Models in kit



**18V Combi Drill Brushless
LXT®
DHP490**



**Impact driver LXT®
DTD157**



18V Combi Drill Brushless LXT® DHP490

Model DHP490 is a Combi Drill powered by an 18V LXT Li-ion battery.

This model ensures sufficient torque by adopting a Brushless Motor is lightweight and compact, easy to handle even in narrow spaces. Features and Benefits: Max.torque of 65Nm, Mechanical 2 speed, Electric brake, Variable speed control by trigger



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Brushless Motor	✓
No load speed	0 - 500 / 1900 min ⁻¹
Max. fastening torque Hard/Soft	50 / 27 Nm
Max Torque	65 Nm
Torque setting	20
Impacts per Minute (IPM)	0 - 7500 / 28500 min ⁻¹
Max. Drilling Diameter in Wood	38 mm
Max. Drilling Diameter in Masonry	13 mm
Max. Drilling Diameter in Steel	13 mm
Drilling Capacity Wood (Auger Bit)	38 mm
Drilling Capacity Wood (Self-feed bit)	38 mm
Drilling Capacity Flat bit	40 mm
Drilling Capacity Hole Saw	51 mm

User benefits

- Keyless chuck for easy bit installation and removal
- Mechanical 2-speed gearing; High speed mode for speedy drilling in light duty applications; Low speed mode for heavy duty applications requiring high torque
- Built-in LED light with pre-glow and afterglow functions illuminates the work area
- Variable speed trigger allows operator to adjust speed based on materials or application
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Battery protection circuit protects against overloading, over-discharging and over-heating

Link to product - www.makitauk.com



Impact driver LXT®

DTD157

18V • 1/4" • 140 Nm • 0 – 3 000 min⁻¹

Extra-compact brushless impact driver with assist mode and three power settings for quick driving.

A compact and light impact wrench with a hex. 1/4" drive shank. A compact tool with a max. torque of 140 Nm. 3-mode operation for A-mode / Hard mode / Soft mode for multiple applications. Handy LED light.



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Brushless Motor	✓
No load speed	0 - 1300 / 3000 min ⁻¹
Max Fastening Torque Impact Drill	140 Nm
Impacts per Minute (IPM)	0 - 2000 / 4100 min ⁻¹
Tightening Capacity Standard Bolt	M5 - M14
Driving Shank	1/4 "
Sound Power Level (L _{WA})	106 dB(A)
Sound Pressure Level (L _{pA})	95 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level, Impact Tightening of Fasteners of the Maximum Capacity of the Tool	11,5 m/s ²
Vibration Uncertainty (K Factor), Impact Tightening of Fasteners of the	1,5 m/s ²

User benefits

- Brushless motor is electronically controlled to optimise battery energy use for longer run time per charge
- LED light illuminates the work site
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Anti wobbling bit structure
- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makita.com



Related products kit

■ Standard MA

BL1850B (2x)
Battery LXT® 5,0 Ah



DC18SD
Battery Charger LXT®



■ Other - DHP490

User manual

Parts drawing

■ Other - DTD157

User manual

Parts drawing