

General Information

Extended Product Type:	S800-RT2125
Product ID:	2CCS800900R0161
EAN:	7612271208240
Catalog Description:	S800-RT2125 Ring tongue terminal connection
Long Description:	The S800-RT2125 is a ring tongue terminal kit. Inside of packaging are two terminals to change 1-pole. The modification can be done very easy and fast.

Categories

Products » Low Voltage Products and Systems » Modular DIN Rail Products » High Performance Circuit Breakers HPCBs Accessories

Ordering

EAN:	7612271208240
Minimum Order Quantity:	2 piece
Customs Tariff Number:	85389040

Dimensions

Product Net Width:	27 mm
Product Net Height:	12 mm
Product Net Depth:	45 mm
Product Net Weight:	0.3 kg

Container Information

Package Level 1 Units:	2 piece
Package Level 1 Width:	100 mm
Package Level 1 Length:	100 mm
Package Level 1 Gross Weight:	0.03 kg
Package Level 1 EAN:	7612271208240

Environmental

Ambient Air Temperature:	Operation -25 ... +60 °C Storage -40 ... +70 °C
RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment

Additional Information

Degree of Protection:	acc. to IEC 60529 IP20
Product Main Type:	Accessories for High Performance Circuit Breakers HPCBs
Product Name:	Accessories for High Performance Circuit Breakers HPCBs
Recommended Screw Driver:	Pozidriv 2
RoHS Date:	0205
Standards:	IEC/EN 60947-2
Terminal Type:	Screw Terminals
Tightening Torque:	3.5 N·m

Certificates and Declarations (Document Number)

Data Sheet, Technical Information:	2CCC413003C0203
Declaration of Conformity - CE:	2CCY412101D0601
RoHS Information:	2CCC413008D0204

Classifications

ETIM 4.0:	EC002278 - Distributor assembly miniature circuit breaker (MCB)
ETIM 5.0:	EC002278 - Distributor assembly miniature circuit breaker (MCB)
Object Classification Code:	F

