

## PRODUCT-DETAILS

# MLBL-01BY

## MLBL-01BY LED block



### General Information

Extended Product Type	MLBL-01BY
Product ID	1SFA611621R2013
EAN	7320500545133
Catalog Description	MLBL-01BY LED block
Long Description	Modular LED block - 24V AC / DC, integrated LED - Yellow - Illuminated

### Ordering

E-Number (Finland)	2315797
E-Number (Sweden)	3705647
EAN	7320500545133
Minimum Order Quantity	10 piece
Customs Tariff Number	85369001

### Dimensions

Product Net Width	0.044 m
Product Net Height	0.01 m
Product Net Depth / Length	0.035 m
Product Net Weight	0.01 kg

## Container Information

Package Level 1 Units	bag 10 piece
Package Level 1 Width	0.11 m
Package Level 1 Height	0.01 m
Package Level 1 Depth / Length	0.15 m
Package Level 1 Gross Weight	0.11 kg
Package Level 1 EAN	7320500373767

## Environmental

RoHS Status	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
-------------	--

## Additional Information

Accessory Type	LED and lamp blocks
Color	Yellow
Connecting Capacity	Flexible with Ferrule 1x 0.75 ... 2.5 mm <sup>2</sup>
Control Circuit	Flexible with Ferrule 2x 0.75 ... 2.5 mm <sup>2</sup>
	Flexible with Insulated Ferrule 1x 0.75 ... 2.5 mm <sup>2</sup>
	Flexible with Insulated Ferrule 2x 0.75 ... 2.5 mm <sup>2</sup>
	Flexible 1x 0.75 ... 2.5 mm <sup>2</sup>
	Flexible 2x 0.75 ... 2.5 mm <sup>2</sup>
Connecting Capacity	Flexible with Ferrule 1x0.75....2.5 mm <sup>2</sup>
Supply Circuit	Flexible with Ferrule 2x0.75....2.5 mm <sup>2</sup>
	Flexible with Insulated Ferrule 1x0.75...2.5 mm <sup>2</sup>
	Flexible with Insulated Ferrule 2x0.75...2.5 mm <sup>2</sup>
	Flexible 1x0.75...2.5 2 square millimeters
	Flexible 2x0.75...2.5 2 square millimeters
Connection Type	Screw Clamp
Degree of Protection	Terminals IP20
Illumination	Illuminated
Lamp Type	24V AC / DC, integrated LED
Luminance	250 millicandela
Mounting Type	Rear mounting
Power Loss	Approximately 0.3 W
Product Main Type	MLBL
Product Name	LED block
Product Range	Modular range
Product Type	MLBL
Rated Current (I <sub>n</sub> )	10 mA
Rated Frequency (f)	50 / 60 Hz
Rated Operational Voltage	24 V AC/DC
Recommended Screw Driver	Pozidriv 2
RoHS Date	0635 4
Suitable For	MCBH-00
	MCBH5-00
	MP1
	MP2
	MP3
	MP4
	MPMT3
	MPMP3
	M2SS1
	M2SS2
	M2SS3
	M2SS4
	M2SS5
	M2SS6

	M3SS1
	M3SS2
	M3SS3
	M3SS4
	M3SS5
	M3SS6
	M3SS7
	M3SS8
	MPM1
Suitable for Product Class	Pilot Devices
Terminal Type	Screw Terminals
Tightening Torque	0.9 N·m
Wave Length (λ)	588 nm
Wire Stripping Length	8 mm

Certificates and Declarations (Document Number)

CQC Certificate	CQC2008010305274953
cULus Certificate	9AKK107046A9925
Data Sheet, Technical Information	1SFC151007C02__
Declaration of Conformity - CCC	2020980305001106
Declaration of Conformity - CE	2CMT2015-005452
DNV GL Certificate	E-14107
EAC Certificate	1SFC150017D1101
Environmental Information	1SAC200078H0001
Instructions and Manuals	1SFC151011M0201
RoHS Information	2CMT2015-005452

Classifications

ETIM 4	EC002024 - Accessories for control circuit devices
ETIM 5	EC000204 - Lamp holder block for control circuit devices
ETIM 6	EC000204 - Lamp holder block for control circuit devices
ETIM 7	EC000204 - Lamp holder block for control circuit devices
Object Classification Code	E
UNSPSC	39121500
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
eClass	V11.0 : 27371209

Categories

Low Voltage Products and Systems → Control Products → Pilot Devices → Accessories

Low Voltage Products and Systems → Control Products → Pilot Devices → Modular Plastic Range

