



Description: CP8910 BNC 2PC crimp for RG59/62TE

Part No: 27-9015

Application: For RG59, 62TFE Cable

Crimp Tool: 24-9858P

Impedance: 50 ohm

Frequency Range: 0~4 GHz


Material: Body Brass Nickel plated
Insulator PE
Contact Phos-bronze Gold plated
Sleeve Brass Nickel plated

RoHS Compliance: Yes

Technical Detail: Refer to Emerson Document P/N 27-0000

DRAWING NO. 27-9015				
REVISIONS				
01	OFFICIAL RELEASE			
	08-18-09	L	L	T H Betty 2008.09.09 08:09:34:05


受控 CONTROLLED DOCUMENT					
编号 P/N	27-9015-C UST	版本 Rev	01	日期 Rel'd Date	SEP 14,09



DIM OUTLINE

TOLERANCE UNLESS OTHERWISE SPECIFIED		DRAWN BY LINDA.WU	DATE 08-18-09
DECIMALS	mm	CHECKED BY LINDA.WU	DATE 08-18-09
X	± 0.5	APPROVED BY THOMAS	DATE 08-18-09
X.X	± 0.3		
X.XX	± 0.1		
ANGLES	± 0.5°	U/M	mm

THIS DRAWING WAS PRODUCED BY COMPUTER,
DO NOT SCALE DRAWING OR UPDATE MANUALLY.

 Connectivity Solutions		
TITLE CP8910 BNC 2PC CRIMP RG59/62TE		
SHEET 1 OF 1	DRAWING NO. 27-9015	SIZE A